




数量	品番	外注方法 A	加工 B	備考
	S2520	170	120	2箇所止
	S3020	220	〃	
	S4020	320	〃	
	S3025	220	170	
	S3525	270	〃	
	S5025	420	〃	
	S6025	520	〃	
	S3030	220	220	
	S3530	270	〃	
	S4030	320	〃	
	S4530	370	〃	
	S5030	420	〃	
	S6030	520	〃	
	S8030	720	〃	
	S1030	920	〃	
	S7035	620	270	
	S8035	720	〃	
	S9035	820	〃	
	S1035	920	〃	
	S1135	1020	〃	
	S1235	1120	〃	
	S1335	1220	〃	
	S1435	1320	〃	
	S3540	270	320	
	S4040	320	〃	
	S4540	370	〃	
	S5040	420	〃	
	S5540	470	〃	
	S6040	520	〃	
	S6540	570	〃	
	S7040	620	〃	
	S8040	720	〃	
	S9040	820	〃	
	S1040	920	〃	
	S1140	1020	〃	
	S1240	1120	〃	
	S1340	1220	〃	
	S1440	1320	〃	
	S1540	1420	〃	
	S1640	1520	〃	
	S1740	1620	〃	
	S1840	1720	〃	

数量	品 番	外形寸法 mm		備 考
		φ	h	
	S6045	520	370	
	S5050	420	420	
	S6050	520	〃	
	S7050	620	〃	
	S8050	720	〃	
	S9050	820	〃	
	S1050	920	〃	
	S1150	1020	〃	
	S1250	1120	〃	
	S1350	1220	〃	
	S1450	1320	〃	
	S1550	1420	〃	
	S1650	1520	〃	
	S1750	1620	〃	
	S1850	1720	〃	
	S9055	820	470	
	S6060	520	520	
	S7060	620	〃	
	S8060	720	〃	
	S9060	820	〃	
	S1060	920	〃	
	S1160	1020	〃	
	S1260	1120	〃	
	S1360	1220	〃	
	S1460	1320	〃	
	S1560	1420	〃	
	S1660	1520	〃	
	S1760	1620	〃	
	S1860	1720	〃	

数量	品番	外形寸法 mm		備考
		A	B	
	S7070	620	620	
	S8070	720	〃	
	S9070	820	〃	
	S1070	920	〃	
	S1170	1020	〃	
	S1270	1120	〃	
	S1470	1320	〃	
	S1670	1520	〃	
	S1870	1720	〃	
	S8080	720	720	
	S9080	820	〃	
	S1280	1120	〃	
	S1480	1320	〃	
	S1680	1520	〃	
	S9090	820	820	
	S1190	1020	〃	
	S8095	720	870	
	S9095	820	〃	
	S1095	920	〃	
	S8010	720	920	
	S9010	820	〃	
	S1010	920	〃	
	S1110	1020	〃	
	S1210	1120	〃	
	S1410	1320	〃	
	S1610	1520	〃	
	S1810	1720	〃	
	S9012	820	1120	
	S1212	1120	〃	
	S1412	1320	〃	
	S1512	1420	〃	
	S1612	1520	〃	

F	変更履歴	特記事項	品番	S		検図	設計	製図	名称	数量
									鉄製基板	
					作成日	縮尺		A3 標準 1:2	整理番号	ページ
			材質	t 2.3 (スチール)						
			色/仕上げ	ナイガイクリーム色 (2.5Y9/1 近似色)				内外電機株式会社 Naigai Engineering Inc.	国番	欠