

R04 コネクタ付ケーブル

Webなら機器対応ケーブル多数取扱!!

■R04P コネクタ対応型番表

形状仕様	芯数	型番	CN1	素材ページ	CN2	素材ページ
PP	2	R04P-PP-□2	R04-P2M-4.8	259	R04-P2M-4.8	259
	3	R04P-PP-□3	R04-P3M-4.8	259	R04-P3M-4.8	259
	5	R04P-PP-□5	R04-P5M-4.8	259	R04-P5M-4.8	259
	6	R04P-PP-□6	R04-P6M-6.3	259	R04-P6M-6.3	259
	8	R04P-PP-□8	R04-P8M-6.3	259	R04-P8M-6.3	259
	8	R04P-PP-F-8	R04-P8M-7.3	259	R04-P8M-7.3	259
12	R04P-PP-□12	R04-P12M-8.5	259	R04-P12M-8.5	259	
SS	2	R04P-SS-□2	R04-P2F-4.8	259	R04-P2F-4.8	259
	3	R04P-SS-□3	R04-P3F-4.8	259	R04-P3F-4.8	259
	5	R04P-SS-□5	R04-P5F-4.8	259	R04-P5F-4.8	259
	6	R04P-SS-□6	R04-P6F-6.3	259	R04-P6F-6.3	259
	8	R04P-SS-□8	R04-P8F-6.3	259	R04-P8F-6.3	259
	8	R04P-SS-F-8	R04-P8F-7.3	259	R04-P8F-7.3	259
12	R04P-SS-□12	R04-P12F-8.5	259	R04-P12F-8.5	259	
PS	2	R04P-PS-□2	R04-P2M-4.8	259	R04-P2F-4.8	259
	3	R04P-PS-□3	R04-P3M-4.8	259	R04-P3F-4.8	259
	5	R04P-PS-□5	R04-P5M-4.8	259	R04-P5F-4.8	259
	6	R04P-PS-□6	R04-P6M-6.3	259	R04-P6F-6.3	259
	8	R04P-PS-□8	R04-P8M-6.3	259	R04-P8F-6.3	259
	8	R04P-PS-F-8	R04-P8M-7.3	259	R04-P8F-7.3	259
12	R04P-PS-□12	R04-P12M-8.5	259	R04-P12F-8.5	259	
P	2	R04P-P-□2	R04-P2M-4.8	259		
	3	R04P-P-□3	R04-P3M-4.8	259		
	5	R04P-P-□5	R04-P5M-4.8	259		
	6	R04P-P-□6	R04-P6M-6.3	259		
	8	R04P-P-□8	R04-P8M-6.3	259		
	8	R04P-P-□8	R04-P8M-7.3	259		
12	R04P-P-□12	R04-P12M-8.5	259			
S	2	R04P-S-□2	R04-P2F-4.8	259		
	3	R04P-S-□3	R04-P3F-4.8	259		
	5	R04P-S-□5	R04-P5F-4.8	259		
	6	R04P-S-□6	R04-P6F-6.3	259		
	8	R04P-S-□8	R04-P8F-6.3	259		
	8	R04P-S-□8	R04-P8F-7.3	259		
12	R04P-S-□12	R04-P12F-8.5	259			
PT	2	R04P-PT-□2	R04-P2M-4.8	259		
	3	R04P-PT-□3	R04-P3M-4.8	259		
	5	R04P-PT-□5	R04-P5M-4.8	259		
	6	R04P-PT-□6	R04-P6M-6.3	259		
	8	R04P-PT-□8	R04-P8M-6.3	259		
	8	R04P-PT-□8	R04-P8M-7.3	259		
12	R04P-PT-□12	R04-P12M-8.5	259			
ST	2	R04P-ST-□2	R04-P2F-4.8	259		
	3	R04P-ST-□3	R04-P3F-4.8	259		
	5	R04P-ST-□5	R04-P5F-4.8	259		
	6	R04P-ST-□6	R04-P6F-6.3	259		
	8	R04P-ST-□8	R04-P8F-6.3	259		
	8	R04P-ST-□8	R04-P8F-7.3	259		
12	R04P-ST-□12	R04-P12F-8.5	259			
PY	2	R04P-PY-□2	R04-P2M-4.8	259	F1.25-V3.5	468
	3	R04P-PY-□3	R04-P3M-4.8	259	F1.25-V3.5	468
	5	R04P-PY-□5	R04-P5M-4.8	259	F1.25-V3.5	468
	6	R04P-PY-□6	R04-P6M-6.3	259	F1.25-V3.5	468
	8	R04P-PY-□8	R04-P8M-6.3	259	F1.25-V3.5	468
	8	R04P-PY-□8	R04-P8M-7.3	259	F1.25-V3.5	468
12	R04P-PY-□12	R04-P12M-8.5	259	F1.25-V3.5	468	
SY	2	R04P-SY-□2	R04-P2F-4.8	259	F1.25-V3.5	468
	3	R04P-SY-□3	R04-P3F-4.8	259	F1.25-V3.7	468
	5	R04P-SY-□5	R04-P5F-4.8	259	F1.25-V3.9	468
	6	R04P-SY-□6	R04-P6F-6.3	259	F1.25-V3.11	468
	8	R04P-SY-□8	R04-P8F-6.3	259	F1.25-V3.13	468
	8	R04P-SY-□8	R04-P8F-7.3	259	F1.25-V3.14	468
12	R04P-SY-□12	R04-P12F-8.5	259	F1.25-V3.16	468	
RP	2	R04P-RP-□2	R04-R2M	260		
	3	R04P-RP-□3	R04-R3M	260		
	5	R04P-RP-□5	R04-R5M	260		
	6	R04P-RP-□6	R04-R6M	260		
	8	R04P-RP-□8	R04-R8M	260		
	12	R04P-RP-□12	R04-R12M	260		
RS	2	R04P-RS-□2	R04-R2F	260		
	3	R04P-RS-□3	R04-R3F	260		
	5	R04P-RS-□5	R04-R5F	260		
	6	R04P-RS-□6	R04-R6F	260		
	8	R04P-RS-□8	R04-R8F	260		
	12	R04P-RS-□12	R04-R12F	260		
RPT	2	R04P-RPT-□2	R04-R2M	260		
	3	R04P-RPT-□3	R04-R3M	260		
	5	R04P-RPT-□5	R04-R5M	260		
	6	R04P-RPT-□6	R04-R6M	260		
	8	R04P-RPT-□8	R04-R8M	260		
	12	R04P-RPT-□12	R04-R12M	260		
RST	2	R04P-RST-□2	R04-R2F	260		
	3	R04P-RST-□3	R04-R3F	260		
	5	R04P-RST-□5	R04-R5F	260		
	6	R04P-RST-□6	R04-R6F	260		
	8	R04P-RST-□8	R04-R8F	260		
	12	R04P-RST-□12	R04-R12F	260		
RPRT	2	R04P-RPRT-□2	R04-R2M	260		
	3	R04P-RPRT-□3	R04-R3M	260		
	5	R04P-RPRT-□5	R04-R5M	260		
	6	R04P-RPRT-□6	R04-R6M	260		
	8	R04P-RPRT-□8	R04-R8M	260		
	12	R04P-RPRT-□12	R04-R12M	260		
RPST	2	R04P-RSRT-□2	R04-R2F	260		
	3	R04P-RSRT-□3	R04-R3F	260		
	5	R04P-RSRT-□5	R04-R5F	260		
	6	R04P-RSRT-□6	R04-R6F	260		
	8	R04P-RSRT-□8	R04-R8F	260		
	12	R04P-RSRT-□12	R04-R12F	260		

■R04J コネクタ対応型番表

形状仕様	芯数	型番	CN1	素材ページ	CN2	素材ページ	
JPJP	2	R04J-JPJP-□2	R04-J2M-4.8	259	R04-J2M-4.8	259	
	3	R04J-JPJP-□3	R04-J3M-4.8	259	R04-J3M-4.8	259	
	5	R04J-JPJP-□5	R04-J5M-4.8	259	R04-J5M-4.8	259	
	6	R04J-JPJP-□6	R04-J6M-6.3	259	R04-J6M-6.3	259	
	8	R04J-JPJP-□8	R04-J8M-6.3	259	R04-J8M-6.3	259	
	8	R04J-JPJP-□8	R04-J8M-7.3	259	R04-J8M-7.3	259	
	12	R04J-JPJP-□12	R04-J12M-8.5	259	R04-J12M-8.5	259	
	JSJS	2	R04J-JSJS-□2	R04-J2F-4.8	259	R04-J2F-4.8	259
		3	R04J-JSJS-□3	R04-J3F-4.8	259	R04-J3F-4.8	259
		5	R04J-JSJS-□5	R04-J5F-4.8	259	R04-J5F-4.8	259
		6	R04J-JSJS-□6	R04-J6F-6.3	259	R04-J6F-6.3	259
		8	R04J-JSJS-□8	R04-J8F-6.3	259	R04-J8F-6.3	259
8		R04J-JSJS-□8	R04-J8F-7.3	259	R04-J8F-7.3	259	
12		R04J-JSJS-□12	R04-J12F-8.5	259	R04-J12F-8.5	259	
JPSJ		2	R04J-JPSJ-□2	R04-J2M-4.8	259	R04-J2F-4.8	259
		3	R04J-JPSJ-□3	R04-J3M-4.8	259	R04-J3F-4.8	259
		5	R04J-JPSJ-□5	R04-J5M-4.8	259	R04-J5F-4.8	259
		6	R04J-JPSJ-□6	R04-J6M-6.3	259	R04-J6F-6.3	259
		8	R04J-JPSJ-□8	R04-J8M-6.3	259	R04-J8F-6.3	259
	8	R04J-JPSJ-□8	R04-J8M-7.3	259	R04-J8F-7.3	259	
	12	R04J-JPSJ-□12	R04-J12M-8.5	259	R04-J12F-8.5	259	
	JP	2	R04J-JP-□2	R04-J2M-4.8	259		
		3	R04J-JP-□3	R04-J3M-4.8	259		
		5	R04J-JP-□5	R04-J5M-4.8	259		
		6	R04J-JP-□6	R04-J6M-6.3	259		
		8	R04J-JP-□8	R04-J8M-6.3	259		
8		R04J-JP-□8	R04-J8M-7.3	259			
12		R04J-JP-□12	R04-J12M-8.5	259			
JS		2	R04J-JS-□2	R04-J2F-4.8	259		
		3	R04J-JS-□3	R04-J3F-4.8	259		
		5	R04J-JS-□5	R04-J5F-4.8	259		
		6	R04J-JS-□6	R04-J6F-6.3	259		
		8	R04J-JS-□8	R04-J8F-6.3	259		
	8	R04J-JS-□8	R04-J8F-7.3	259			
	12	R04J-JS-□12	R04-J12F-8.5	259			
	JPT	2	R04J-JPT-□2	R04-J2M-4.8	259		
		3	R04J-JPT-□3	R04-J3M-4.8	259		
		5	R04J-JPT-□5	R04-J5M-4.8	259		
		6	R04J-JPT-□6	R04-J6M-6.3	259		
		8	R04J-JPT-□8	R04-J8M-6.3	259		
8		R04J-JPT-□8	R04-J8M-7.3	259			
12		R04J-JPT-□12	R04-J12M-8.5	259			
JST		2	R04J-JST-□2	R04-J2F-4.8	259		
		3	R04J-JST-□3	R04-J3F-4.8	259		
		5	R04J-JST-□5	R04-J5F-4.8	259		
		6	R04J-JST-□6	R04-J6F-6.3	259		
		8	R04J-JST-□8	R04-J8F-6.3	259		
	8	R04J-JST-□8	R04-J8F-7.3	259			
	12	R04J-JST-□12	R04-J12F-8.5	259			
	JPY	2	R04J-JPY-□2	R04-J2M-4.8	259	F1.25-V3.5	468
		3	R04J-JPY-□3	R04-J3M-4.8	259	F1.25-V3.5	468
		5	R04J-JPY-□5	R04-J5M-4.8	259	F1.25-V3.5	468
		6	R04J-JPY-□6	R04-J6M-6.3	259	F1.25-V3.5	468
		8	R04J-JPY-□8	R04-J8M-6.3	259	F1.25-V3.5	468
8		R04J-JPY-□8	R04-J8M-7.3	259	F1.25-V3.5	468	
12		R04J-JPY-□12	R04-J12M-8.5	259	F1.25-V3.5	468	
JSY		2	R04J-JSY-□2	R04-J2F-4.8	259	F1.25-V3.5	468
		3	R04J-JSY-□3	R04-J3F-4.8	259	F1.25-V3.7	468
		5	R04J-JSY-□5	R04-J5F-4.8	259	F1.25-V3.9	468
		6	R04J-JSY-□6	R04-J6F-6.3	259	F1.25-V3.11	468
		8	R04J-JSY-□8	R04-J8F-6.3	259	F1.25-V3.13	468
	8	R04J-JSY-□8	R04-J8F-7.3	259	F1.25-V3.14	468	
	12	R04J-JSY-□12	R04-J12F-8.5	259	F1.25-V3.16	468	
	JPP	2	R04J-JPP-□2	R04-J2M-4.8	259	R04-P2M-4.8	259
		3	R04J-JPP-□3	R04-J3M-4.8	259	R04-P3M-4.8	259
		5	R04J-JPP-□5	R04-J5M-4.8	259	R04-P5M-4.8	259
		6	R04J-JPP-□6	R04-J6M-6.3	259	R04-P6M-6.3	259
		8	R04J-JPP-□8	R04-J8M-6.3	259	R04-P8M-6.3	259
8		R04J-JPP-□8	R04-J8M-7.3	259	R04-P8M-7.3	259	
12		R04J-JPP-□12	R04-J12M-8.5	259	R04-P12M-8.5	259	
JPS		2	R04J-JPS-□2	R04-J2F-4.8	259	R04-P2F-4.8	259
		3	R04J-JPS-□3	R04-J3F-4.8	259	R04-P3F-4.8	259
		5	R04J-JPS-□5	R04-J5F-4.8	259	R04-P5F-4.8	259
		6	R04J-JPS-□6	R04-J6F-6.3	259	R04-P6F-6.3	259
		8	R04J-JPS-□8	R04-J8F-6.3	259	R04-P8F-6.3	259
	8	R04J-JPS-□8	R04-J8F-7.3	259	R04-P8F-7.3	259	
	12	R04J-JPS-□12	R04-J12F-8.5	259	R04-P12F-8.5	259	
	JSS	2	R04J-JSS-□2	R04-J2F-4.8	259	R04-P2F-4.8	259
		3	R04J-JSS-□3	R04-J3F-4.8	259	R04-P3F-4.8	259
		5	R04J-JSS-□5	R04-J5F-4.8	259	R04-P5F-4.8	259
		6	R04J-JSS-□6	R04-J6F-6.3	259	R04-P6F-6.3	259
		8	R04J-JSS-□8	R04-J8F-6.3	259	R04-P8F-6.3	259
8		R04J-JSS-□8	R04-J8F-7.3	259	R04-P8F-7.3	259	
12		R04J-JSS-□12	R04-J12F-8.5	259	R04-P12F-8.5	259	
JSP		2	R04J-JSP-□2	R04-J2F-4.8	259	R04-P2M-4.8	259
		3	R04J-JSP-□3	R04-J3F-4.8	259	R04-P3M-4.8	259
		5	R04J-JSP-□5	R04-J5F-4.8	259	R04-P5M-4.8	259
		6	R04J-JSP-□6	R04-J6F-6.3	259	R04-P6M-6.3	259
		8	R04J-JSP-□8	R04-J8F-6.3	259	R04-P8M-6.3	259
	8	R04J-JSP-□8	R04-J8F-7.3	259	R04-P8M-7.3	259	
	12	R04J-JSP-□12	R04-J12F-8.5	259	R04-P12M-8.5	259	

コネクタ付ケーブル

- MS コネクタ付ケーブル
- MS コネクタ付ケーブル(防滴)