


TOOL NO.	REV.	DESCRIPTION	ECN NO	NAME	DATE
DVI24+1 M	1.0	NEW	Y20141015		
DVI24+1 M					14.10.15

ITEM	DESCRIPTION	Q'TY	UNIT	INITS:	SHEET:	OF	REV:
1		2		1	1	10	1.0



P1 PIN ASSIGNMENT
P2
24 24
23 23
22 22
21 21
20 20
19 19
18 18
17 17
16 16
15 15
14 14
13 13
12 12
11 11
10 10
9 9
7 7
6 6
5 5
4 4
3 3
2 2
1 1
S S

NOTE: 1. OPEN/SHORT: 100% Testing Line-Process
2. TEST VOLTAGE: 300V DC/0.1Sec
3. INSULATION RESISTANCE: 20MΩ(MIN)
4. CONDUCTION RESISTANCE: 10Ω(MAX)

