

角シム

ーキリ欠き穴タイプ・丸穴タイプー



📄カタログ規格外品はこちら 📄P.131

■キリ欠き穴タイプ

■丸穴タイプ

RoHS

型式			材質	硬度	T厚さ(T)公差							キリ欠き穴タイプ加工条件 📍f≧3 📍a≧3 📍m≧3 📍n≧3
キリ欠き穴1コ	キリ欠き穴2コ	キリ欠き穴3コ			0.05	0.1	0.2	0.3	0.5	1.0	2.0	
ASAFR	ASFFR	ASCFR	SPCC相当	—	—	±0.03	±0.04	±0.06	±0.11	±0.17	—	キリ欠き穴タイプ加工条件 📍f≧3 📍a≧3 📍m≧3 📍n≧3
ASAFB	ASFFB	ASCFB	黄銅 (C2801P又はC2680P)	—	±0.005	±0.02	±0.03	±0.04	±0.05	±0.08	±0.12	
ASAFS	ASFFS	ASCFS	T=0.05~1.0 SUS304H T=2.0・3.0 SUS304	370~430HV	±0.005	±0.02	±0.03	±0.035	±0.04	±0.05	±0.20	

キリ欠き穴1コ

キリ欠き穴2コ

キリ欠き穴3コ

型式 Type	指定1mm単位		選択 T	指定0.1mm単位				📍穴1コタイプ は指定不要
	A	B		Q	E	C	P	
SPCC相当 黄銅 SUS304(H)								
穴1コ	ASAFR	ASAFB	ASAFS	10~150	10~150	(0.05) 0.1 0.2 0.3 0.5 1.0 2.0 (3.0)	3~31	Q/2+3~
穴2コ	ASFFR	ASFFB	ASFFS	16~200	10~200			B-(Q/2+3)
穴3コ	ASCFR	ASCFB	ASCFS					Q+3~

📍T(0.05), (3.0)はSPCC相当材で指定できません。

Order
注文例

型式

— A — B — T — Q — E — C — P

ASFFB — A100 — B25 — T1.0 — Q12 — E15 — C12 — P70

型式			材質	硬度	T厚さ(T)公差							丸穴タイプ加工条件 📍f≧2 📍a≧2 📍m≧2 📍n≧2 📍h≧2
丸穴1コ	丸穴2コ	丸穴3コ			0.05	0.1	0.2	0.3	0.5	1.0	2.0	
ASACR	ASFCR	ASCCR	SPCC相当	—	—	±0.03	±0.04	±0.06	±0.11	±0.17	—	
ASACB	ASFCB	ASCCB	黄銅 (C2801P又はC2680P)	—	±0.005	±0.02	±0.03	±0.04	±0.05	±0.08	±0.12	
ASACS	ASFCs	ASCCS	T=0.05~1.0 SUS304H T=2.0・3.0 SUS304	370~430HV	±0.005	±0.02	±0.03	±0.035	±0.04	±0.05	±0.20	

丸穴1コ

丸穴2コ

丸穴3コ

型式 Type	指定1mm単位		選択 T	指定0.1mm単位				📍穴1コタイプ は指定不要
	A	B		D	E	C	P	
SPCC相当 黄銅 SUS304(H)								
穴1コ	ASACR	ASACB	ASACS	10~150	10~150	(0.05) 0.1 0.2 0.3 0.5 1.0 2.0 (3.0)	3~100	D/2+2~
穴2コ	ASFCR	ASFCB	ASFCs	15~200	10~200			B-(D/2+2)
穴3コ	ASCCR	ASCCB	ASCCS					D+2~

📍T(0.05), (3.0)はSPCC相当材で指定できません。

Order
注文例

型式

— A — B — T — D — E — C — P

ASACR — A50 — B25 — T0.1 — D7.5 — E25 — C11
ASCCS — A120 — B15 — T3.0 — D10 — E15 — C7 — P45

Delivery
出荷日

1 日目出荷

🚚 ストーク T 当日出荷

200円/1本

📄注文締切

正午迄 📄P.128

Price
価格

■数量スライド価格 (📍1円未満切り捨て) P.127

数量区分	標準対応						個別対応 大口
	小口			大口			
数 量	1~4	5~9	10~19	20~49	50~150	151~300	301~
値引率	基準単価	10%	20%	30%	35%	39%	お見積り
出荷日	通常				+5日	+8日	

📍表示数量超えはWOSにてご確認ください。
📍標準対応大口以上はストーク対応なし

■キリ欠き穴・丸穴 1コタイプ												
A	B	¥基準単価										
		ASAFR・ASACR			ASAFB・ASACB				ASAFS・ASACS			
		T0.1～0.5	T1.0	T2.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0
10～50	10～ 50	550	550	750	650	650	800	890	570	570	730	810
	51～100	760	780	790	1,040	860	870	1,020	900	740	780	880
	101～150	770	790	800	1,220	880	900	1,160	1,050	780	790	1,010
51～70	10～ 50	600	600	750	750	750	850	940	730	730	750	870
	51～100	760	770	780	990	860	880	1,100	1,000	760	820	1,080
	101～150	790	790	800	1,330	890	930	1,270	1,180	810	900	1,140
71～100	10～ 50	600	600	780	800	800	860	1,010	900	730	780	1,020
	51～100	770	780	790	1,000	880	910	1,220	1,020	790	840	1,180
	101～150	790	800	820	1,500	920	970	1,440	1,310	860	940	1,260
101～130	10～ 50	770	780	790	1,000	880	910	1,050	980	760	780	1,030
	51～100	780	790	800	1,310	900	950	1,310	1,220	800	850	1,220
	101～150	800	800	820	1,660	950	1,000	1,620	1,570	860	940	1,510
131～150	10～ 50	770	780	790	1,050	880	910	1,100	1,010	780	790	1,060
	51～100	780	790	810	1,400	920	970	1,400	1,260	860	880	1,260
	101～150	800	820	840	1,810	970	1,030	1,750	1,590	890	970	1,520

■ キリ欠き穴・丸穴 2コタイプ												
A	B	¥基準単価										
		ASFFR・ASFCR			ASFFB・ASFCB				ASFFS・ASFCS			
		T0.1～0.5	T1.0	T2.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0
15～50	10～ 50	650	850	900	700	800	900	1,170	750	750	880	1,030
	51～100	950	960	960	1,290	1,010	1,030	1,310	1,160	860	930	1,150
	101～150	960	970	980	1,490	1,020	1,040	1,470	1,300	890	960	1,290
51～70	10～ 50	750	930	940	830	850	1,000	1,230	840	840	880	1,070
	51～100	880	940	970	960	960	1,020	1,410	980	870	950	1,230
	101～150	960	970	1,000	1,610	1,030	1,050	1,590	1,430	890	1,010	1,390
71～100	10～ 50	750	930	940	850	850	1,020	1,310	850	850	920	1,150
	51～100	900	960	990	980	980	1,040	1,550	990	880	950	1,360
	101～150	970	970	1,010	1,820	1,040	1,090	1,810	1,630	900	1,060	1,580
101～130	10～ 50	950	960	960	1,320	1,030	1,030	1,410	1,170	870	960	1,230
	51～100	960	970	1,010	1,660	1,050	1,070	1,700	1,480	900	1,020	1,480
	101～150	970	970	1,020	2,070	1,080	1,120	2,060	1,840	930	1,130	1,810
131～150	10～ 50	950	960	1,000	1,370	1,030	1,030	1,470	1,220	890	970	1,290
	51～100	960	970	1,020	1,780	1,050	1,070	1,810	1,580	930	1,020	1,580
	101～150	970	1,000	1,080	2,200	1,080	1,150	2,220	2,020	980	1,130	1,940
151～200	10～ 50	1,370	1,410	1,520	3,030	1,490	1,580	3,050	3,250	1,580	1,820	3,120
	51～100	1,390	1,430	1,540	3,210	1,580	1,670	3,220	3,370	1,640	1,880	3,220
	101～150	1,410	1,450	1,560	3,250	1,600	1,690	3,250	3,590	1,750	2,000	3,420
	151～200	1,470	1,510	1,620	3,370	1,660	1,750	3,360	3,810	1,860	2,120	3,620

■キリ欠き穴・丸穴 3コタイプ												
A	B	¥基準単価										
		ASCFR・ASCCR			ASCFB・ASCCB				ASFCs・ASCCS			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
15~50	10~ 50	890	920	920	1,040	990	1,010	1,180	950	850	880	1,060
	51~100	960	970	970	1,310	1,020	1,040	1,320	1,190	880	950	1,180
	101~150	970	980	990	1,510	1,030	1,050	1,490	1,340	910	980	1,320
51~70	10~ 50	890	920	930	1,090	990	1,010	1,240	1,000	840	880	1,100
	51~100	910	940	960	1,320	1,000	1,020	1,420	1,200	870	950	1,260
	101~150	970	980	1,010	1,620	1,040	1,070	1,600	1,470	910	1,030	1,430
71~100	10~ 50	900	930	930	1,170	990	1,010	1,320	1,070	850	920	1,180
	51~100	920	950	980	1,460	1,010	1,040	1,560	1,310	880	950	1,390
	101~150	980	980	1,020	1,840	1,050	1,100	1,820	1,670	930	1,080	1,620
101~130	10~ 50	960	970	970	1,330	1,040	1,040	1,420	1,200	890	980	1,260
	51~100	970	980	1,020	1,680	1,070	1,080	1,720	1,520	930	1,050	1,520
	101~150	980	980	1,030	2,090	1,090	1,130	2,080	1,890	950	1,160	1,850
131~150	10~ 50	960	970	1,010	1,380	1,040	1,040	1,490	1,250	910	990	1,320
	51~100	970	980	1,030	1,800	1,070	1,080	1,820	1,620	950	1,050	1,620
	101~150	980	1,020	1,090	2,230	1,090	1,160	2,250	2,070	1,000	1,160	1,990
151~200	10~ 50	1,470	1,530	1,630	3,270	1,600	1,700	3,290	3,490	1,690	1,960	3,360
	51~100	1,490	1,550	1,650	3,450	1,690	1,790	3,460	3,610	1,750	2,020	3,460
	101~150	1,520	1,580	1,680	3,490	1,710	1,810	3,490	3,830	1,860	2,140	3,660
	151~200	1,580	1,640	1,740	3,610	1,770	1,870	3,600	4,030	1,960	2,250	3,840

33
カラー・シム
ワッシャー