


規格追加  
赤字表示  
追加

SHAFTS - ONE SIDE MALE SCREW / BOTH SIDE MALE SCREW TYPE-

シャフト  
一片端段付おねじ/両端段付おねじ



軸端部の直角度精度が高い(L 0.03)、精密シャフトはP.241をご覧ください。



Table with columns: Type, Material, Hardness, Surface Treatment, D, g6, h5, f8. Includes sub-tables for single and double end threads and material options like SFUF, SFUX, SSFAX, etc.



軸端加工部(ネジ有効長さ+約10mm)加工のための焼きなましによる硬度低下の可能性がります。P.148  
寸公差・真円度・真直度・直角度・同軸度・硬度変化 P.147  
低温黒色クロムメッキの特長 P.162

Table with columns: Type, D, L, F・T, B・S, P・Q, M・N (並目) 選択, (Y) Max, R, C. Includes a table for thread pitch and diameter.

Alterations table with columns: Alterations, Code, Spec., ¥/1Code. Lists various modification options like LKC, SC, WSC, FC, WFC.

Alterations table with columns: Alterations, Code, Spec., ¥/1Code. Lists modification options like RC, WRC, KC, MMC, MMS, NMC, NMS.

価格改訂  
大口対応  
ステンレス・めっき品  
脱脂洗浄サービス  
http://fa.misumi.jp

数量スライド価格 (※1円未満切り捨て) P.133  
SUJ2相当 D公差 g6 D8-D12

Table showing quantity discounts for SUJ2 equivalent shafts with D公差 g6 D8-D12. Columns include quantity ranges and prices.

カタログ規格外品はこちら P.137  
CADデータフォルダ名: 01\_Shafits

Table showing quantity discounts for catalog standard parts. Columns include quantity ranges and prices.

Table with columns: 型式, Type, D, 規格, L51, L101, L151, L201, L301, L401, L501, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

Table with columns: 型式, Type, D, 規格, L51, L101, L151, L201, L301, L401, L501, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

D公差h5は、上記価格に¥390プラス。

Table with columns: 型式, Type, D, 規格, L51, L101, L151, L201, L301, L401, L501, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

D公差h5は、上記価格に¥390プラス。

Table with columns: 型式, Type, D, 規格, L51, L101, L151, L201, L301, L401, L501, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

D公差h5は、上記価格に¥390プラス。

Table with columns: 型式, Type, D, 規格, L101, L201, L401, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

D公差h5は、上記価格に¥390プラス。

Table with columns: 型式, Type, D, 規格, L101, L201, L401, L601, L801, L1001, L1201. Lists various shaft types and their dimensions.

1 シャフト

**規格追加**  
赤文字表示  
: 追加

SHAFTS -ONE SIDE MALE SCREW / BOTH SIDE MALE SCREW TYPE-

# シャフト

一片端段付おねじ/両端段付おねじ

**価格改訂**

□: 値下げ価格  
□: 新価格  
□: スライド値引率変更

**大口**  
対応  
**BIG ORDER**

ステンレス・めっき品  
**脱脂洗浄サービス**  
対応商品詳細は下記URLへ  
<http://fa.misumi.jp>

型式		¥基準単価						
Type	D	最短L ↓ 50	L51 ↓ 100	L101 ↓ 150	L151 ↓ 200	L201 ↓ 300	L301 ↓ 400	L401 ↓ 500
RSFAF	8	1,250	1,500	1,800	2,110	2,420	2,780	3,320
	10	1,270	1,570	1,880	2,240	2,660	3,020	3,400
	12	1,330	1,710	2,080	2,440	2,890	3,390	3,870
	13	1,340	1,720	2,090	2,520	3,020	3,520	4,030
	15	1,790	2,330	2,920	3,580	4,140	4,770	5,390
	16	1,790	2,390	2,970	3,690	4,370	4,980	5,600
	18	1,860	2,520	3,180	3,940	4,690	5,440	5,990
	20	1,920	2,680	3,390	4,220	5,070	5,680	6,300
	25	2,250	3,170	4,080	4,970	5,930	6,800	7,620
	30	2,570	3,680	4,590	5,700	6,700	7,830	9,140
RSSFAF	8	1,380	1,750	2,180	2,590	3,100	3,650	4,380
	10	1,410	1,840	2,280	2,750	3,390	3,950	4,550
	12	1,510	2,070	2,600	3,110	3,830	4,620	5,390
	13	1,520	2,070	2,620	3,170	3,920	4,700	5,490
	15	2,000	2,730	3,500	4,320	5,200	6,160	7,120
	16	2,030	2,830	3,610	4,510	5,540	6,530	7,530
	18	2,100	2,980	3,840	4,780	5,920	7,060	8,030
	20	2,140	3,110	4,020	5,040	6,280	7,300	8,340
	25	2,640	3,900	5,140	6,370	8,030	9,590	11,110
	30	2,970	4,550	5,870	7,390	9,250	11,220	13,390

型式		¥基準単価						
Type	D	最短L ↓ 50	L51 ↓ 100	L101 ↓ 150	L151 ↓ 200	L201 ↓ 300	L301 ↓ 400	L401 ↓ 500
RSFAX	8	1,550	1,960	2,460	2,850	3,210	3,580	4,290
	10	1,560	2,070	2,470	3,090	3,450	3,820	4,180
	12	1,680	2,210	2,720	3,230	3,730	4,220	4,720
	13	1,690	2,220	2,740	3,360	3,880	4,380	4,890
	15	1,970	2,560	3,270	3,980	4,610	5,230	5,860
	16	1,970	2,660	3,270	4,200	4,830	5,450	6,080
	18	2,110	2,810	3,540	4,480	5,230	5,970	6,330
	20	2,210	3,040	3,750	4,800	5,670	6,020	6,890
	25	2,600	3,570	4,530	5,460	6,600	7,420	8,030
	30	2,960	4,180	4,910	6,490	7,240	8,550	9,860
RSSFAX	8	1,670	2,180	2,800	3,290	3,850	4,410	5,330
	10	1,680	2,320	2,840	3,560	4,130	4,730	5,550
	12	1,850	2,540	3,190	3,850	4,640	5,420	6,220
	13	1,850	2,540	3,190	3,960	4,750	5,550	6,350
	15	2,200	2,920	3,790	4,670	5,640	6,620	7,590
	16	2,240	3,060	3,850	4,970	5,990	6,990	8,010
	18	2,470	3,220	4,150	5,290	6,450	7,590	8,370
	20	2,600	3,410	4,310	5,560	6,850	7,610	8,900
	25	3,350	4,270	5,580	6,850	8,690	10,210	11,520
	30	3,770	5,090	6,180	8,190	9,780	11,950	14,100

1 シャフト