

溝付ガイドレール

—スタンダードタイプ/油溝なし・油溝付(ガイド溝高さ5mm・8mm・15mm)—

追加加工価格も数量スライド適用 P.49

RoHS

型式		材質	硬度	S ガイド溝高さ	U	R
油溝なし	油溝付					
GR5SC	GR5SCM	SKS3	53~56HRC	5	2.5	R≤0.3
GR5MC	GR5MCM	HPM2T相当	37~41HRC			
GR5S	GR5SM	SKS3	53~56HRC	5	3.5	R≤0.8
GR5M	GR5MM	HPM2T相当	37~41HRC			
GR8S	GR8SM	SKS3	53~56HRC	8	4.5	R≤0.8
GR8M	GR8MM	HPM2T相当	37~41HRC			
GR15S	GR15SM	SKS3	53~56HRC	15	5	R≤0.8
GR15M	GR15MM	HPM2T相当	37~41HRC			

■取付ボルト穴2ヶ所 **■取付ボルト穴3ヶ所** **ガイド溝高さ (5mm・8mm)**

■取付ボルト穴4ヶ所

■ボルト穴サイズ表

W	T	d1	d2	t1	ω1
10	12.5・15	8	4.5	5	4.5
12.5	12.5・15・20	8	4.5	5	5
15	12.5・15・20・25	9.5	5.5	6	6
20	15・20	11	6.5	7	7
25	20・25・29・30・34	14	9	9	9
35	34・39	17	11.5	11	12

※ガイド溝高さ15mm (GR15□)のみ適用ガイド溝高さ5mm・8mm (GR5□□・GR8□□)はC≤0.3となります。
 ※指示のない角部はC≤1となります。

■油溝詳細 (GR5SCM・GR5MCM・GR5SM・GR5MM・GR8SM・GR8MM・GR15SM・GR15MM)

■油溝ピッチ算出方法
 $P = (T - S - 2e - N) \times 2$

■油溝詳細寸法

T-S	e	N	f	R
T-S≤7.5	1.5	1.5	0.3	1.0
T-S≥10	2.0	2.0	0.5	1.25

※L≤P+10の時、油溝が1サイクル(1ピッチ)分、切れない場合がありますのでご注意ください。

Price 価格

数量	1~9	10~19	20~30	表示数量超えは
値引率	基準単価	5%	10%	価格・出荷日お見積り

■数量スライド価格 (1円未満切り捨て) P.47

■ガイド溝高さ5mm・8mm 油溝なし

W	T	¥基準単価 1~9本					
		L35~90		L100~150		L160~200	
		GR5S GR8S GR5SC	GR5M GR8M GR5MC	GR5S GR8S GR5SC	GR5M GR8M GR5MC	GR5S GR8S	GR5M GR8M
10	12.5	3,350	3,090	3,350	3,090		
	15						
12.5	12.5	3,030	2,790	4,870	4,150		
	15	3,110	2,870	4,950	4,230		
15	12.5	3,110	2,870	5,190	4,390		
	15	3,110	2,870	4,950	4,230		
20	12.5	3,110	2,870	5,110	4,310		
	15	3,110	2,870	5,190	4,390		
25	12.5	3,190	2,950	5,350	4,390		
	15	3,110	2,870	5,190	4,390	6,230	5,270
30	12.5	3,190	2,950	5,350	4,390	6,390	5,270
	15	3,430	2,950	5,670	4,550	6,790	5,430
35	12.5	3,510	3,030	5,830	4,630	7,030	5,590
	15	3,860	3,270	6,150	4,870	7,350	5,830
40	12.5	3,980	3,350	6,310	4,950	7,590	5,910
	15	4,100	3,510	6,470	5,110	7,750	6,150

■ガイド溝高さ5mm・8mm 油溝付

W	T	¥基準単価 1~9本			
		L40~90		L100~150	
		GR5SM GR8SM GR5SCM	GR5MM GR8MM GR5MCM	GR5SM GR8SM GR5SCM	GR5MM GR8MM GR5MCM
10	12.5	3,810	3,520	3,810	3,520
	15				
12.5	12.5	3,490	3,250	5,700	4,980
	15	3,570	3,330	5,780	5,060
15	12.5	3,570	3,330	6,020	5,220
	15	3,570	3,330	5,780	5,060
20	12.5	3,570	3,330	5,940	5,140
	15	3,570	3,330	6,020	5,220
25	12.5	3,650	3,410	6,180	5,220
	15	3,570	3,330	6,020	5,220
30	12.5	3,650	3,410	6,180	5,220
	15	3,890	3,410	6,500	5,380
35	12.5	3,970	3,490	6,660	5,460
	15	4,330	3,730	6,980	5,700
40	12.5	4,450	3,810	7,140	5,780
	15	4,570	3,970	7,300	5,940

■ガイド溝高さ15mm 油溝なし

W	T	¥基準単価 1~9本					
		L60~90		L100~150		L160~200	
		GR15S GR15M	GR15S GR15M	GR15S GR15M	GR15S GR15M	GR15S GR15M	GR15S GR15M
20	29	5,690	5,650	8,030	7,840	13,420	13,170
	34	6,640	6,540	8,910	8,650	14,790	14,480
25	29	7,480	7,410	9,590	9,330	16,150	15,730
	34	8,990	8,900	11,330	11,090	17,910	17,390
35	29	9,970	9,890	12,990	12,160	19,340	18,830
	39						

■ガイド溝高さ15mm 油溝付

W	T	¥基準単価 1~9本			
		L60~90		L100~150	
		GR15SM GR15MM	GR15SM GR15MM	GR15SM GR15MM	GR15SM GR15MM
25	29	7,640	7,530	10,250	9,950
	34	8,610	8,530	11,030	10,730
35	29	10,340	10,240	13,030	12,760
	39	11,470	11,380	14,250	13,980

■ガイド溝高さ5mm・8mm

型式		T 選択	L	ボルト 穴数	A	B	C
油溝なし	油溝付						
GR5SC GR5MC GR5SCM GR5MCM	(SKS3) (HPM2T相当)	10	12.5 (*1) 15	35 (*1)	2	7.5	—
				40			
				50 60 70			
				80			
GR5S GR5M GR8S GR8M	(SKS3) (HPM2T相当)	12.5	15 (*2) 20	35 (*1)	2	7.5	—
				40			
				50 60 70			
				80			
GR5SM GR5MM GR8SM GR8MM	(SKS3) (HPM2T相当)	15	25 (*2) 30	40 50 60	2	7.5	—
				70 80 90 100 110 120			
				130			
				140			
GR5SM GR5MM GR8SM GR8MM	(SKS3) (HPM2T相当)	20	30 (*2) 35	40 50 60 70 80 90	2	10	—
				100 110 120 130 140 150			
				160			
				180			
GR5SM GR5MM GR8SM GR8MM	(SKS3) (HPM2T相当)	25	35 (*2) 40	40 50 60 70 80 90	2	10	—
				100 110 120 130 140 150			
				160			
				180			

※ (*1)は、ガイド溝高さ5mm・油溝なしタイプのみ適用 ※ (*2)は、ガイド溝高さ5mmタイプのみ適用

■ガイド溝高さ15mm

型式		T 選択	L	ボルト 穴数	A	B	C
油溝なし	油溝付						
GR15S GR15M	(SKS3) (HPM2T相当)	20	30	80 90	2	10	—
				100 110 120 130 140 150 160			
				180			
				200			
GR15S GR15M	(SKS3) (HPM2T相当)	25	34	60 70 80 90	2	10	—
				100 110 120 130 140 150 160			
				170 180			
				190 200			
GR15SM GR15MM	(SKS3) (HPM2T相当)	35	39	60 70 80 90 100	2	10	—
				110 120 130 140 150 160			
				170 180			
				190 200			

Order 注文例 **Example 使用例**

型式: GR5M15 - 20 - 80 溝付ガイドレール(ガイド溝高さ15mm)使用例

Delivery 出荷日 **5** 日目発送 ストック B 300円/1本 P.48

※ 同一サイズ3本以上は一律810円

Alterations 追加加工 **3** 日目発送 ストック A 500円/1本 P.48

※ 同一サイズ3本以上は一律1,350円

スライドコア フランジ厚8mm

Alteration

Code **Spec.** **¥/1Code**

W	T	M
10	12.5・15	M
12.5	12.5・15・20	M5
15	12.5・15・20・25	M6
20	15・20	M8
25	25・30	M10
35	20・25・29・30・34	M10

取りはずし用タップ加工を2ヶ所(両端)に行います。
 ※ W10~25に適用

500