

WASHERS ワッシャ・スペーサ

MSRB

t	t
0.1	±0.020
0.2	±0.020
0.3	±0.030
0.5	±0.030
1.0	±0.040
2.0	±0.090

材質 SK5

LRB

t	t
0.1	±0.020
0.2	±0.020
0.3	±0.030
0.5	±0.030
1.0	±0.040

材質 SK5

T・R

材質 S45C
硬度 48~52HRC

K・W

d	t	K	W
+0.3	±0.005	+0.1	±0.005
+0.2	±0.01	+0.1	±0.01

材質 S45C
硬度 48~52HRC

SRW

材質 SS400

SPW

材質 S45C

D	d	型式	t
6.5	4	MSRB	*4
7	4.5		*4.5
8	5		*5
9	5.5		*5.5
10	6		*6
13	6.5		*6.5
16	8		*8
17	10		*10
18	12		*12
24	13		*13
27	16	*16	
27	20	*20	

*の付いたサイズにt=2.0はありません。

D	d	型式	t
6	4	LRB	4
7	5		5
8	6		6
10	8		8
13	10		10
16	13	13	0.1
19	16	16	0.2
23	20	20	0.3
			0.5
			1.0

D	d	型式	t
11.5	4	T	6.5
13	5		8
15	6		10
18	8		13
21	10		16
23	12	20	
16	4	R	6.5-16
18	5		6.5-18
18	6		8-18
20	8		8-20
22	10		8-22
20	10		10-20
22	12		10-22
25	15		10-25
27	20		10-27
25	20		13-25
27	25	13-27	
30	30	13-30	
30	10	16-30	
35	16	16-35	
40	20	16-40	
35	12	20-35	
40	12	20-40	

D	d	型式	t
10	6	K	10
13	8		13
16	10		16
20	12		20
8	5	W	10
11	6		13
14	8		16
17	10		20

D	d	t	型式	
12	5.3	3	SRW	
15				8
19				10
22				13
22	6.4	4	16	
26			20	
30	8.4	5	25	

D	型式	d
13	SPW	4.5
		5.5
		6.5
		8.5
		10.5
16	16	6.5
20	20	10.5
25	25	12.5

Order 注文例

- MSRB・LRB 型式 - t
MSRB10 - 0.1
- T・R・K・W SRW 型式
T10
R16-30
- SPW 型式 - d
SPW13 - 5.5

SPWG (欠円タイプ)

材質 S45C

STR

材質 S45C
硬度 46~50HRC

SW

材質 S45C
硬度 48~52HRC

SSWA

材質 SS400

USR

材質 S45C
硬度 20~25HRC

SBW

材質 S45C
硬度 48~52HRC

Delivery 出荷日 在庫品 Order 注文例

- STR SW USR 型式
SW 22
USR13

- SSWA 型式 - t
SSWA24 - 3.0
- SPWG SBW 型式 - d
SBW27 - 8

D	K	型式	d
13	5	SPWG	5.5
16	6		6.5
20	7		8.5
25	8		10.5
			12.5

D	d	t	型式
16	5.5	3.0	STR
20	6.5	3.5	
25	8.5	4.5	

D	d	t	型式	
10	4.5	3	SW	
12	5.5			10
12	6			12
16	6.5	4		12-6
20	8	5		16
22	10			20
25	12		22	
27	13		25	
30	16		25-12	
35	20	8	27	
40	25		30	
40	20		35	
50	30		40	
50	20		50	

d	適用 スプリング径	型式 Type	D	t
3.0	6	SSWA	5	1.0
5.0	8		7	
6.0	10		9	
7.0	12		11.5	
8.0	14		13	
9.0	16		15	2.0
10.0	18		17	3.0
12.0	20		19	
12.0	22		21	
14.5	25		24	
15.0	27	26	5.0	
17.0	30	29		
20.0	35	34		
23.0	40	39		

D	D2	型式 Type	t
10	22	USR	10
13	27		13
16	32		16
20	37		20
25	44		25
32	54		32
38	64		38
45	74		45

t	型式 Type	D	d
5	SBW	20	5
		22	5
		25	6
		27	5
		30	6
7		35	8