



SC (標準タイプ)

S-SC (フリーサイズタイプ)

E-SC (エコノミータイプ)

Type	寸法公差	
	A・B	T
標準タイプ フリーサイズ	99mm以下	+0.4 0
	100～250mm	+0.5 0
	251mm以上	+0.8 0
エコノミータイプ	99mm以下	+0.4 0
	100～250mm	+0.5 0
	251mm以上	+0.8 0

精度基準は  P.1488

 材質 S50C (生材)

Order 注文例	型式	A	B	T
	SC	100	100	8
Delivery 出荷日	S-SC	380	200	30
	E-SC	210	150	22
3 日目出荷		PM 6:00迄 P40		
ストーク A 翌日出荷 800円/1本		◎3本以上で1明細行当たり一律2,160円		

		¥基準単価 (標準タイプ)															
A	B	T	8	10	13	15	16	20	22	25	30	35	40	50			
60	60		930	970	840	840	840	970									
80			1,020	1,020	880	880	880	1,060									
500			3,960	4,100	3,610	3,790	3,790	4,320									
80			1,020	1,100	930	930	930	1,100	1,150	1,280	1,500	1,850					
100	80		1,060	1,100	1,020	1,150	1,150	1,320	1,410	1,460	1,680	2,030					
125			1,150	1,190	1,100	1,190	1,190	1,370	1,460	1,500	1,760	2,200					
150			1,280	1,370	1,240	1,320	1,320	1,410	1,500	1,590	1,850	2,290					
160			1,320	1,410	1,280	1,410	1,410	1,460	1,540	1,630	1,940	2,380					
200			1,590	1,680	1,460	1,590	1,590	1,720	1,940	2,120	2,380	2,820					
250			2,030	2,160	1,940	2,030	2,030	2,290	2,420	2,560	2,820	3,260					
500			4,010	4,180	3,700	3,880	3,880	4,360	4,620	4,980	5,460	6,250					
100		100		1,150	1,190	1,100	1,190	1,190	1,320	1,370	1,500	1,760	1,940	2,040	2,390		
125			1,280	1,320	1,150	1,240	1,240	1,370	1,410	1,540	1,850	2,290	2,420	2,840			
150			1,370	1,410	1,240	1,320	1,320	1,410	1,500	1,590	1,900	2,340	2,830	3,320			
160			1,500	1,540	1,370	1,460	1,460	1,540	1,630	1,720	2,030	2,470	2,970	3,470			
180			1,590	1,680	1,460	1,540	1,540	1,630	1,720	1,900	2,200	2,640	3,300	3,860			
200			1,680	1,760	1,590	1,680	1,680	1,850	1,980	2,070	2,380	2,820	3,620	4,240			
210			1,760	1,850	1,630	1,760	1,760	1,940	2,070	2,380	2,730	3,300	3,760	4,390			
250			2,160	2,290	2,030	2,160	2,160	2,420	2,510	2,640	3,000	3,570	4,380	5,130			
300			2,510	2,640	2,290	2,560	2,560	2,690	3,000	3,080	3,480	4,050	4,780	5,920			
350			2,950	3,130	2,690	2,950	2,950	3,300	3,440	3,740	4,180	4,840	5,590	6,820			
400			3,390	3,610	3,080	3,350	3,350	3,700	3,920	4,140	4,580	5,240	5,940	7,100			
450			3,830	4,100	3,520	3,740	3,740	4,180	4,400	4,760	5,240	5,940	6,510	7,950			
500			4,230	4,450	3,880	4,100	4,100	4,620	4,800	5,240	5,770	6,520	7,420	8,810			
125	125			1,370	1,410	1,280	1,370	1,370	1,410	1,500	1,590	1,980	2,470	3,040	4,010		
150				1,460	1,680	1,320	1,410	1,410	1,590	1,680	1,760	2,160	2,640	3,220	4,180		
160				1,590	1,810	1,460	1,540	1,540	1,680	1,760	1,940	2,340	2,820	3,390	4,360		
180			1,630	1,850	1,500	1,590	1,590	1,720	1,810	1,980	2,420	2,910	3,480	4,450			
200			1,760	1,900	1,680	1,810	1,810	1,900	2,030	2,250	2,690	3,220	3,830	4,890			
210			1,850	1,940	1,720	1,900	1,900	2,030	2,200	2,380	2,820	3,350	3,960	5,020			
250			2,290	2,380	2,120	2,200	2,200	2,380	2,470	2,640	3,130	3,700	4,360	5,500			
300			2,640	2,730	2,380	2,640	2,640	2,780	3,040	3,170	3,660	4,230	4,890	6,030			
350			3,130	3,220	2,860	3,130	3,130	3,350	3,520	3,830	4,360	4,980	5,680	6,910			
400			3,610	3,700	3,350	3,620	3,620	3,790	4,050	4,260	4,760	5,390	6,080	7,310			
450			4,100	4,180	3,830	4,010	4,010	4,230	4,540	4,800	5,370	6,030	6,780	8,100			
500			4,580	4,670	4,180	4,450	4,450	4,670	5,020	5,460	6,080	6,780	7,570	8,980			

Price 価格	
数量スライド価格 (◎1円未満切り捨て) P.39	
数量区分	標準対応
数量	1～9 10～30 31～
値引率	標準単価 5% お見積り
◎表示数量超えはWOSにてご確認ください。	
価格計算式 A(寸法) × 価格係数 = 基準単価	
(ex) S-SC-300-200-30	
300 × 25 = ¥7,500 (1円単位切り捨て)	
詳細 P.1504 (B・T寸法も自由に変更できます。)	
フリーサイズタイプ・エコノミータイプは追加加工がご利用できます。	

		¥基準単価（標準タイプ）															
A	B	T	8	10	13	15	16	20	22	25	30	35	40	50			
150	150		1,900	1,940	1,720	1,810	1,810	1,980	2,070	2,200	2,470	3,040	3,780	4,890			
180		2,160	2,200	1,980	2,120	2,120	2,380	2,560	2,730	3,170	3,740	4,150	4,990				
200		2,290	2,380	2,160	2,290	2,290	2,600	2,820	3,040	3,520	4,140	4,520	5,290				
210		2,420	2,510	2,290	2,420	2,420	2,690	2,910	3,130	3,660	4,270	4,920	5,780				
250		2,910	3,040	2,730	2,950	2,950	3,000	3,170	3,350	3,960	4,620	5,760	6,520				
300		3,480	3,610	3,220	3,440	3,440	3,520	3,660	3,960	4,670	5,330	6,270	7,380				
350		4,050	4,180	3,700	3,920	3,920	4,010	4,180	4,490	5,330	6,030	6,790	8,260				
400		4,710	4,840	4,270	4,490	4,490	4,580	4,800	5,150	6,120	6,820	7,410	8,810				
450	160		5,240	5,420	4,760	4,980	4,980	5,110	5,330	5,770	6,820	7,570	8,230	9,750			
500		5,460	5,810	5,110	5,420	5,420	5,590	5,860	6,300	7,530	8,320	9,080	10,730				
160		1,810	1,850	1,630	1,720	1,720	1,900	1,980	2,120	2,380	2,950	3,610	4,760				
200		2,030	2,120	1,900	2,030	2,030	2,340	2,560	2,780	3,260	3,880	4,230	5,020				
250		2,560	2,690	2,380	2,600	2,600	2,640	2,820	3,000	3,610	4,270	5,020	5,990				
300		3,130	3,260	2,860	3,080	3,080	3,170	3,300	3,610	4,320	4,980	5,720	7,040				
350		3,700	3,830	3,350	3,570	3,570	3,660	3,830	4,140	4,980	5,680	6,470	7,880				
400		4,270	4,400	3,830	4,050	4,050	4,140	4,360	4,710	5,680	6,380	7,180	8,580				
450	200		4,800	4,980	4,320	4,540	4,540	4,670	4,890	5,330	6,380	7,130	7,970	9,460			
500		5,020	5,370	4,670	4,980	4,980	5,150	5,420	5,860	7,090	7,880	8,760	10,340				
200		2,640	2,780	2,510	2,690	2,690	2,910	3,040	3,260	3,700	4,050	4,400	5,200				
250		3,170	3,350	3,000	3,170	3,170	3,440	3,610	3,920	4,360	4,840	5,370	6,300				
300		3,610	3,830	3,440	3,700	3,700	4,010	4,230	4,540	5,280	5,680	6,250	7,400				
350		4,140	4,400	3,920	4,230	4,230	4,580	4,800	5,200	5,810	6,520	7,180	8,450				
400		4,670	4,980	4,400	4,980	4,980	5,420	5,720	6,160	6,870	7,620	8,360	10,170				
450		5,200	5,590	4,890	5,680	5,680	6,030	6,520	6,740	7,790	8,360	9,600	11,180				
500	250		5,680	6,120	5,330	5,770	5,770	6,300	6,870	7,350	8,410	9,240	10,700	12,150			
250		4,230	4,540	4,010	4,580	4,580	4,840	5,280	5,590	5,640	5,990	6,600	7,700				
300		4,930	5,060	4,710	4,930	4,930	5,420	5,720	6,210	6,470	6,960	7,660	9,020				
350		5,500	5,720	5,240	5,500	5,500	6,120	6,470	7,000	7,470	7,970	8,800	10,700				
400		6,080	6,380	5,770	6,340	6,340	7,090	7,530	8,100	8,320	9,240	10,520	12,280				
450		6,650	7,040	6,300	7,040	7,040	8,140	8,580	9,240	9,730	10,390	11,530	13,600				
500		7,090	7,530	6,780	7,480	7,480	8,410	8,890	9,600	10,300	11,140	12,720	14,300				
300		300		4,890	5,200	4,710	5,420	5,420	6,380	6,740	7,260	7,840	8,230	13,360	15,470		
350	5,640		5,940	5,420	6,210	6,210	7,180	7,570	8,230	9,290	10,040	15,340	17,750				
400	6,380		6,690	6,120	7,130	7,130	8,140	8,630	9,330	10,250	11,180	17,320	20,590				
450	7,130		7,440	6,820	7,840	7,840	8,980	9,510	10,300	11,800	12,410	19,280	22,920				
500	7,700		8,100	7,480	8,010	8,010	9,240	9,950	10,830	12,590	13,640	21,280	24,580				