

ハイス鋼スパイラルマシンリーマ

●右刃左ねじれ12° 0.1mm単位指定タイプ

SPMR

刃径D	公差	刃径D	MT No.
3	+0.007 +0.002	3 ~14	1
3.1~6	+0.009 +0.004	14.1~23	2
6.1~10	+0.012 +0.006	23.1~30	3
10.1~18	+0.015 +0.007		
18.1~30	+0.017 +0.008		

材質 **HSS**

型番 SPMR

刃径D	食付長T	刃長l	全長L	刃数	¥単価1~4本
3	0.5	35	110	6	5,600
3.1	0.5	35	110	6	5,960
3.2	0.5	35	110	6	5,960
3.3	0.5	35	110	6	5,960
3.4	0.5	35	110	6	5,960
3.5	0.5	35	110	6	5,450
3.6	0.5	35	110	6	5,960
3.7	0.5	35	110	6	5,960
3.8	0.5	35	110	6	5,960
3.9	0.5	35	110	6	5,960
4	0.5	35	110	6	5,020
4.1	0.5	45	120	6	5,520
4.2	0.5	45	120	6	5,520
4.3	0.5	45	120	6	5,520
4.4	0.5	45	120	6	5,520
4.5	0.5	45	120	6	4,670
4.6	1	45	120	6	5,520
4.7	1	45	120	6	5,520
4.8	1	45	120	6	5,520
4.9	1	45	120	6	5,520
5	1	45	120	6	4,670
5.1	1	45	120	6	5,160
5.2	1	45	120	6	5,160
5.3	1	45	120	6	5,160
5.4	1	45	120	6	5,160
5.5	1	45	120	6	4,530
5.6	1	50	130	6	4,950
5.7	1	50	130	6	4,950
5.8	1	50	130	6	4,950
5.9	1	50	130	6	4,950
6	1	50	130	6	4,530
6.1	1	50	130	6	5,160
6.2	1	50	130	6	5,160
6.3	1	50	130	6	5,160
6.4	1	50	130	6	5,160
6.5	1	50	130	6	4,670
6.6	1	55	140	6	5,160
6.7	1	55	140	6	5,160
6.8	1	55	140	6	5,160
6.9	1	55	140	6	5,160
7	1	55	140	6	4,670
7.1	1	55	140	6	5,310
7.2	1	55	140	6	5,310
7.3	1	55	140	6	5,310
7.4	1	55	140	6	5,310
7.5	1	55	140	6	4,890
7.6	1	60	150	6	5,310
7.7	1	60	150	6	5,310
7.8	1	60	150	6	5,310
7.9	1	60	150	6	5,310
8	1	60	150	6	5,000
8.1	1	60	150	6	5,960
8.2	1	60	150	6	5,960
8.3	1	60	150	6	5,960
8.4	1	60	150	6	5,960
8.5	1	60	150	6	5,450
8.6	1	70	160	6	5,960
8.7	1	70	160	6	5,960
8.8	1	70	160	6	5,960
8.9	1	70	160	6	5,960
9	1	70	160	6	5,020
9.1	1	70	160	6	5,520
9.2	1	70	160	6	5,520
9.3	1	70	160	6	5,520
9.4	1	70	160	6	5,520
9.5	1	70	160	6	4,670
9.6	1	70	160	6	5,520
9.7	1	70	160	6	5,520

Order 注文例 **SPMR - 10.1** 型番 刃径 (D)

Delivery 出荷日 **3** 日目発送

Price 価格 ■数量スライド価格 (※1円未満切捨て)

数量	1~4	5~9	10~49	50~99	100~
値引率			5%	10%	15%
価格表					

お見積り

切削条件 P.691

●右刃左ねじれ12° 0.01mm単位指定タイプ

SPMR

刃径D	公差	刃径D	MT No.
3.01~30.05	+0.007 0	3.01~14.09	1
		15.01~23.09	2
		24.01~30.05	3

材質 **HSS**

型番 SPMR

刃径D 0.01mm単位指定	食付長T	刃長l	全長L	刃数	¥単価1~4本
3.01 ~ 3.09	0.5	35	110	6	7,400
4.01 ~ 4.09	0.5	35	110	6	7,100
5.01 ~ 5.09	1	45	120	6	6,100
6.01 ~ 6.09	1	50	130	6	6,100
7.01 ~ 7.09	1	55	140	6	6,400
8.01 ~ 8.09	1	60	150	6	6,600
9.01 ~ 9.09	1	70	160	6	6,600
10.01 ~ 10.09	1	70	160	6	7,100
11.01 ~ 11.09	1	75	170	6	7,100
12.01 ~ 12.09	1	75	170	6	7,300
13.01 ~ 13.09	1	80	180	8	7,300
14.01 ~ 14.09	1	85	190	8	8,000
15.01 ~ 15.09	1.5	90	210	8	8,200
16.01 ~ 16.09	1.5	95	215	8	9,800

切削条件 P.691

Order 注文例 **SPMR - 10.01** 型番 刃径 (D)

Delivery 出荷日 **3** 日目発送

Price 価格 ■数量スライド価格 (※1円未満切捨て)

数量	1~4	5~9	10~49	50~99	100~
値引率			5%	10%	15%
価格表					

お見積り

数量	1~4	5~9	10~49	50~99	100~
値引率			5%	10%	15%
価格表					

お見積り