

■ 型番置換表

・2024年7月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番 : OLFLEX CLASSIC 110 2X0.5-100

新型番 : OLFLEX-CLASSIC110-0.5SQ-2-100

	旧販売型番	7/31~販売型番
1	OLFLEX CLASSIC 110 2X0.5	OLFLEX-CLASSIC110-0.5SQ-2
2	OLFLEX CLASSIC 110 3X0.5	OLFLEX-CLASSIC110-0.5SQ-3
3	OLFLEX CLASSIC 110 4X0.5	OLFLEX-CLASSIC110-0.5SQ-4
4	OLFLEX CLASSIC 110 5X0.5	OLFLEX-CLASSIC110-0.5SQ-5
5	OLFLEX CLASSIC 110 7X0.5	OLFLEX-CLASSIC110-0.5SQ-7
6	OLFLEX CLASSIC 110 2X0.75	OLFLEX-CLASSIC110-0.75SQ-2
7	OLFLEX CLASSIC 110 3X0.75	OLFLEX-CLASSIC110-0.75SQ-3
8	OLFLEX CLASSIC 110 3X0.75 BK	OLFLEX-CLASSIC110-0.75SQ-3-BK
9	OLFLEX CLASSIC 110 4X0.75	OLFLEX-CLASSIC110-0.75SQ-4
10	OLFLEX CLASSIC 110 4X0.75 BK	OLFLEX-CLASSIC110-0.75SQ-4-BK
11	OLFLEX CLASSIC 110 5X0.75	OLFLEX-CLASSIC110-0.75SQ-5
12	OLFLEX CLASSIC 110 7X0.75	OLFLEX-CLASSIC110-0.75SQ-7
13	OLFLEX CLASSIC 110 12X0.75	OLFLEX-CLASSIC110-0.75SQ-12
14	OLFLEX CLASSIC 110 2X1.0	OLFLEX-CLASSIC110-1SQ-2
15	OLFLEX CLASSIC 110 3X1	OLFLEX-CLASSIC110-1SQ-3
16	OLFLEX CLASSIC 110 4X1	OLFLEX-CLASSIC110-1SQ-4
17	OLFLEX CLASSIC 110 5X1.0	OLFLEX-CLASSIC110-1SQ-5
18	OLFLEX CLASSIC 110 7X1.0	OLFLEX-CLASSIC110-1SQ-7
19	OLFLEX CLASSIC 110 2X1.5	OLFLEX-CLASSIC110-1.5SQ-2
20	OLFLEX CLASSIC 110 3X1.5	OLFLEX-CLASSIC110-1.5SQ-3
21	OLFLEX CLASSIC 110 4X1.5	OLFLEX-CLASSIC110-1.5SQ-4
22	OLFLEX CLASSIC 110 5X1.5	OLFLEX-CLASSIC110-1.5SQ-5
23	OLFLEX CLASSIC 110 7X1.5	OLFLEX-CLASSIC110-1.5SQ-7
24	OLFLEX CLASSIC 110 2X2.5	OLFLEX-CLASSIC110-2.5SQ-2
25	OLFLEX CLASSIC 110 3G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-3
26	OLFLEX CLASSIC 110 4G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-4
27	OLFLEX CLASSIC 110 5G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-5
28	OLFLEX CLASSIC 110 7G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-7
29	OLFLEX CLASSIC 110 10G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-10
30	OLFLEX CLASSIC 110 12G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-12
31	OLFLEX CLASSIC 110 14G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-14
32	OLFLEX CLASSIC 110 18G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-18
33	OLFLEX CLASSIC 110 21G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-21
34	OLFLEX CLASSIC 110 25G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-25
35	OLFLEX CLASSIC 110 30G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-30
36	OLFLEX CLASSIC 110 35G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-35
37	OLFLEX CLASSIC 110 40G0.5	OLFLEX-CLASSIC110-GY-0.5SQ-40
38	OLFLEX CLASSIC 110 3G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-3
39	OLFLEX CLASSIC 110 4G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-4

40	OLFLEX CLASSIC 110 5G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-5
41	OLFLEX CLASSIC 110 7G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-7
42	OLFLEX CLASSIC 110 9G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-9
43	OLFLEX CLASSIC 110 10G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-10
44	OLFLEX CLASSIC 110 12G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-12
45	OLFLEX CLASSIC 110 16G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-16
46	OLFLEX CLASSIC 110 18G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-18
47	OLFLEX CLASSIC 110 25G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-25
48	OLFLEX CLASSIC 110 34G0.75	OLFLEX-CLASSIC110-GY-0.75SQ-34
49	OLFLEX CLASSIC 110 3G1.0	OLFLEX-CLASSIC110-GY-1SQ-3
50	OLFLEX CLASSIC 110 4G1.0	OLFLEX-CLASSIC110-GY-1SQ-4
51	OLFLEX CLASSIC 110 5G1.0	OLFLEX-CLASSIC110-GY-1SQ-5
52	OLFLEX CLASSIC 110 7G1.0	OLFLEX-CLASSIC110-GY-1SQ-7
53	OLFLEX CLASSIC 110 8G1	OLFLEX-CLASSIC110-GY-1SQ-8
54	OLFLEX CLASSIC 110 9G1	OLFLEX-CLASSIC110-GY-1SQ-9
55	OLFLEX CLASSIC 110 12G1.0	OLFLEX-CLASSIC110-GY-1SQ-12
56	OLFLEX CLASSIC 110 14G1	OLFLEX-CLASSIC110-GY-1SQ-14
57	OLFLEX CLASSIC 110 18G1	OLFLEX-CLASSIC110-GY-1SQ-18
58	OLFLEX CLASSIC 110 20G1	OLFLEX-CLASSIC110-GY-1SQ-20
59	OLFLEX CLASSIC 110 3G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-3
60	OLFLEX CLASSIC 110 3G1.5 BK	OLFLEX-CLASSIC110-GY-1.5SQ-3-BK
61	OLFLEX CLASSIC 110 4G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-4
62	OLFLEX CLASSIC 110 4G1.5 BK	OLFLEX-CLASSIC110-GY-1.5SQ-4-BK
63	OLFLEX CLASSIC 110 5G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-5
64	OLFLEX CLASSIC 110 6G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-6
65	OLFLEX CLASSIC 110 7G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-7
66	OLFLEX CLASSIC 110 9G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-9
67	OLFLEX CLASSIC 110 12G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-12
68	OLFLEX CLASSIC 110 14G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-14
69	OLFLEX CLASSIC 110 18G1.5	OLFLEX-CLASSIC110-GY-1.5SQ-18
70	OLFLEX CLASSIC 110 12G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-12
71	OLFLEX CLASSIC 110 18G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-18
72	OLFLEX CLASSIC 110 3G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-3
73	OLFLEX CLASSIC 110 4G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-4
74	OLFLEX CLASSIC 110 5G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-5
75	OLFLEX CLASSIC 110 7G2.5	OLFLEX-CLASSIC110-GY-2.5SQ-7
76	OLFLEX CLASSIC 110 3G4	OLFLEX-CLASSIC110-GY-4SQ-3
77	OLFLEX CLASSIC 110 5G4	OLFLEX-CLASSIC110-GY-4SQ-5
78	OLFLEX CLASSIC 110 3G6	OLFLEX-CLASSIC110-GY-6SQ-3
79	OLFLEX CLASSIC 110 4G6	OLFLEX-CLASSIC110-GY-6SQ-4
80	OLFLEX CLASSIC 110 5G6	OLFLEX-CLASSIC110-GY-6SQ-5
81	OLFLEX CLASSIC 110 5G10	OLFLEX-CLASSIC110-GY-10SQ-5