

No	商品(長さ抜き)	導体構成(mm)		導体外径(mm)		絶縁体外径(mm)		仕上がり外径(mm)		重量(g)	
		変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後
1	STO-14-2	84/0.18	41/0.254	—	—	—	—	—	—	—	—
2	STO-14-3	84/0.18	41/0.254	—	—	—	—	—	—	245	240
3	STO-14-4	84/0.18	41/0.254	—	—	—	—	—	—	295	290
4	STO-8-3	7/15/0.32	7/24/0.254	—	—	—	—	—	—	690	695
5	STO-8-4	7/15/0.32	7/24/0.254	—	—	—	—	—	—	895	900
6	STO-6-3	7/24/0.32	7/39/0.254	—	—	—	—	—	—	955	970
7	STO-6-4	7/24/0.32	7/39/0.254	—	—	—	—	—	—	1,230	1,250
8	STO-4-3	7/38/0.32	7/61/0.254	—	—	—	—	—	—	1,330	1,340
9	STO-4-4	7/38/0.32	7/61/0.254	—	—	—	—	—	—	1,710	1,730
10	STO-2-3	7/60/0.32	19/35/0.254	8.3	8.4	11.9	12	34.4	34.7	1,910	1,900
11	STO-2-4	7/60/0.32	19/35/0.254	8.3	8.4	11.9	12	38.3	38.6	2,460	2,440
12	STOSB-N-14-2	84/0.18	41/0.254	—	—	—	—	—	—	—	—
13	STOSB-N-14-3	84/0.18	41/0.254	—	—	—	—	—	—	—	—
14	STOSB-N-14-4	84/0.18	41/0.254	—	—	—	—	—	—	355	350

※変更無の場合、“—”と表示