

■型番置換表

- ・2023年3月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。
- ・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番 : VCTF-A-0.3-2-100

新型番 : VCTF-0.3SQ-2-100

	旧販売型番	3/31~販売型番
1	VCTF-A-0.3-2	VCTF-0.3SQ-2
2	VCTF-A-0.3-3	VCTF-0.3SQ-3
3	VCTF-A-0.3-4	VCTF-0.3SQ-4
4	VCTF-A-0.3-5	VCTF-0.3SQ-5
5	VCTF-A-0.3-6	VCTF-0.3SQ-6
6	VCTF-A-0.3-7	VCTF-0.3SQ-7
7	VCTF-A-0.3-8	VCTF-0.3SQ-8
8	VCTF-A-0.3-10	VCTF-0.3SQ-10
9	VCTF-A-0.3-12	VCTF-0.3SQ-12
10	VCTF-A-0.3-16	VCTF-0.3SQ-16
11	VCTF-A-0.3-20	VCTF-0.3SQ-20
12	VCTF-A-0.3-24	VCTF-0.3SQ-24
13	VCTF-A-0.3-30	VCTF-0.3SQ-30
14	VCTF-A-0.3-40	VCTF-0.3SQ-40
15	VCTF-A-0.5-2	VCTF-0.5SQ-2
16	VCTF-A-0.5-3	VCTF-0.5SQ-3
17	VCTF-A-0.5-4	VCTF-0.5SQ-4
18	VCTF-A-0.5-5	VCTF-0.5SQ-5
19	VCTF-A-0.5-6	VCTF-0.5SQ-6
20	VCTF-A-0.5-7	VCTF-0.5SQ-7
21	VCTF-A-0.5-8	VCTF-0.5SQ-8
22	VCTF-A-0.5-10	VCTF-0.5SQ-10
23	VCTF-A-0.5-12	VCTF-0.5SQ-12
24	VCTF-A-0.5-16	VCTF-0.5SQ-16
25	VCTF-A-0.5-20	VCTF-0.5SQ-20
26	VCTF-A-0.5-24	VCTF-0.5SQ-24
27	VCTF-A-0.5-30	VCTF-0.5SQ-30
28	VCTF-A-0.5-40	VCTF-0.5SQ-40
29	VCTF-A-0.75-2	VCTF-0.75SQ-2
30	VCTF-A-0.75-3	VCTF-0.75SQ-3
31	VCTF-A-0.75-4	VCTF-0.75SQ-4
32	VCTF-A-0.75-5	VCTF-0.75SQ-5
33	VCTF-A-0.75-6	VCTF-0.75SQ-6
34	VCTF-A-0.75-7	VCTF-0.75SQ-7
35	VCTF-A-0.75-8	VCTF-0.75SQ-8
36	VCTF-A-0.75-10	VCTF-0.75SQ-10
37	VCTF-A-0.75-12	VCTF-0.75SQ-12
38	VCTF-A-0.75-14	VCTF-0.75SQ-14
39	VCTF-A-0.75-16	VCTF-0.75SQ-16
40	VCTF-A-0.75-20	VCTF-0.75SQ-20
41	VCTF-A-0.75-24	VCTF-0.75SQ-24
42	VCTF-A-0.75-30	VCTF-0.75SQ-30
43	VCTF-A-1.25-2	VCTF-1.25SQ-2
44	VCTF-A-1.25-3	VCTF-1.25SQ-3
45	VCTF-A-1.25-4	VCTF-1.25SQ-4
46	VCTF-A-1.25-5	VCTF-1.25SQ-5
47	VCTF-A-1.25-6	VCTF-1.25SQ-6
48	VCTF-A-1.25-7	VCTF-1.25SQ-7
49	VCTF-A-1.25-8	VCTF-1.25SQ-8
50	VCTF-A-1.25-10	VCTF-1.25SQ-10
51	VCTF-A-1.25-12	VCTF-1.25SQ-12
52	VCTF-A-1.25-14	VCTF-1.25SQ-14
53	VCTF-A-1.25-16	VCTF-1.25SQ-16
54	VCTF-A-1.25-20	VCTF-1.25SQ-20
55	VCTF-A-1.25-24	VCTF-1.25SQ-24
56	VCTF-A-1.25-30	VCTF-1.25SQ-30
57	VCTF-A-2.0-2	VCTF-2SQ-2
58	VCTF-A-2.0-3	VCTF-2SQ-3
59	VCTF-A-2.0-4	VCTF-2SQ-4
60	VCTF-A-2.0-5	VCTF-2SQ-5
61	VCTF-A-2.0-6	VCTF-2SQ-6
62	VCTF-A-2.0-7	VCTF-2SQ-7
63	VCTF-A-2.0-8	VCTF-2SQ-8
64	VCTF-A-2.0-10	VCTF-2SQ-10
65	VCTF-A-2.0-12	VCTF-2SQ-12
66	VCTF-A-2.0-20	VCTF-2SQ-20
67	VCTF-A-3.5-2	VCTF-3.5SQ-2
68	VCTF-A-3.5-3	VCTF-3.5SQ-3
69	VCTF-A-3.5-4	VCTF-3.5SQ-4
70	VCTF-B-0.3-2	EMT-0.3SQ-2
71	VCTF-B-0.3-3	EMT-0.3SQ-3
72	VCTF-B-0.3-4	EMT-0.3SQ-4
73	VCTF-B-0.3-5	EMT-0.3SQ-5
74	VCTF-B-0.3-6	EMT-0.3SQ-6
75	VCTF-B-0.3-7	EMT-0.3SQ-7
76	VCTF-B-0.3-8	EMT-0.3SQ-8
77	VCTF-B-0.3-10	EMT-0.3SQ-10
78	VCTF-B-0.3-12	EMT-0.3SQ-12
79	VCTF-B-0.3-16	EMT-0.3SQ-16
80	VCTF-B-0.3-20	EMT-0.3SQ-20
81	VCTF-B-0.3-24	EMT-0.3SQ-24
82	VCTF-B-0.3-30	EMT-0.3SQ-30
83	VCTF-B-0.3-40	EMT-0.3SQ-40
84	VCTF-B-0.5-16	EMT-0.5SQ-16
85	VCTF-B-0.5-20	EMT-0.5SQ-20
86	VCTF-B-0.5-24	EMT-0.5SQ-24
87	VCTF-B-0.5-30	EMT-0.5SQ-30
88	VCTF-B-0.5-40	EMT-0.5SQ-40
89	VCTF-B-0.75-14	ACS-0.75SQ-14
90	VCTF-B-0.75-16	ACS-0.75SQ-16
91	VCTF-B-0.75-20	ACS-0.75SQ-20
92	VCTF-B-0.75-24	ACS-0.75SQ-24
93	VCTF-B-0.75-30	ACS-0.75SQ-30
94	VCTF-B-1.25-14	ACS-1.25SQ-14
95	VCTF-B-1.25-16	ACS-1.25SQ-16
96	VCTF-B-1.25-20	ACS-1.25SQ-20
97	VCTF-B-1.25-30	ACS-1.25SQ-30
98	VCTF-B-2.0-16	ACS-2SQ-16
99	VCTF-B-2.0-30	ACS-2SQ-30
100	VCTF-BWG-0.75-3	VCTF-BWG-0.75SQ-3
101	VCTF-BWG-1.25-3	VCTF-BWG-1.25SQ-3
102	VCTF-BWG-2.0-3	VCTF-BWG-2SQ-3