

No	商品(長さ抜き)	導体構成(mm)		導体外径(mm)		絶縁体外径(mm)		仕上がり外径(mm)		重量(g)	
		変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後
1	UE/STO(N)/TC 2X14AWG	84/0.18	41/0.254	-	-	-	-	-	-	-	-
2	UE/STO(N)/TC 3EX14AWG	84/0.18	41/0.254	-	-	-	-	-	-	245	240
3	UE/STO(N)/TC 4EX14AWG	84/0.18	41/0.254	-	-	-	-	-	-	295	290
4	UE/STO(N)/TC 3EX8AWG	7/15/0.32	7/24/0.254	-	-	-	-	-	-	690	695
5	UE/STO(N)/TC 4EX8AWG	7/15/0.32	7/24/0.254	-	-	-	-	-	-	895	900
6	UE/STO(N)/TC 3EX6AWG	7/24/0.32	7/39/0.254	-	-	-	-	-	-	955	970
7	UE/STO(N)/TC 4EX6AWG	7/24/0.32	7/39/0.254	-	-	-	-	-	-	1,230	1,250
8	UE/STO(N)/TC 3EX4AWG	7/38/0.32	7/61/0.254	-	-	-	-	-	-	1,330	1,340
9	UE/STO(N)/TC 4EX4AWG	7/38/0.32	7/61/0.254	-	-	-	-	-	-	1,710	1,730
10	UE/STO(N)/TC 3EX2AWG	7/60/0.32	19/35/0.254	8.3	8.4	11.9	12	34.4	34.7	1,910	1,900
11	UE/STO(N)/TC 4EX2AWG	7/60/0.32	19/35/0.254	8.3	8.4	11.9	12	38.3	38.6	2,460	2,440

※変更無の場合、“-”と表示