

No	商品(長さ抜き)	導体構成(mm)		導体外径(mm)		絶縁体外径(mm)		仕上がり外径(mm)		重量(g)	
		変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後	変更前	変更後
1	UE/STO-SB(N)/TC 2X14AWG	84/0.18	41/0.254	-	-	-	-	-	-	-	-
2	UE/STO-SB(N)/TC 3EX14AWG	84/0.18	41/0.254	-	-	-	-	-	-	-	-
3	UE/STO-SB(N)/TC 4EX14AWG	84/0.18	41/0.254	-	-	-	-	-	-	355	350
4	UE/STO-SB(N)/TC 2X8AWG	7/15/0.32	7/24/0.254	-	-	-	-	-	-	-	-
5	UE/STO-SB(N)/TC 4X8AWG	7/15/0.32	7/24/0.254	-	-	-	-	-	-	-	-
6	UE/STO-SB(N)/TC 3X6AWG	7/24/0.32	7/39/0.254	-	-	-	-	-	-	1,130	1,140
7	UE/STO-SB(N)/TC 4X6AWG	7/24/0.32	7/39/0.254	-	-	-	-	-	-	1,420	1,440

※変更無の場合、“-”と表示