

| No | 商品(長さ抜き)              | 導体構成(mm)   |               | 導体外径(mm) |      | 絶縁体外径(mm) |     | 仕上がり外径(mm) |      | 重量(g) |       |
|----|-----------------------|------------|---------------|----------|------|-----------|-----|------------|------|-------|-------|
|    |                       | 変更前        | 変更後           | 変更前      | 変更後  | 変更前       | 変更後 | 変更前        | 変更後  | 変更前   | 変更後   |
| 1  | UE/THHW-LF-14AWG-クロ   | 84/0.18    | 41/0.254      | —        | —    | —         | —   | —          | —    | —     | —     |
| 2  | UE/THHW-LF-14AWG-G/Y  | 84/0.18    | 41/0.254      | —        | —    | —         | —   | —          | —    | —     | —     |
| 3  | UE/THHW-LF-8AWG-クロ    | 7/15/0.32  | 7/24/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 4  | UE/THHW-LF-8AWG-G/Y   | 7/15/0.32  | 7/24/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 5  | UE/THHW-LF-6AWG-クロ    | 7/24/0.32  | 7/39/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 6  | UE/THHW-LF-6AWG-G/Y   | 7/24/0.32  | 7/39/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 7  | UE/THHW-LF-4AWG-クロ    | 7/38/0.32  | 7/61/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 8  | UE/THHW-LF-4AWG-G/Y   | 7/38/0.32  | 7/61/0.254    | —        | —    | —         | —   | —          | —    | —     | —     |
| 9  | UE/THHW-LF-2AWG-クロ    | 7/60/0.32  | 19/35/0.254   | 8.3      | 8.4  | —         | —   | 11.7       | 11.8 | —     | —     |
| 10 | UE/THHW-LF-2AWG-G/Y   | 7/60/0.32  | 19/35/0.254   | 8.3      | 8.4  | —         | —   | 11.7       | 11.8 | 550   | 515   |
| 11 | UE/THHW-LF-1AWG-クロ    | 19/18/0.45 | 19/44/0.254   | 9.8      | 9.4  | —         | —   | 14.4       | 14   | 550   | 515   |
| 12 | UE/THHW-LF-1AWG-G/Y   | 19/18/0.45 | 19/44/0.254   | 9.8      | 9.4  | —         | —   | 14.4       | 14   | 550   | 515   |
| 13 | UE/THHW-LF-1/OAWG-クロ  | 19/18/0.45 | 19/57/0.254   | —        | —    | —         | —   | —          | —    | 640   | 645   |
| 14 | UE/THHW-LF-1/OAWG-G/Y | 19/18/0.45 | 19/57/0.254   | —        | —    | —         | —   | —          | —    | 640   | 645   |
| 15 | UE/THHW-LF-2/OAWG-クロ  | 19/30/0.45 | 7/7/29/0.254  | 12.1     | 13.1 | —         | —   | 16.7       | 17.9 | 800   | 850   |
| 16 | UE/THHW-LF-2/OAWG-G/Y | 19/30/0.45 | 7/7/29/0.254  | 12.1     | 13.1 | —         | —   | 16.7       | 17.9 | 800   | 850   |
| 17 | UE/THHW-LF-3/OAWG-クロ  | 19/30/0.45 | 7/7/39/0.254  | 13.8     | 15.2 | —         | —   | 18.4       | 15.2 | 1,020 | 1,100 |
| 18 | UE/THHW-LF-4/OAWG-クロ  | 19/39/0.45 | 7/7/45/0.254  | 15.7     | 16.3 | —         | —   | 20.3       | 21.1 | 1,290 | 1,270 |
| 19 | UE/THHW-LF-300MCM-クロ  | 19/51/0.45 | 7/7/65/0.254  | 19.6     | 18   | —         | —   | 23.4       | 25.2 | 1,700 | 1,830 |
| 20 | UE/THHW-LF-400MCM-クロ  | 37/35/0.45 | 19/7/32/0.254 | 22.8     | 20.7 | —         | —   | 28.4       | 26.3 | 2,190 | 2,360 |

※変更無の場合、“—”と表示