




NOTE
1. NET WEIGHT: -1:10.10g
-2:11.00g
2. APPLICABLE WIRE: SEE TABLE 2



P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED	13MAY2019	T.G	N.Y
B		REVISED	29FEB2024	M.S	N.Y
C		REVISED	07OCT2025	T.G	N.Y
D		REVISED	20JAN2026	T.G	N.Y



TRADE MARK



DATE CODE MARK



SCALE 1:1




TABLE 1

QTY	FINISH	MATERIAL	NAME	ITEM
-	CONTACT AREA TO HDR CONT:GOLD PLATING OTHER AREA:NICKEL PLATING. HDRコンタクトとの接触領域:金めっき それ以外の領域:ニッケルめっき	COPPER ALLOY 銅合金	REC CONTACT 4Pos. リセコンタクト4極	5
-		HNBR, BLACK 水素化ニトリルゴム, 黒	BUSH L ブッシュ L	4
-		POLYESTER RESIN, BLACK ポリエステル樹脂, 黒	SCREW HSG L スクリューハウジング L	3
-		POLYESTER RESIN, BLACK ポリエステル樹脂, 黒	INNER HOUSING POWER インナーハウジング パワー	2
-		CASE:POLYESTER RESIN, BLACK LOCK SPRING:STAINLESS STEEL ケース:ポリエステル樹脂, 黒 ロックスプリング:ステンレススチール	CASE ASSY L ケース アッセンブリ L	1

リセコネクタ組立て後寸法(参考)
DIMENSION AFTER ASSEMBLY REC CONNECTOR(REF)

TABLE 2

WIRE SIZE 電線サイズ(AWG)	INSULATION DIAMETER 被覆外径	JACKET DIAMETER ジャケット外径
0.50~1.15mm ² (AWG20-17)	Ø1.85-2.65mm	Ø9.10~9.80mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 概 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3
	0 PLC ±
	1 PLC ±0.5
	2 PLC ±0.13
	3 PLC ±0.013
	4 PLC ±0.0001
	ANGLES ±5°

DWN	T.GOTO	13MAY2019
CHK	N.YAMASAKI	13MAY2019
APVD	N.YAMASAKI	13MAY2019
PRODUCT SPEC	108-140119, 140310	
APPLICATION SPEC	114-5540-1	
WEIGHT	SEE NOTE 1	

TE Connectivity		NAME 名称		RESTRICTED TO
		REC CONNECTOR VERTICAL KIT, MMC PUSH ON-P-F		
SIZE	CAGE CODE	DRAWING NO 番号	-	
A3	-	C=2320297	-	

CUSTOMER DRAWING SCALE 2:1 SHEET 1 OF 1 REV D