

■型番置換表

・2023年1月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番：MVVS-A-0.3-2-100

新型番：MVVS-0.3SQ-2-100

|     | 旧販売型番          | 1/31~販売型番      |
|-----|----------------|----------------|
| 1   | MVVS-A-0.3-2   | MVVS-0.3SQ-2   |
| 2   | MVVS-A-0.3-3   | MVVS-0.3SQ-3   |
| 3   | MVVS-A-0.3-4   | MVVS-0.3SQ-4   |
| 4   | MVVS-A-0.3-5   | MVVS-0.3SQ-5   |
| 5   | MVVS-A-0.3-6   | MVVS-0.3SQ-6   |
| 6   | MVVS-A-0.3-7   | MVVS-0.3SQ-7   |
| 7   | MVVS-A-0.3-8   | MVVS-0.3SQ-8   |
| 8   | MVVS-A-0.3-10  | MVVS-0.3SQ-10  |
| 9   | MVVS-A-0.3-12  | MVVS-0.3SQ-12  |
| 10  | MVVS-A-0.3-16  | MVVS-0.3SQ-16  |
| 11  | MVVS-A-0.3-20  | MVVS-0.3SQ-20  |
| 12  | MVVS-A-0.3-30  | MVVS-0.3SQ-30  |
| 13  | MVVS-A-0.3-40  | MVVS-0.3SQ-40  |
| 14  | MVVS-A-0.5-2   | MVVS-0.5SQ-2   |
| 15  | MVVS-A-0.5-3   | MVVS-0.5SQ-3   |
| 16  | MVVS-A-0.5-4   | MVVS-0.5SQ-4   |
| 17  | MVVS-A-0.5-5   | MVVS-0.5SQ-5   |
| 18  | MVVS-A-0.5-6   | MVVS-0.5SQ-6   |
| 19  | MVVS-A-0.5-7   | MVVS-0.5SQ-7   |
| 20  | MVVS-A-0.5-8   | MVVS-0.5SQ-8   |
| 21  | MVVS-A-0.5-10  | MVVS-0.5SQ-10  |
| 22  | MVVS-A-0.5-12  | MVVS-0.5SQ-12  |
| 23  | MVVS-A-0.5-16  | MVVS-0.5SQ-16  |
| 24  | MVVS-A-0.5-20  | MVVS-0.5SQ-20  |
| 25  | MVVS-A-0.5-30  | MVVS-0.5SQ-30  |
| 26  | MVVS-A-0.5-40  | MVVS-0.5SQ-40  |
| 27  | MVVS-A-0.75-2  | MVVS-0.75SQ-2  |
| 28  | MVVS-A-0.75-3  | MVVS-0.75SQ-3  |
| 29  | MVVS-A-0.75-4  | MVVS-0.75SQ-4  |
| 30  | MVVS-A-0.75-5  | MVVS-0.75SQ-5  |
| 31  | MVVS-A-0.75-6  | MVVS-0.75SQ-6  |
| 32  | MVVS-A-0.75-8  | MVVS-0.75SQ-8  |
| 33  | MVVS-A-0.75-10 | MVVS-0.75SQ-10 |
| 34  | MVVS-A-0.75-12 | MVVS-0.75SQ-12 |
| 35  | MVVS-A-0.75-16 | MVVS-0.75SQ-16 |
| 36  | MVVS-A-0.75-20 | MVVS-0.75SQ-20 |
| 37  | MVVS-A-0.75-30 | MVVS-0.75SQ-30 |
| 38  | MVVS-A-1.25-2  | MVVS-1.25SQ-2  |
| 39  | MVVS-A-1.25-3  | MVVS-1.25SQ-3  |
| 40  | MVVS-A-1.25-4  | MVVS-1.25SQ-4  |
| 41  | MVVS-A-1.25-5  | MVVS-1.25SQ-5  |
| 42  | MVVS-A-1.25-6  | MVVS-1.25SQ-6  |
| 43  | MVVS-A-1.25-7  | MVVS-1.25SQ-7  |
| 44  | MVVS-A-1.25-8  | MVVS-1.25SQ-8  |
| 45  | MVVS-A-1.25-10 | MVVS-1.25SQ-10 |
| 46  | MVVS-A-1.25-12 | MVVS-1.25SQ-12 |
| 47  | MVVS-A-1.25-16 | MVVS-1.25SQ-16 |
| 48  | MVVS-A-1.25-20 | MVVS-1.25SQ-20 |
| 49  | MVVS-A-1.25-30 | MVVS-1.25SQ-30 |
| 50  | MVVS-A-2.0-2   | MVVS-2SQ-2     |
| 51  | MVVS-A-2.0-3   | MVVS-2SQ-3     |
| 52  | MVVS-A-2.0-4   | MVVS-2SQ-4     |
| 53  | MVVS-A-2.0-6   | MVVS-2SQ-6     |
| 54  | MVVS-A-2.0-8   | MVVS-2SQ-8     |
| 55  | MVVS-A-2.0-10  | MVVS-2SQ-10    |
| 56  | MVVS-B-0.3-2   | CHC-0.3SQ-2    |
| 57  | MVVS-B-0.3-3   | CHC-0.3SQ-3    |
| 58  | MVVS-B-0.3-4   | CHC-0.3SQ-4    |
| 59  | MVVS-B-0.3-5   | CHC-0.3SQ-5    |
| 60  | MVVS-B-0.3-6   | CHC-0.3SQ-6    |
| 61  | MVVS-B-0.3-7   | CHC-0.3SQ-7    |
| 62  | MVVS-B-0.3-8   | CHC-0.3SQ-8    |
| 63  | MVVS-B-0.3-10  | CHC-0.3SQ-10   |
| 64  | MVVS-B-0.3-12  | CHC-0.3SQ-12   |
| 65  | MVVS-B-0.3-16  | CHC-0.3SQ-16   |
| 66  | MVVS-B-0.3-20  | CHC-0.3SQ-20   |
| 67  | MVVS-B-0.3-30  | CHC-0.3SQ-30   |
| 68  | MVVS-B-0.3-40  | CHC-0.3SQ-40   |
| 69  | MVVS-B-0.5-2   | CHC-0.5SQ-2    |
| 70  | MVVS-B-0.5-3   | CHC-0.5SQ-3    |
| 71  | MVVS-B-0.5-4   | CHC-0.5SQ-4    |
| 72  | MVVS-B-0.5-5   | CHC-0.5SQ-5    |
| 73  | MVVS-B-0.5-6   | CHC-0.5SQ-6    |
| 74  | MVVS-B-0.5-7   | CHC-0.5SQ-7    |
| 75  | MVVS-B-0.5-8   | CHC-0.5SQ-8    |
| 76  | MVVS-B-0.5-10  | CHC-0.5SQ-10   |
| 77  | MVVS-B-0.5-12  | CHC-0.5SQ-12   |
| 78  | MVVS-B-0.5-16  | CHC-0.5SQ-16   |
| 79  | MVVS-B-0.5-20  | CHC-0.5SQ-20   |
| 80  | MVVS-B-0.5-30  | CHC-0.5SQ-30   |
| 81  | MVVS-B-0.5-40  | CHC-0.5SQ-40   |
| 82  | MVVS-B-0.75-2  | CHC-0.75SQ-2   |
| 83  | MVVS-B-0.75-3  | CHC-0.75SQ-3   |
| 84  | MVVS-B-0.75-4  | CHC-0.75SQ-4   |
| 85  | MVVS-B-0.75-5  | CHC-0.75SQ-5   |
| 86  | MVVS-B-0.75-6  | CHC-0.75SQ-6   |
| 87  | MVVS-B-0.75-8  | CHC-0.75SQ-8   |
| 88  | MVVS-B-0.75-10 | CHC-0.75SQ-10  |
| 89  | MVVS-B-0.75-12 | CHC-0.75SQ-12  |
| 90  | MVVS-B-0.75-16 | CHC-0.75SQ-16  |
| 91  | MVVS-B-0.75-20 | CHC-0.75SQ-20  |
| 92  | MVVS-B-0.75-30 | CHC-0.75SQ-30  |
| 93  | MVVS-B-1.25-2  | CHC-1.25SQ-2   |
| 94  | MVVS-B-1.25-3  | CHC-1.25SQ-3   |
| 95  | MVVS-B-1.25-4  | CHC-1.25SQ-4   |
| 96  | MVVS-B-1.25-5  | CHC-1.25SQ-5   |
| 97  | MVVS-B-1.25-6  | CHC-1.25SQ-6   |
| 98  | MVVS-B-1.25-7  | CHC-1.25SQ-7   |
| 99  | MVVS-B-1.25-8  | CHC-1.25SQ-8   |
| 100 | MVVS-B-1.25-10 | CHC-1.25SQ-10  |
| 101 | MVVS-B-1.25-12 | CHC-1.25SQ-12  |
| 102 | MVVS-B-1.25-16 | CHC-1.25SQ-16  |
| 103 | MVVS-B-1.25-20 | CHC-1.25SQ-20  |
| 104 | MVVS-B-2.0-2   | CHC-2SQ-2      |
| 105 | MVVS-B-2.0-4   | CHC-2SQ-4      |
| 106 | MVVS-B-2.0-6   | CHC-2SQ-6      |
| 107 | MVVS-B-2.0-8   | CHC-2SQ-8      |
| 108 | MVVS-B-2.0-10  | CHC-2SQ-10     |
| 114 | SCIC-B-0.18-2  | SCIC-0.18SQ-2  |
| 116 | SCIC-B-0.18-3  | SCIC-0.18SQ-3  |
| 118 | SCIC-B-0.18-4  | SCIC-0.18SQ-4  |
| 120 | SCIC-B-0.18-5  | SCIC-0.18SQ-5  |
| 121 | SCIC-B-0.18-6  | SCIC-0.18SQ-6  |
| 122 | SCIC-B-0.18-7  | SCIC-0.18SQ-7  |
| 123 | SCIC-B-0.18-8  | SCIC-0.18SQ-8  |
| 109 | SCIC-B-0.18-10 | SCIC-0.18SQ-10 |
| 110 | SCIC-B-0.18-12 | SCIC-0.18SQ-12 |
| 111 | SCIC-B-0.18-16 | SCIC-0.18SQ-16 |
| 112 | SCIC-B-0.18-20 | SCIC-0.18SQ-20 |
| 113 | SCIC-B-0.18-24 | SCIC-0.18SQ-24 |
| 115 | SCIC-B-0.18-30 | SCIC-0.18SQ-30 |
| 117 | SCIC-B-0.18-40 | SCIC-0.18SQ-40 |
| 119 | SCIC-B-0.18-50 | SCIC-0.18SQ-50 |