

■ 型番置換表

・1月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 200m購入希望の場合

旧型番 : KIV-0.75-BE-200

新型番 : KIV-0.75SQ-BE-200

	旧販売型番	1/31~販売型番
1	KIV-0.75-BE	KIV-0.75SQ-BE
2	KIV-0.75-BK	KIV-0.75SQ-BK
3	KIV-0.75-GN	KIV-0.75SQ-GN
4	KIV-0.75-R	KIV-0.75SQ-R
5	KIV-0.75-W	KIV-0.75SQ-W
6	KIV-0.75-Y	KIV-0.75SQ-Y
7	KIV-1.25-BE	KIV-1.25SQ-BE
8	KIV-1.25-BK	KIV-1.25SQ-BK
9	KIV-1.25-GN	KIV-1.25SQ-GN
10	KIV-1.25-R	KIV-1.25SQ-R
11	KIV-1.25-W	KIV-1.25SQ-W
12	KIV-1.25-Y	KIV-1.25SQ-Y
13	KIV-2.0-BE	KIV-2SQ-BE
14	KIV-2.0-BK	KIV-2SQ-BK
15	KIV-2.0-GN	KIV-2SQ-GN
16	KIV-2.0-R	KIV-2SQ-R
17	KIV-2.0-W	KIV-2SQ-W
18	KIV-2.0-Y	KIV-2SQ-Y
19	KIV-3.5-BE	KIV-3.5SQ-BE
20	KIV-3.5-BK	KIV-3.5SQ-BK
21	KIV-3.5-GN	KIV-3.5SQ-GN
22	KIV-3.5-R	KIV-3.5SQ-R
23	KIV-3.5-W	KIV-3.5SQ-W
24	KIV-3.5-Y	KIV-3.5SQ-Y
25	KIV-5.5-BE	KIV-5.5SQ-BE
26	KIV-5.5-BK	KIV-5.5SQ-BK
27	KIV-5.5-GN	KIV-5.5SQ-GN
28	KIV-5.5-R	KIV-5.5SQ-R
29	KIV-5.5-W	KIV-5.5SQ-W
30	KIV-5.5-Y	KIV-5.5SQ-Y
31	KIV-8-BE	KIV-8SQ-BE
32	KIV-8-BK	KIV-8SQ-BK
33	KIV-8-GN	KIV-8SQ-GN
34	KIV-8-R	KIV-8SQ-R
35	KIV-8-W	KIV-8SQ-W
36	KIV-8-Y	KIV-8SQ-Y
37	KIV-14-BE	KIV-14SQ-BE
38	KIV-14-BK	KIV-14SQ-BK
39	KIV-14-GN	KIV-14SQ-GN
40	KIV-14-R	KIV-14SQ-R
41	KIV-14-W	KIV-14SQ-W
42	KIV-14-Y	KIV-14SQ-Y
43	KIV-22-BE	KIV-22SQ-BE

44	KIV-22-BK	KIV-22SQ-BK
45	KIV-22-GN	KIV-22SQ-GN
46	KIV-22-R	KIV-22SQ-R
47	KIV-22-W	KIV-22SQ-W
48	KIV-22-Y	KIV-22SQ-Y
49	KIV-38-BE	KIV-38SQ-BE
50	KIV-38-BK	KIV-38SQ-BK
51	KIV-38-GN	KIV-38SQ-GN
52	KIV-38-R	KIV-38SQ-R
53	KIV-38-W	KIV-38SQ-W
54	KIV-38-Y	KIV-38SQ-Y
55	KIV-60-BE	KIV-60SQ-BE
56	KIV-60-BK	KIV-60SQ-BK
57	KIV-60-GN	KIV-60SQ-GN
58	KIV-60-R	KIV-60SQ-R
59	KIV-60-W	KIV-60SQ-W
60	KIV-60-Y	KIV-60SQ-Y
61	KIV-100-BE	KIV-100SQ-BE
62	KIV-100-BK	KIV-100SQ-BK
63	KIV-100-GN	KIV-100SQ-GN
64	KIV-100-R	KIV-100SQ-R
65	KIV-100-W	KIV-100SQ-W
66	KIV-100-Y	KIV-100SQ-Y