

■ 型番置換表

・1月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 200m購入希望の場合

旧型番 : KIV 0.5SQ ア-200

新型番 : KIV-0.5SQ-BE-200

	旧販売型番	1/31~販売型番
1	KIV 0.5SQ ア	KIV-0.5SQ-BE
2	KIV 0.5SQ ㇏	KIV-0.5SQ-R
3	KIV 0.5SQ ㇑	KIV-0.5SQ-Y
4	KIV 0.5SQ ㇒	KIV-0.5SQ-BK
5	KIV 0.5SQ ㇓	KIV-0.5SQ-W
6	KIV 0.5SQ ミドリ	KIV-0.5SQ-GN
7	KIV 0.75SQ ア	KIV-0.75SQ-BE
8	KIV 0.75SQ ア-200-R	KIV-0.75SQ-BE-200-R
9	KIV 0.75SQ ㇏	KIV-0.75SQ-R
10	KIV 0.75SQ ㇏-200-R	KIV-0.75SQ-R-200-R
11	KIV 0.75SQ ㇑	KIV-0.75SQ-Y
12	KIV 0.75SQ ㇑-200-R	KIV-0.75SQ-Y-200-R
13	KIV 0.75SQ ㇒	KIV-0.75SQ-BK
14	KIV 0.75SQ ㇒-200-R	KIV-0.75SQ-BK-200-R
15	KIV 0.75SQ ㇓	KIV-0.75SQ-W
16	KIV 0.75SQ ㇓-200-R	KIV-0.75SQ-W-200-R
17	KIV 0.75SQ ミドリ	KIV-0.75SQ-GN
18	KIV 0.75SQ ミドリ-200-R	KIV-0.75SQ-GN-200-R
19	KIV 1.25SQ ア	KIV-1.25SQ-BE
20	KIV 1.25SQ ア-200-R	KIV-1.25SQ-BE-200-R
21	KIV 1.25SQ ㇏	KIV-1.25SQ-R
22	KIV 1.25SQ ㇏-200-R	KIV-1.25SQ-R-200-R
23	KIV 1.25SQ ㇑	KIV-1.25SQ-Y
24	KIV 1.25SQ ㇑/ミドリ	KIV-1.25SQ-Y/G
25	KIV 1.25SQ ㇑-200-R	KIV-1.25SQ-Y-200-R
26	KIV 1.25SQ ㇒	KIV-1.25SQ-BK
27	KIV 1.25SQ ㇒-200-R	KIV-1.25SQ-BK-200-R
28	KIV 1.25SQ ㇓	KIV-1.25SQ-W
29	KIV 1.25SQ ㇓-200-R	KIV-1.25SQ-W-200-R
30	KIV 1.25SQ ミドリ	KIV-1.25SQ-GN
31	KIV 1.25SQ ミドリ/㇑	KIV-1.25SQ-G/Y
32	KIV 1.25SQ ミドリ-200-R	KIV-1.25SQ-GN-200-R
39	KIV 2.0SQ ア	KIV-2SQ-BE
40	KIV 2.0SQ ㇏	KIV-2SQ-R
41	KIV 2.0SQ ㇑	KIV-2SQ-Y
42	KIV 2.0SQ ㇑/ミドリ	KIV-2SQ-Y/G
43	KIV 2.0SQ ㇒	KIV-2SQ-BK
44	KIV 2.0SQ ㇓	KIV-2SQ-W
45	KIV 2.0SQ ミドリ	KIV-2SQ-GN
46	KIV 2.0SQ ミドリ/㇑	KIV-2SQ-G/Y
47	KIV 3.5SQ ア	KIV-3.5SQ-BE
48	KIV 3.5SQ ㇏	KIV-3.5SQ-R
49	KIV 3.5SQ ㇑	KIV-3.5SQ-Y

50	KIV 3.5SQ ｷ/ﾐﾄﾞﾘ	KIV-3.5SQ-Y/G
51	KIV 3.5SQ ｶ	KIV-3.5SQ-BK
52	KIV 3.5SQ ｼ	KIV-3.5SQ-W
53	KIV 3.5SQ ﾐﾄﾞﾘ	KIV-3.5SQ-GN
54	KIV 3.5SQ ﾐﾄﾞﾘ/ｷ	KIV-3.5SQ-G/Y
55	KIV 5.5SQ ﾏ	KIV-5.5SQ-BE
56	KIV 5.5SQ ﾏｶ	KIV-5.5SQ-R
57	KIV 5.5SQ ｷ	KIV-5.5SQ-Y
58	KIV 5.5SQ ｷ/ﾐﾄﾞﾘ	KIV-5.5SQ-Y/G
59	KIV 5.5SQ ｶ	KIV-5.5SQ-BK
60	KIV 5.5SQ ｼ	KIV-5.5SQ-W
61	KIV 5.5SQ ﾐﾄﾞﾘ	KIV-5.5SQ-GN
62	KIV 5.5SQ ﾐﾄﾞﾘ/ｷ	KIV-5.5SQ-G/Y
63	KIV 8.0SQ ﾏ	KIV-8SQ-BE
64	KIV 8.0SQ ﾏｶ	KIV-8SQ-R
65	KIV 8.0SQ ｷ	KIV-8SQ-Y
66	KIV 8.0SQ ｷ/ﾐﾄﾞﾘ	KIV-8.0SQ-Y/G
67	KIV 8.0SQ ｶ	KIV-8SQ-BK
68	KIV 8.0SQ ｼ	KIV-8SQ-W
69	KIV 8.0SQ ﾐﾄﾞﾘ	KIV-8SQ-GN
70	KIV 8.0SQ ﾐﾄﾞﾘ/ｷ	KIV-8.0SQ-G/Y
33	KIV 14.0SQ ﾏ	KIV-14SQ-BE
34	KIV 14.0SQ ﾏｶ	KIV-14SQ-R
35	KIV 14.0SQ ｷ	KIV-14SQ-Y
36	KIV 14.0SQ ｶ	KIV-14SQ-BK
37	KIV 14.0SQ ｼ	KIV-14SQ-W
38	KIV 14.0SQ ﾐﾄﾞﾘ	KIV-14SQ-GN