

■ 型番置換表

・6月30日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番： NAUL1015-24-Y-100

新型番： UL1015-24AWG-Y-100

	旧販売型番	6/30~販売型番
1	NAUL1015-24-Y	UL1015-24AWG-Y
2	NAUL1015-24-W	UL1015-24AWG-W
3	NAUL1015-24-R	UL1015-24AWG-R
4	NAUL1015-24-O	UL1015-24AWG-O
5	NAUL1015-24-H	UL1015-24AWG-H
6	NAUL1015-24-GY	UL1015-24AWG-GY
7	NAUL1015-24-GN	UL1015-24AWG-GN
8	NAUL1015-24-BN	UL1015-24AWG-BN
9	NAUL1015-24-BK	UL1015-24AWG-BK
10	NAUL1015-24-BE	UL1015-24AWG-BE
11	NAUL1015-22-Y	UL1015-22AWG-Y
12	NAUL1015-22-W	UL1015-22AWG-W
13	NAUL1015-22-R	UL1015-22AWG-R
14	NAUL1015-22-O	UL1015-22AWG-O
15	NAUL1015-22-H	UL1015-22AWG-H
16	NAUL1015-22-GY	UL1015-22AWG-GY
17	NAUL1015-22-GN	UL1015-22AWG-GN
18	NAUL1015-22-BN	UL1015-22AWG-BN
19	NAUL1015-22-BK	UL1015-22AWG-BK
20	NAUL1015-22-BE	UL1015-22AWG-BE
21	NAUL1015-20-Y	UL1015-20AWG-Y
22	NAUL1015-20-W	UL1015-20AWG-W
23	NAUL1015-20-R	UL1015-20AWG-R
24	NAUL1015-20-O	UL1015-20AWG-O
25	NAUL1015-20-H	UL1015-20AWG-H
26	NAUL1015-20-GY	UL1015-20AWG-GY
27	NAUL1015-20-GN	UL1015-20AWG-GN
28	NAUL1015-20-BN	UL1015-20AWG-BN
29	NAUL1015-20-BK	UL1015-20AWG-BK
30	NAUL1015-20-BE	UL1015-20AWG-BE
31	NAUL1015-18-Y	UL1015-18AWG-Y
32	NAUL1015-18-W	UL1015-18AWG-W
33	NAUL1015-18-R	UL1015-18AWG-R
34	NAUL1015-18-O	UL1015-18AWG-O
35	NAUL1015-18-H	UL1015-18AWG-H
36	NAUL1015-18-GY	UL1015-18AWG-GY
37	NAUL1015-18-GN	UL1015-18AWG-GN
38	NAUL1015-18-BN	UL1015-18AWG-BN
39	NAUL1015-18-BK	UL1015-18AWG-BK

40	NAUL1015-18-BE	UL1015-18AWG-BE
41	NAUL1015-16-Y	UL1015-16AWG-Y
42	NAUL1015-16-W	UL1015-16AWG-W
43	NAUL1015-16-R	UL1015-16AWG-R
44	NAUL1015-16-O	UL1015-16AWG-O
45	NAUL1015-16-H	UL1015-16AWG-H
46	NAUL1015-16-GY	UL1015-16AWG-GY
47	NAUL1015-16-GN	UL1015-16AWG-GN
48	NAUL1015-16-BN	UL1015-16AWG-BN
49	NAUL1015-16-BK	UL1015-16AWG-BK
50	NAUL1015-16-BE	UL1015-16AWG-BE
51	NAUL1015-14-Y	UL1015-14AWG-Y
52	NAUL1015-14-W	UL1015-14AWG-W
53	NAUL1015-14-R	UL1015-14AWG-R
54	NAUL1015-14-O	UL1015-14AWG-O
55	NAUL1015-14-H	UL1015-14AWG-H
56	NAUL1015-14-GY	UL1015-14AWG-GY
57	NAUL1015-14-GN	UL1015-14AWG-GN
58	NAUL1015-14-BN	UL1015-14AWG-BN
59	NAUL1015-14-BK	UL1015-14AWG-BK
60	NAUL1015-14-BE	UL1015-14AWG-BE
61	NAUL1015-12-Y	UL1015-12AWG-Y
62	NAUL1015-12-W	UL1015-12AWG-W
63	NAUL1015-12-R	UL1015-12AWG-R
64	NAUL1015-12-O	UL1015-12AWG-O
65	NAUL1015-12-H	UL1015-12AWG-H
66	NAUL1015-12-GY	UL1015-12AWG-GY
67	NAUL1015-12-GN	UL1015-12AWG-GN
68	NAUL1015-12-BN	UL1015-12AWG-BN
69	NAUL1015-12-BK	UL1015-12AWG-BK
70	NAUL1015-12-BE	UL1015-12AWG-BE
71	NAUL1015-10-Y	UL1015-10AWG-Y
72	NAUL1015-10-W	UL1015-10AWG-W
73	NAUL1015-10-R	UL1015-10AWG-R
74	NAUL1015-10-O	UL1015-10AWG-O
75	NAUL1015-10-H	UL1015-10AWG-H
76	NAUL1015-10-GY	UL1015-10AWG-GY
77	NAUL1015-10-GN	UL1015-10AWG-GN
78	NAUL1015-10-BN	UL1015-10AWG-BN
79	NAUL1015-10-BK	UL1015-10AWG-BK
80	NAUL1015-10-BE	UL1015-10AWG-BE