

■ 型番置換表

・6月30日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番： UL1284-4-0-BK-100

新型番： UL1284-4/0-BK-100

	旧販売型番	6/30~販売型番
1	UL1284-4-0-BK	UL1284-4/0-BK
2	UL1284-3-0-BK	UL1284-3/0-BK
3	UL1284-2-0-BK	UL1284-2/0-BK
4	UL1284-1-BK	UL1284-1AWG-BK
5	UL1284-1-0-BK	UL1284-1/0-BK
6	UL1283-8-W	UL1283-8AWG-W
7	UL1283-8-R	UL1283-8AWG-R
8	UL1283-8-GY	UL1283-8AWG-GY
9	UL1283-8-G	UL1283-8AWG-G
10	UL1283-8-BK	UL1283-8AWG-BK
11	UL1283-8-BE	UL1283-8AWG-BE
12	UL1283-6-W	UL1283-6AWG-W
13	UL1283-6-R	UL1283-6AWG-R
14	UL1283-6-GY	UL1283-6AWG-GY
15	UL1283-6-G	UL1283-6AWG-G
16	UL1283-6-BK	UL1283-6AWG-BK
17	UL1283-6-BE	UL1283-6AWG-BE
18	UL1283-4-W	UL1283-4AWG-W
19	UL1283-4-R	UL1283-4AWG-R
20	UL1283-4-GY	UL1283-4AWG-GY
21	UL1283-4-G	UL1283-4AWG-G
22	UL1283-4-BK	UL1283-4AWG-BK
23	UL1283-4-BE	UL1283-4AWG-BE
24	UL1283-2-W	UL1283-2AWG-W
25	UL1283-2-R	UL1283-2AWG-R
26	UL1283-2-GY	UL1283-2AWG-GY
27	UL1283-2-G	UL1283-2AWG-G
28	UL1283-2-BK	UL1283-2AWG-BK
29	UL1283-2-BE	UL1283-2AWG-BE
30	UL1015-24-YG	UL1015-24AWG-YG
31	UL1015-24-Y	UL1015-24AWG-Y
32	UL1015-24-W	UL1015-24AWG-W
33	UL1015-24-R	UL1015-24AWG-R
34	UL1015-24-O	UL1015-24AWG-O
35	UL1015-24-GN	UL1015-24AWG-GN
36	UL1015-24-BN	UL1015-24AWG-BN
37	UL1015-24-BK	UL1015-24AWG-BK
38	UL1015-24-BE	UL1015-24AWG-BE
39	UL1015-22-YG	UL1015-22AWG-YG

40	UL1015-22-Y	UL1015-22AWG-Y
41	UL1015-22-W	UL1015-22AWG-W
42	UL1015-22-R	UL1015-22AWG-R
43	UL1015-22-O	UL1015-22AWG-O
44	UL1015-22-GN	UL1015-22AWG-GN
45	UL1015-22-BN	UL1015-22AWG-BN
46	UL1015-22-BK	UL1015-22AWG-BK
47	UL1015-22-BE	UL1015-22AWG-BE
48	UL1015-20-YG	UL1015-20AWG-YG
49	UL1015-20-Y	UL1015-20AWG-Y
50	UL1015-20-W	UL1015-20AWG-W
51	UL1015-20-R	UL1015-20AWG-R
52	UL1015-20-O	UL1015-20AWG-O
53	UL1015-20-GN	UL1015-20AWG-GN
54	UL1015-20-BN	UL1015-20AWG-BN
55	UL1015-20-BK	UL1015-20AWG-BK
56	UL1015-20-BE	UL1015-20AWG-BE
57	UL1015-18-YG	UL1015-18AWG-YG
58	UL1015-18-Y	UL1015-18AWG-Y
59	UL1015-18-W	UL1015-18AWG-W
60	UL1015-18-R	UL1015-18AWG-R
61	UL1015-18-O	UL1015-18AWG-O
62	UL1015-18-GN	UL1015-18AWG-GN
63	UL1015-18-BN	UL1015-18AWG-BN
64	UL1015-18-BK	UL1015-18AWG-BK
65	UL1015-18-BE	UL1015-18AWG-BE
66	UL1015-16-YG	UL1015-16AWG-YG
67	UL1015-16-Y	UL1015-16AWG-Y
68	UL1015-16-W	UL1015-16AWG-W
69	UL1015-16-R	UL1015-16AWG-R
70	UL1015-16-O	UL1015-16AWG-O
71	UL1015-16-GN	UL1015-16AWG-GN
72	UL1015-16-BN	UL1015-16AWG-BN
73	UL1015-16-BK	UL1015-16AWG-BK
74	UL1015-16-BE	UL1015-16AWG-BE
75	UL1015-14-YG	UL1015-14AWG-YG
76	UL1015-14-Y	UL1015-14AWG-Y
77	UL1015-14-W	UL1015-14AWG-W
78	UL1015-14-R	UL1015-14AWG-R
79	UL1015-14-O	UL1015-14AWG-O
80	UL1015-14-GN	UL1015-14AWG-GN
81	UL1015-14-BN	UL1015-14AWG-BN
82	UL1015-14-BK	UL1015-14AWG-BK
83	UL1015-14-BE	UL1015-14AWG-BE
84	UL1015-12-YG	UL1015-12AWG-YG
85	UL1015-12-Y	UL1015-12AWG-Y
86	UL1015-12-W	UL1015-12AWG-W

87	UL1015-12-R	UL1015-12AWG-R
88	UL1015-12-O	UL1015-12AWG-O
89	UL1015-12-GN	UL1015-12AWG-GN
90	UL1015-12-BN	UL1015-12AWG-BN
91	UL1015-12-BK	UL1015-12AWG-BK
92	UL1015-12-BE	UL1015-12AWG-BE
93	UL1015-10-YG	UL1015-10AWG-YG
94	UL1015-10-Y	UL1015-10AWG-Y
95	UL1015-10-W	UL1015-10AWG-W
96	UL1015-10-R	UL1015-10AWG-R
97	UL1015-10-O	UL1015-10AWG-O
98	UL1015-10-GN	UL1015-10AWG-GN
99	UL1015-10-BN	UL1015-10AWG-BN
100	UL1015-10-BK	UL1015-10AWG-BK
101	UL1015-10-BE	UL1015-10AWG-BE