

■ 型番置換表

・2023年5月31日より新たな型式にて販売を致します。商品仕様に関する変更はございません。

・以下型番には末尾に長さが入ります。

例) 100m購入希望の場合

旧型番： UL1007-28-YG-100

新型番： UL1007-28AWG-YG-100

	旧販売型番	5/31~販売型番
1	UL1007-28-YG	UL1007-28AWG-YG
2	UL1007-28-Y	UL1007-28AWG-Y
3	UL1007-28-W	UL1007-28AWG-W
4	UL1007-28-R	UL1007-28AWG-R
5	UL1007-28-PL	UL1007-28AWG-PL
6	UL1007-28-O	UL1007-28AWG-O
7	UL1007-28-H	UL1007-28AWG-H
8	UL1007-28-GN	UL1007-28AWG-GN
9	UL1007-28-BN	UL1007-28AWG-BN
10	UL1007-28-BK	UL1007-28AWG-BK
11	UL1007-28-BE	UL1007-28AWG-BE
12	UL1007-26-Y	UL1007-26AWG-Y
13	UL1007-26-W	UL1007-26AWG-W
14	UL1007-26-R	UL1007-26AWG-R
15	UL1007-26-PL	UL1007-26AWG-PL
16	UL1007-26-O	UL1007-26AWG-O
17	UL1007-26-H	UL1007-26AWG-H
18	UL1007-26-GN	UL1007-26AWG-GN
19	UL1007-26-BN	UL1007-26AWG-BN
20	UL1007-26-BK	UL1007-26AWG-BK
21	UL1007-26-BE	UL1007-26AWG-BE
22	UL1007-24-YG	UL1007-24AWG-YG
23	UL1007-24-Y	UL1007-24AWG-Y
24	UL1007-24-W	UL1007-24AWG-W
25	UL1007-24-R	UL1007-24AWG-R
26	UL1007-24-PL	UL1007-24AWG-PL
27	UL1007-24-O	UL1007-24AWG-O
28	UL1007-24-H	UL1007-24AWG-H
29	UL1007-24-GN	UL1007-24AWG-GN
30	UL1007-24-BN	UL1007-24AWG-BN
31	UL1007-24-BK	UL1007-24AWG-BK
32	UL1007-24-BE	UL1007-24AWG-BE
33	UL1007-22-YG	UL1007-22AWG-YG
34	UL1007-22-Y	UL1007-22AWG-Y
35	UL1007-22-W	UL1007-22AWG-W
36	UL1007-22-R	UL1007-22AWG-R
37	UL1007-22-PL	UL1007-22AWG-PL
38	UL1007-22-O	UL1007-22AWG-O
39	UL1007-22-H	UL1007-22AWG-H

40	UL1007-22-GN	UL1007-22AWG-GN
41	UL1007-22-BN	UL1007-22AWG-BN
42	UL1007-22-BK	UL1007-22AWG-BK
43	UL1007-22-BE	UL1007-22AWG-BE
44	UL1007-20-YG	UL1007-20AWG-YG
45	UL1007-20-Y	UL1007-20AWG-Y
46	UL1007-20-W	UL1007-20AWG-W
47	UL1007-20-R	UL1007-20AWG-R
48	UL1007-20-PL	UL1007-20AWG-PL
49	UL1007-20-O	UL1007-20AWG-O
50	UL1007-20-H	UL1007-20AWG-H
51	UL1007-20-GN	UL1007-20AWG-GN
52	UL1007-20-BN	UL1007-20AWG-BN
53	UL1007-20-BK	UL1007-20AWG-BK
54	UL1007-20-BE	UL1007-20AWG-BE
55	UL1007-18-YG	UL1007-18AWG-YG
56	UL1007-18-Y	UL1007-18AWG-Y
57	UL1007-18-W	UL1007-18AWG-W
58	UL1007-18-R	UL1007-18AWG-R
59	UL1007-18-PL	UL1007-18AWG-PL
60	UL1007-18-O	UL1007-18AWG-O
61	UL1007-18-H	UL1007-18AWG-H
62	UL1007-18-GN	UL1007-18AWG-GN
63	UL1007-18-BN	UL1007-18AWG-BN
64	UL1007-18-BK	UL1007-18AWG-BK
65	UL1007-18-BE	UL1007-18AWG-BE
66	UL1007-16-YG	UL1007-16AWG-YG
67	UL1007-16-Y	UL1007-16AWG-Y
68	UL1007-16-W	UL1007-16AWG-W
69	UL1007-16-R	UL1007-16AWG-R
70	UL1007-16-PL	UL1007-16AWG-PL
71	UL1007-16-O	UL1007-16AWG-O
72	UL1007-16-H	UL1007-16AWG-H
73	UL1007-16-GN	UL1007-16AWG-GN
74	UL1007-16-BN	UL1007-16AWG-BN
75	UL1007-16-BK	UL1007-16AWG-BK
76	UL1007-16-BE	UL1007-16AWG-BE