

六角スペーサ/(メス/メス)



結束部品

マーカー・スペーサ・ネジ

結束部品

マーカー・スペーサ・ネジ



ココが特長 非貫通タイプの六角スペーサ



1個から注文OK!

出荷日

○のついたサイズ(在庫品)

1~20個 翌日(当日)

21個~ 都度見積

当日出荷は、17時までに都度お申し付けください。

○印のみ
在庫品

出荷日(非在庫品)

1~20個 3日目出荷

21個~ 都度見積

その他
非在庫品



型式	L
SB-S2.6	5

■材質: ステンレス (RoHS) (単位: mm)

型式	L	M	在庫	H	M 深さ	重量 (g)					
SB-S2	5	M2	○	4	全ネジ	0.4					
	6					0.5					
	7					0.6					
	8					0.7					
	9					0.8					
	10					0.8					
	11					0.9					
	12					1.0					
	13					1.1					
	14					1.2					
	15					1.3					
	16					1.4					
17	1.5										
18	1.6										
19	1.7										
20	1.8										
SB-S2.6	5	M2.6	○	5	全ネジ	0.6					
	6					0.8					
	7					0.9					
	8					1.0					
	9					1.2					
	10					1.3					
	12					1.6					
	13					1.8					
	14					2.0					
	15					2.0					
	16					0.8					
	17					1.2					
18	1.5										
19	1.8										
20	2.3										
25	3.2										
30	4.1										
35	5.2										
40	5.2										
50	9.2										
SB-S3	8	M3	○	5.5	全ネジ	1.9					
	10					2.4					
	12					2.9					
	15					3.6					
	20					4.9					
	25					6.1					
	30					8.0					
	35					9.7					
	40					11.4					
	50					14.6					
	SB-S4					8	M4	○	7	全ネジ	2.3
						10					2.9
15		4.5									
20		5.9									
25		7.4									
30		9.3									
35		11.4									
40		13.6									
50		17.9									
60		22.2									
SB-S5		8	M5	○	8	全ネジ					2.3
		10									2.9
	15	4.5									
	20	5.9									
	25	7.4									
	30	9.3									
	35	11.4									
	40	13.6									
	50	17.9									
	60	22.2									

■材質: ジュラコン(POM) (RoHS) (単位: mm)

型式	L	M	在庫	H	M 深さ	重量 (g)
SB-J2	3	M2	○	4	全ネジ (貫通)	0.1
	4					0.1
	5					0.1
	6					0.1
	7					0.1
	8					0.1
	9					0.1
	10					0.2
	11					0.2
	12					0.2
	13					0.2
	14					0.2
15	0.2					
16	0.3					
17	0.3					
18	0.3					
19	0.3					
20	0.3					
25	0.4					
30	0.4					
SB-J2.6	3	M2.6	○	5	全ネジ	0.1
	4					0.1
	5					0.1
	6					0.1
	7					0.2
	8					0.2
	9					0.2
	10					0.2
	11					0.3
	12					0.3
	13					0.3
	14					0.3
15	0.4					
16	0.4					
17	0.4					
18	0.4					
19	0.5					
20	0.5					
25	0.6					
30	0.7					
SB-J3	4	M3	○	5.5	全ネジ	0.1
	5					0.1
	6					0.2
	7					0.2
	8					0.2
	9					0.2
	10					0.3
	11					0.3
	12					0.3
	13					0.3
	14					0.4
	15					0.4
16	0.4					
17	0.5					
18	0.5					
19	0.5					
20	0.5					
23	0.8					
25	0.7					
30	0.8					
40	0.8					
50	1.0					
60	1.3					
SB-J4	5	M4	○	7	全ネジ	0.2
	8					0.3
	10					0.4
	12					0.5
	13					0.6
	15					0.8
	17					0.7
	18					0.8
	20					0.9
	23					1.0
	25					1.1
	28					1.2
30	1.2					
35	1.5					
40	1.7					
50	2.2					
60	2.6					

■材質: 快削黄銅 (RoHS) (単位: mm)

型式	L	M	在庫	H	M 深さ	重量 (g)
SB-O2	3	M2	○	4	全ネジ	0.3
	4					0.4
	5					0.5
	6					0.6
	7					0.7
	8					0.8
	9					0.9
	10					1.0
	11					1.1
	12					1.2
	13					1.2
	14					1.3
15	1.4					
16	1.5					
17	1.6					
18	1.7					
19	1.8					
20	1.8					
25	2.4					
30	3.0					
SB-O2.6	3	M2.6	○	5	全ネジ	0.4
	4					0.6
	5					0.7
	6					0.8
	7					1.0
	8					1.1
	9					1.3
	10					1.4
	11					1.6
	12					1.7
	13					1.9
	14					1.9
15	2.1					
18	2.6					
20	2.9					
25	3.1					
30	3.3					
40	3.9					
50	4.2					
60	4.8					
SB-O3	3	M3	○	5.5	全ネジ	0.5
	4					0.7
	5					0.8
	6					1.0
	7					1.2
	8					1.5
	9					1.7
	10					1.8
	11					2.0
	12					2.0
	13					2.1
	14					2.3
15	2.5					
16	2.7					
17	2.8					
18	3.0					
19	3.1					
20	3.3					
23	3.9					
25	4.2					
30	4.8					
40	5.6					
50	6.7					
60	7.7					
SB-O4	6	M4	○	7	全ネジ	1.5
	8					2.1
	10					2.6
	12					3.1
	13					3.4
	14					3.6
	15					3.9
	16					4.1
	18					4.7
	20					5.2
	23					6.0
	25					6.6
28	7.4					
30	8.7					
35	10.5					
40	12.8					
45	14.1					
50	15.7					
60	19.4					
SB-O5	10	M5	○	8	全ネジ	3.1
	15					4.7
	20					6.4
	25					7.9
	30					9.8
	40					14.5
	50					19.2
	60					23.9



型式	SB-S			SB-J			SB-O		
	パラチャージ	基準単価	スライド単価	パラチャージ	基準単価	スライド単価	パラチャージ	基準単価	スライド単価
Mネジサイズ	1~9個	10~49個	50~99個	1~9個	10~49個	50~99個	1~9個	10~49個	50~99個
2	+¥90/個	¥180	¥150	+¥90/個	¥110	¥75	+¥90/個	¥110	¥75
2.6		¥130	¥100		¥100	¥60		¥120	¥80
3	+¥90/個	¥150	¥120	+¥90/個	¥110	¥75	+¥90/個	¥120	¥80
4		¥220	¥190		¥140	¥85		¥130	¥80
5	+¥90/個	¥290	¥240	+¥90/個	—	—	+¥90/個	¥150	¥85
6		—	—		—	—		—	—

■部 1~9個のご注文は基準単価+パラチャージを申し受けます。

【計算例】 SB-S-2-5 を2個ご注文の場合
(基準単価 180円+パラチャージ90円)×2個=540円

パラチャージに関しては [0101ページ](#)

¥*** 新価格 適用開始時期に関しては [0101ページ](#)

2012.9

2013.8