

P.11517<価格>

赤枠内 価格を変更

■T5タイプ (センターベアリングタイプ)

Catalog No.			P.D.	O.D.	F	E	A	W	S	ベアリング寸法				使用 止め輪	¥単価 1~4コ		
Type	歯数	対応ベルト								No.	d	D	B		AHTF	KHTF	NHTF
AHTF KHTF NHTF	18	T5100	28.65	27.80	33	22	11	16	5	698ZZ×1	8	19	6	RTWS19	2,880	3,160	3,450
	20	T5100	31.83	31.00	36	24	11	16	5	698ZZ×1	8	19	6	RTWS19	2,850	3,470	3,790
		T5150					17	22	5						698ZZ×2	3,170	3,870
	22	T5100	35.01	34.25	40	27	11	16	5	6900ZZ×1	10	22	6	RTWS22	3,360	3,690	4,030
	24	T5100	38.20	37.40	45	30	11	16	4	6000ZZ×1	10	26	8	RTWS26	3,580	3,930	4,290
	25	T5100	39.79	39.00	45	30	11	16	4	6000ZZ×1	10	26	8	RTWS26	3,720	4,090	4,460
	28	T5100	44.56	43.75	48	35	11	16	3.5	6200ZZ×1	10	30	9	RTWS30	3,610	4,410	4,810
		T5150					17	22	6.5						3,710	4,530	4,940
	30	T5100	47.75	46.95	52	36	11	16	3	6201ZZ×1	12	32	10	RTWS32	3,820	4,660	5,080
		T5150					17	22	6						4,850	5,910	6,450