



追加加工価格も数量スライド適用 P.49

RoHS

$C \leq 0.3$
 $H = 0.3$
 $2-R \leq 0.5$
 $(D \leq 2 \dots R \leq 0.3)$
 $D = 0.02$
 $T = 4 - 0.02$
 $N = 5$
 $L = 0.02$
 $(L > 200 \dots L + 0.05)$
 $S = 0.02$
 $P = 0$
 $P = -0.005$
 $P = -0.01$
 $P = -0.02$

EP SHS **EP SHSE**
 $P = 0$ $P = -0.01$
 $P = -0.005$ $P = -0.02$

※保持径(D)精度保証範囲(詳細 P.1475)
 ※つなぎR(詳細 P.1476)
 □ 材質 SKH51
 □ 硬度 58~60HRC
 母材硬度保証範囲(詳細 P.1477)
 EP SHS, EP SHSEは総焼入れ品

型式	ツバ厚	P公差
EP SHS	4mm(T4)	0 -0.005
EP SHSE		-0.01 -0.02

H	型式		指定0.01mm単位		指定1mm単位	指定0.01mm単位
	Type	D	L	P	N	S
3	EP SHS ($P = 0$)	1.5	35.00~200.00	0.80~1.40	$N \geq 15$ and $20 \leq (L-N) \leq 150$	5.00~40.00
4		2		0.80~1.90		
5		2.5		0.80~2.40		
6	EP SHSE ($P = -0.01$)	3	35.00~250.00	1.00~2.90	$N \geq 15$ and $20 \leq (L-N) \leq 185$	5.00~50.00
7		3.5		1.50~3.40		
8		4		2.50~4.40		
8	4.5	3.00~4.90				
9	5.5	3.50~5.40				
9	6	4.00~5.90				

Order 注文例 型式 - L - P - N - S
 EP SHS 5 - 60.00 - P4.62 - N30 - S10.00

Delivery 出荷日 3 日目発送

Alterations 追加加工 型式 - L - P - N - S - (HC・TC・DC...etc.)
 EP SHS 5 - 60.00 - P4.62 - N30 - S10.00 - TC3.0

追加加工詳細 P.186

Alterations	Code	Spec.	¥/1Code	Alterations	Code	Spec.	¥/1Code
	KC	KC=指定0.1mm単位 ① $D/2+0.1 \leq KC < H/2$	120		KGC	KGC=指定0.1mm単位 AG=指定1°単位 ① $D/2+0.1 \leq KGC < H/2$, $0 < AG < 360$	360
	WKC	WKC=指定0.1mm単位 ① $D/2+0.1 \leq WKC < H/2$	240		KTC	KTC=指定0.1mm単位 ① $D/2+0.1 \leq KTC < H/2$	480
	KAC KBC	KAC, KBC=指定0.1mm単位 ① $D/2+0.1 \leq KAC < KBC < H/2$	360		HC	HC=指定0.1mm単位 ① $D+1 \leq HC < H$	200
	RKC	RKC=指定0.1mm単位 ① $D/2+0.1 \leq RKC < H/2$	240		TC	TC=指定0.1mm単位 ① $2.0 \leq TC \leq 10$ and $TC \leq N-10$ (L, N, S寸法は指定寸法通り)	500
	DKC	DKC=指定0.1mm単位 ① $D/2+0.1 \leq DKC < H/2$	360		DC	DC=指定0.1mm単位 ① $D-2 \leq DC < D$ and $DC \geq 1.5$ ② 変更はS寸法側のDサイズのみです。	200
	SKC	SKC=指定0.1mm単位 ① $D/2+0.1 \leq SKC < H/2$	480				

Price 価格 数量スライド価格 (①1円未満切り捨て) P.47

数量	1~4	5~12	13~49	50~100	表示数量超えは
値引率	基準単価	5%	10%	20%	価格・出荷日お見積り

型式	Type	D	L	¥基準単価 1~4本					
				L35.00~50.00	L50.01~100.00	L100.01~150.00	L150.01~200.00	L200.01~250.00	
EP SHS	EP SHS	1.5		1,510	1,600	1,690	1,780	-	
		2		1,510	1,600	1,690	1,780		
		2.5		1,750	1,840	1,930	2,020		
		3		1,920	2,010	2,100	2,190		2,380
		3.5		2,080	2,170	2,260	2,350		2,540
		4		2,410	2,490	2,590	2,670		2,860
EP SHSE	EP SHSE	4.5		2,410	2,490	2,590	2,670	2,860	
		5		2,690	2,780	2,870	2,960	3,150	
		5.5		2,690	2,780	2,870	2,960	3,150	

