

HSS MACHINE REAMER

ハイス鋼マシンリーマ

● 右刃ストレート刃 0.1mm単位指定タイプ

刃径D	公差	刃径D	MT No.
3	+0.007 +0.002	3 ~ 14	1
3.1 ~ 6	+0.009 +0.004	14.1 ~ 23	2
6.1 ~ 10	+0.012 +0.006	23.1 ~ 30	3
10.1 ~ 18	+0.015 +0.007		
18.1 ~ 30	+0.017 +0.008		

材質

型番 MRST

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本	刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本	刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本
3	0.5	35	110	6	5,330	9.8	1	70	160	6	5,330	16.6	1.5	100	220	8	7,880
3.1	0.5	35	110	6	5,860	9.9	1	70	160	6	5,330	16.7	1.5	100	220	8	7,880
3.2	0.5	35	110	6	5,860	10	1	70	160	6	4,810	16.8	1.5	100	220	8	7,880
3.3	0.5	35	110	6	5,860	10.1	1	70	160	6	5,700	16.9	1.5	100	220	8	7,880
3.4	0.5	35	110	6	5,860	10.2	1	70	160	6	5,700	17	1.5	100	220	8	7,130
3.5	0.5	35	110	6	5,330	10.3	1	70	160	6	5,700	17.1	1.5	105	225	8	8,400
3.6	0.5	35	110	6	5,700	10.4	1	70	160	6	5,700	17.2	1.5	105	225	8	8,400
3.7	0.5	35	110	6	5,700	10.5	1	70	160	6	5,190	17.3	1.5	105	225	8	8,400
3.8	0.5	35	110	6	5,700	10.6	1	75	170	6	5,700	17.4	1.5	105	225	8	8,400
3.9	0.5	35	110	6	5,700	10.7	1	75	170	6	5,700	17.5	1.5	105	225	8	7,430
4	0.5	35	110	6	4,810	10.8	1	75	170	6	5,700	17.6	1.5	105	225	8	9,390
4.1	0.5	45	120	6	5,330	10.9	1	75	170	6	5,700	17.7	1.5	105	225	8	9,390
4.2	0.5	45	120	6	5,330	11	1	75	170	6	5,190	17.8	1.5	105	225	8	9,390
4.3	0.5	45	120	6	5,330	11.1	1	75	170	6	5,700	17.9	1.5	105	225	8	9,390
4.4	0.5	45	120	6	5,330	11.2	1	75	170	6	5,700	18	1.5	105	225	8	7,430
4.5	0.5	45	120	6	4,440	11.3	1	75	170	6	5,700	18.1	1.5	105	225	8	9,390
4.6	1	45	120	6	5,330	11.4	1	75	170	6	5,700	18.2	1.5	105	225	8	9,390
4.7	1	45	120	6	5,330	11.5	1	75	170	6	5,190	18.3	1.5	105	225	8	9,390
4.8	1	45	120	6	5,330	11.6	1	75	170	6	5,700	18.4	1.5	105	225	8	9,390
4.9	1	45	120	6	5,330	11.7	1	75	170	6	5,700	18.5	1.5	105	225	8	9,490
5	1	45	120	6	4,440	11.8	1	75	170	6	5,700	18.6	1.5	105	225	8	9,390
5.1	1	45	120	6	4,880	11.9	1	75	170	6	5,700	18.7	1.5	105	225	8	9,390
5.2	1	45	120	6	4,880	12	1	75	170	6	5,190	18.8	1.5	105	225	8	9,390
5.3	1	45	120	6	4,880	12.1	1	80	180	6	5,860	18.9	1.5	105	225	8	9,390
5.4	1	45	120	6	4,880	12.2	1	80	180	6	5,860	19	1.5	105	225	8	7,730
5.5	1	45	120	6	4,440	12.3	1	80	180	6	5,860	19.1	1.5	110	230	8	9,450
5.6	1	50	130	6	4,730	12.4	1	80	180	6	5,860	19.2	1.5	110	230	8	9,450
5.7	1	50	130	6	4,730	12.5	1	80	180	6	5,330	19.3	1.5	110	230	8	9,450
5.8	1	50	130	6	4,730	12.6	1	80	180	6	5,860	19.4	1.5	110	230	8	9,450
5.9	1	50	130	6	4,730	12.7	1	80	180	6	5,860	19.5	1.5	110	230	8	9,450
6	1	50	130	6	4,270	12.8	1	80	180	6	5,860	19.6	1.5	110	230	8	9,450
6.1	1	50	130	6	4,880	12.9	1	80	180	6	5,860	19.7	1.5	110	230	8	9,450
6.2	1	50	130	6	4,880	13	1	80	180	6	5,330	19.8	1.5	110	230	8	9,450
6.3	1	50	130	6	4,880	13.1	1	85	190	6	5,860	19.9	1.5	110	230	8	9,450
6.4	1	50	130	6	4,880	13.2	1	85	190	6	5,860	20	1.5	110	230	8	9,490
6.5	1	50	130	6	4,440	13.3	1	85	190	6	5,860	20.1	1.5	120	240	8	10,370
6.6	1	55	140	6	4,880	13.4	1	85	190	6	5,860	20.2	1.5	120	240	8	10,370
6.7	1	55	140	6	4,880	13.5	1	85	190	6	5,330	20.3	1.5	120	240	8	10,370
6.8	1	55	140	6	4,880	13.6	1	85	190	6	5,860	20.4	1.5	120	240	8	10,370
6.9	1	55	140	6	4,880	13.7	1	85	190	6	5,860	20.5	1.5	120	240	8	9,390
7	1	55	140	6	4,440	13.8	1	85	190	6	5,860	20.6	1.5	120	240	8	10,370
7.1	1	55	140	6	5,110	13.9	1	85	190	6	5,860	20.7	1.5	120	240	8	10,370
7.2	1	55	140	6	5,110	14	1	85	190	6	4,830	20.8	1.5	120	240	8	10,370
7.3	1	55	140	6	5,110	14.1	1.5	90	210	8	6,310	20.9	1.5	120	240	8	10,370
7.4	1	55	140	6	5,110	14.2	1.5	90	210	8	6,310	21	1.5	120	240	8	9,160
7.5	1	55	140	6	4,650	14.3	1.5	90	210	8	6,310	21.1	1.5	120	240	8	10,580
7.6	1	60	150	6	5,110	14.4	1.5	90	210	8	6,310	21.2	1.5	120	240	8	10,580
7.7	1	60	150	6	5,110	14.5	1.5	90	210	8	5,700	21.3	1.5	120	240	8	10,580
7.8	1	60	150	6	5,110	14.6	1.5	90	210	8	6,310	21.4	1.5	120	240	8	10,580
7.9	1	60	150	6	5,110	14.7	1.5	90	210	8	6,310	21.5	1.5	120	240	8	9,610
8	1	60	150	6	4,650	14.8	1.5	90	210	8	6,310	21.6	1.5	120	240	8	10,580
8.1	1	60	150	6	5,330	14.9	1.5	90	210	8	6,310	21.7	1.5	120	240	8	10,580
8.2	1	60	150	6	5,330	15	1.5	90	210	8	5,300	21.8	1.5	120	240	8	10,580
8.3	1	60	150	6	5,330	15.1	1.5	95	215	8	6,620	21.9	1.5	120	240	8	10,580
8.4	1	60	150	6	5,330	15.2	1.5	95	215	8	6,620	22	1.5	120	240	8	7,970
8.5	1	60	150	6	4,810	15.3	1.5	95	215	8	6,620	22.1	1.5	130	250	8	12,150
8.6	1	70	160	6	5,330	15.4	1.5	95	215	8	6,620	22.2	1.5	130	250	8	12,150
8.7	1	70	160	6	5,330	15.5	1.5	95	215	8	6,010	22.3	1.5	130	250	8	12,150
8.8	1	70	160	6	5,330	15.6	1.5	95	215	8	6,620	22.4	1.5	130	250	8	12,150
8.9	1	70	160	6	5,330	15.7	1.5	95	215	8	6,620	22.5	1.5	130	250	8	11,030
9	1	70	160	6	4,810	15.8	1.5	95	215	8	6,620	22.6	1.5	130	250	8	12,150
9.1	1	70	160	6	5,330	15.9	1.5	95	215	8	6,620	22.7	1.5	130	250	8	12,150
9.2	1	70	160	6	5,330	16	1.5	95	215	8	6,010	22.8	1.5	130	250	8	12,150
9.3	1	70	160	6	5,330	16.1	1.5	100	220	8	7,880	22.9	1.5	130	250	8	12,150
9.4	1	70	160	6	5,330	16.2	1.5	100	220	8	7,880	23	1.5	130	250	8	10,060
9.5	1	70	160	6	4,810	16.3	1.5	100	220	8	7,880	23.1	1.5	130	270	8	13,580
9.6	1	70	160	6	5,330	16.4	1.5	100	220	8	7,880	23.2	1.5	130	270	8	13,580
9.7	1	70	160	6	5,330	16.5	1.5	100	220	8	7,130	23.3	1.5	130	270	8	13,580

Order 注文例

MRST - 10.1
型番 刃径(D)

Delivery 出荷日

3 日目発送

Price 価格

■数量スライド価格(①1円未満切捨て)
数量 1~4 5~9 10~49 50~99 100~
値引率 価格表 5% 10% 15%

お見積り

● 右刃ストレート刃 0.01mm単位指定タイプ

刃径D	公差	刃径D	MT No.
2.95~30.09	+0.005 0	2.95~14.09	1
		14.95~23.09	2
		23.95~30.09	3

材質

型番 MRST

刃径 D 0.01mm単位指定	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本	刃径 D 0.01mm単位指定	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本
2.95 ~ 2.99	0.5	35	110	6	6,990	16.95 ~ 16.99	1.5	100	220	8	9,310
3.01 ~ 3.09	0.5	35	110	6	6,990	17.01 ~ 17.09	1.5	100	220	8	9,680
3.95 ~ 3.99	0.5	35	110	6	6,680	17.95 ~ 17.99	1.5	105	225	8	9,680
4.01 ~ 4.09	0.5	35	110	6	6,680	18.01 ~ 18.09	1.5	105	225	8	11,030
4.95 ~ 4.99	1	45	120	6	6,240						