

P. 1 -798 <規格表>

D2=1.9 D3=2.9

■L寸指定タイプ(0.1mm単位)

型式 Type	D	L 指定0.1mm単位	M 許容差	N	u (n)	d 許容差	T	H	付属止め輪 形状 JIS呼び*	¥基準単価								
										HCCG	HCCGH	PHCCG	PHCCGH	GHCCG	SHCCG	SHCCGH	GSHCCG	
HCCG HCCGH PHCCG PHCCGH GHCCG SHCCG SHCCGH GSHCCGH	2	5.0~30.0	0.5	+0.05 0	1.9	1.5	+0.06 0	4.5	E型	No. 1.5	480	600	600	760	1,200	690	890	1,780
	3	5.0~50.0			2.9	2		5.5		No. 2	480	600	600	760	1,200	690	890	1,780
	4	10.0~60.0	0.7	+0.1 0	3.9	1.5	+0.075 0	6.5		No. 3	500	640	630	800	1,260	730	940	1,880
	5				4.9			8		No. 4	570	720	720	910	1,440	830	1,060	2,120
	6	10.0~100.0	0.9	+0.1 0	5.8	2	+0.09 0 -0.09	9		No. 5	590	760	750	950	1,500	870	1,100	2,220
	8				7.8			12		No. 7	620	790	790	1,000	1,580	920	1,180	2,360
	10	15.0~100.0	1.15	+0.14 0	9.8	1.5 以下	+0.11 0	14		No.10	660	830	830	1,050	1,660	960	1,230	2,460
	12	15.0~200.0			11.8			17		No.12	740	940	970	1,230	1,940	1,150	1,470	2,940
	13	20.0~200.0	1.35	+0.14 0	12.8	3	+0.11 0	18		No.13	760	960	990	1,250	1,980	1,170	1,490	2,980
	14				13.8			19		No.14	810	1,030	1,030	1,310	2,060	1,200	1,540	3,080
	15	20.0~200.0	1.35	+0.14 0	14.8	4	+0.11 0	20		No.15	850	1,080	1,070	1,360	2,140	1,230	1,580	3,160
	16				14.3			21		No.16	860	1,100	1,100	1,400	2,200	1,280	1,640	3,280
	17	20.0~200.0	1.35	+0.14 0	15.8	C型	+0.11 0	22		No.17	880	1,130	1,130	1,440	2,260	1,310	1,690	3,380
	18				16.8			23		No.18	910	1,160	1,160	1,480	2,320	1,350	1,740	3,480
	20	20.0~200.0	1.35	+0.14 0	17.8	4	+0.11 0	26		No.20	920	1,180	1,180	1,510	2,360	1,380	1,780	3,560
	22				19.8			27		No.22	960	1,220	1,220	1,560	2,440	1,420	1,840	3,680
	25	21.8	31	No.25	1,000	1,250	1,260	1,610		2,520	1,460	1,900	3,800					

\*詳細はP2009をご参照ください。 SHCCGH・GSHCCGHは焼入により変色する場合があります。

<訂正用>

1.9
2.9

2021