

P.2-1143<規格表>

オス・メスタイプとメス・メスタイプの、上から1番目と4番目のdを4.2に訂正。

型式 Type	ネジ形状①	No.	T(PT) G(PF) N(NPT)	ネジ形状②	No.	T(PT) G(PF) N(NPT)	L		B	(C)	d	¥基準単価							
							固定	指定1mm単位				L寸固定タイプ			L寸指定タイプ				
												APMTF	APMTS	APMTY	APMTFL	APMTSL	APMTYL		
L寸固定タイプ APMTF APMST APMTY	T G N (PTネジ) (PFネジ) (NPTネジ)	1	1/8	—	M5	—	15	16~30	13	14.4	4.2	850	960	700	1,020	1,150	840		
							1	1/8	15	16~30	13	14.4	4.5	850	960	700	1,020	1,150	840
							2	1/4	20	21~35	17	19.6	4.5	1,000	1,100	850	1,200	1,320	1,020
							1	1/8	15	16~30	17	19.6	4.2	930	1,100	880	1,120	1,320	1,060
L寸指定タイプ APMTFL APMTSL APMTYL	T G N (PTネジ) (PFネジ) (NPTネジ)	2	1/4	—	M5	—	1	1/8	15	16~30	17	19.6	4.5	930	1,100	880	1,120	1,320	1,060
							2	1/4	20	21~35	17	19.6	6.5	1,010	1,200	950	1,210	1,440	1,140
							3	3/8	20	21~35	19	21.9	6.5	1,140	1,400	1,100	1,370	1,680	1,320
							2	1/4	20	21~35	19	21.9	9	1,020	1,260	970	1,220	1,510	1,160
							3	3/8	20	21~35	19	21.9	9	1,200	1,480	1,130	1,440	1,780	1,360
							4	1/2	25	26~40	24	27.7	9	1,490	1,990	1,480	1,790	2,390	1,780
							3	3/8	20	21~35	24	27.7	10	1,290	1,650	1,240	1,550	1,980	1,490
							4	1/2	25	26~40	24	27.7	10	1,400	1,830	1,390	1,680	2,200	1,670

型式 Type	ネジ形状①	No.	T(PT) G(PF) N(NPT)	ネジ形状②	No.	T(PT) G(PF) N(NPT)	L		B	(C)	d	¥基準単価							
							固定	指定1mm単位				L寸固定タイプ			L寸指定タイプ				
												APMFF	APMFS	APMFY	APMFFL	APMFSL	APMFYL		
L寸固定タイプ APMFF APMFS APMFY	T G N (PTネジ) (PFネジ) (NPTネジ)	1	1/8	—	M5	—	20	21~35	13	14.4	4.2	860	920	860	1,030	1,100	1,030		
							1	1/8	20	21~35	13	14.4	8.2	860	920	860	1,030	1,100	1,030
							2	1/4	20	21~35	17	19.6	8.2	950	1,060	970	1,140	1,270	1,160
							1	1/8	25	26~40	17	19.6	4.2	940	1,050	930	1,130	1,260	1,120
L寸指定タイプ APMFFL APMFSL APMFYL	T G N (PTネジ) (PFネジ) (NPTネジ)	2	1/4	—	M5	—	1	1/8	25	26~40	17	19.6	8.2	940	1,050	930	1,130	1,260	1,120
							2	1/4	25	26~40	17	19.6	10.9	990	1,080	980	1,190	1,300	1,180
							3	3/8	25	26~40	19	21.9	10.9	1,100	1,220	1,090	1,320	1,460	1,310
							2	1/4	25	26~40	19	21.9	10.9	1,030	1,200	1,020	1,240	1,440	1,220
							3	3/8	30	31~45	19	21.9	14.2	1,200	1,350	1,190	1,440	1,620	1,430
							4	1/2	35	36~50	24	27.7	14.2	1,410	1,630	1,360	1,690	1,960	1,630
							3	3/8	35	36~50	24	27.7	14.2	1,270	1,540	1,160	1,520	1,850	1,390
							4	1/2	35	36~50	24	27.7	17.8	1,290	1,560	1,330	1,550	1,870	1,600

<訂正用>

d	d
4.2	4.2
4.5	8.2
4.5	8.2
4.2	4.2
4.5	8.2
6.5	10.9
6.5	10.9
9	10.9
9	14.2
9	14.2
10	14.2
10	17.8