

下記赤枠内 表記・内容を変更

RoHS

先端形状				材質	硬度
球面	テーパ	テーパR	段付		
MRSHQ	MRSHT	MRSHR	MRSHD	SKH51	58HRC~
MRSSQ	MRSST	MRSSR	MRSSD	SUS440C相当	56HRC~
MRSQQ	MRSQT	MRSQR	MRSQD	SUS304	—

球面

テーパ

SR部研磨品

テーパR

段付

6.3 / (0.4 G)

■球面タイプ

Catalog No.	指定0.1mm単位		¥単価 1~4コ		
	D	L	SKH51 MRSHQ	SUS440C MRSSQ	SUS304 MRSQQ
MRSHQ MRSSQ MRSQQ	2.0~2.9	5.0~20.0	1,080	1,130	1,120
		20.1~50.0	990	1,030	1,020
		50.1~100.0	990	1,040	1,030
MRSHQ MRSSQ MRSQQ	3.0~3.9	5.0~20.0	1,140	1,180	1,180
		20.1~50.0	1,040	1,070	1,070
		50.1~100.0	1,080	1,120	1,120
MRSHQ MRSSQ MRSQQ	4.0~5.0	5.0~20.0	1,240	1,270	1,270
		20.1~50.0	1,120	1,160	1,160
		50.1~100.0	1,170	1,200	1,200

■テーパタイプ

Catalog No.	指定0.1mm単位		RL D-2 (RLtan15°) ≥0.2	¥単価 1~4コ		
	D	L		SKH51 MRSHT	SUS440C MRSST	SUS304 MRSQT
MRSHT MRSST MRSQT	2.0~2.9	5.0~20.0	0.5~10	640	690	680
		20.1~50.0		640	690	680
		50.1~100.0		640	690	680
MRSHT MRSST MRSQT	3.0~3.9	5.0~20.0		750	790	790
		20.1~50.0		700	740	740
		50.1~100.0		750	790	790
MRSHT MRSST MRSQT	4.0~5.0	5.0~20.0		830	880	880
		20.1~50.0		800	840	840
		50.1~100.0		830	880	880

■テーパRタイプ

Catalog No.	指定0.1mm単位		¥単価 1~4コ		
	D	L	SKH51 MRSHR	SUS440C MRSSR	SUS304 MRSQR
MRSHR MRSSR MRSQR	2.0~2.9	8.0~20.0	1,090	1,140	1,130
		20.1~50.0	990	1,030	1,030
		50.1~100.0	1,000	1,040	1,030
MRSHR MRSSR MRSQR	3.0~3.9	8.0~20.0	1,150	1,180	1,180
		20.1~50.0	1,040	1,080	1,080
		50.1~100.0	1,090	1,120	1,120
MRSHR MRSSR MRSQR	4.0~5.0	8.0~20.0	1,240	1,280	1,280
		20.1~50.0	1,130	1,160	1,160
		50.1~100.0	1,170	1,210	1,210

■段付タイプ

Catalog No.	指定0.1mm単位		¥単価 1~4コ				
	D	L	P (D>P)	B (B-P/2≥1.0)	SKH51 MRSHD	SUS440C MRSSD	SUS304 MRSQD
MRSHD MRSSD MRSQD	1.0~1.9	5.0~20.0	0.9~1.9	1.5~1.9	1,160	1,180	1,170
		20.1~50.0			1,050	1,080	1,070
		50.1~100.0			1,140	1,160	1,150
MRSHD MRSSD MRSQD	2.0~2.9	5.0~20.0			1,140	1,160	1,150
		20.1~50.0			1,030	1,060	1,040
		50.1~100.0			1,110	1,140	1,120
MRSHD MRSSD MRSQD	3.0~5.0	5.0~20.0			1,210	1,240	1,220
		20.1~50.0			1,100	1,130	1,110
		50.1~100.0			1,200	1,230	1,220



Order  
注文例

Catalog No. — D — L — P — B  
MRSHD — D1.5 — L100.0 — P0.9 — B1.9



Price  
価格

■数量スライド価格 (◎1円未満切り捨て) P.81

数量	1~4	5~19	20~49	50~99
値引率	価格表	5%	10%	15%

◎表示数量超えはお見積り




Delivery  
出荷日

3 日目発送

<訂正用>

1

硬度
58HRC~
56HRC~
—



3

L
8.0~20.0
20.1~50.0
50.1~100.0
8.0~20.0
20.1~50.0
50.1~100.0
8.0~20.0
20.1~50.0
50.1~100.0