

P. 1 -1209、1 -1210 <規格表>

1-1209 ①センターベアリング 20P5M150 の S 寸 5 → 4.5 ②両サイドベアリング 25P5M100 の A 寸 44 → 11.6、W 寸 32 → 16

1-1210 センターベアリング 上から 6 段目までの S 寸変更

■P2M・P3M・P5M・P8Mタイプ(センターベアリングタイプ)

Type	型式		軸径 d	P.D.	O.D.	F		E		A	W	S	ベアリング寸法			¥基準単価		
	歯数	対応ベルト				APTF	BPTF	APTF	BPTF				No.	D	B	APTF	BPTF	
APTF BPTF	40	P2M060	6	25.46	24.96	32	—	23	—	7.5	11.5	3.25	696ZZ×1	15	5	3,020	—	
	30	P3M100	6	28.65	27.89	35	35	25	25	12	16	5	626ZZ×1	19	6	3,590	3,500	
		P3M150								17	21	4.5				626ZZ×2	3,830	3,760
	20	P5M100	8	31.83	30.69	35	—	25	—	11.6	16	5	698ZZ×1	19	6	2,740	—	
		P5M150								16.6	21	4.5				698ZZ×2	3,260	—
	28	P5M100	10	44.56	43.42	50	50	38	38	11.6	16	3.5	6200ZZ×1	30	9	3,670	4,080	
		P5M150								16.6	21	6				4,070	4,190	
	20	P8M150	12	50.93	49.56	55	—	40	—	16.8	22	6	6201ZZ×1	32	10	5,430	—	
			15							27.8	33	5.5	6202ZZ×2	35	11	7,050	—	
		24	P8M250	12	61.12	59.74	67	—	50	—	27.8	33	6.5	6201ZZ×2	32	10	7,920	—
				15							16.8	22	5.5	6202ZZ×1	35	11	7,310	7,500
	30	P8M250	15	76.39	75.02	83	83	63	63	27.8	33	5.5	6202ZZ×2	35	11	9,280	9,510	

☞ 止め輪側開口部の径G寸法はD寸法と同じです。


<訂正用>



■P5M・P8Mタイプ(両サイドベアリングタイプ)

Type	型式		軸径 d	P.D.	O.D.	F		E		A	W	Dh	ベアリング寸法			¥基準単価		
	歯数	対応ベルト				APTFW KPTFW	BPTFW	APTFW KPTFW	BPTFW				No.	D	B	APTFW	KPTFW	BPTFW
APTFW KPTFW BPTFW	25	P5M100	6	39.79	38.65	—	44	—	32	11.6	16	13	696ZZ×2	15	5	—	—	5,890
		P5M150								16.6	21					—	—	6,050
		P5M100	8			44	32	11.6	16	16.5	698ZZ×2	19	6	4,240	4,680	6,050		
								P5M150	16.6					21	4,680	5,180	6,210	
	28	P5M100	10	44.56	43.42	50	50	38	38	11.6	16	19.5	6900ZZ×2	22	6	5,510	6,000	7,000
		P5M150								16.6	21					5,990	6,540	7,160
	30	P5M150	12	47.75	46.60	—	55	—	40	16.6	21	24	6001ZZ×2	28	8	—	—	6,880
		P5M150	15	57.30	56.15	—	67	—	50	16.6	21	28	6002ZZ×2	32	9	—	—	7,870
	26	P8M150	12	66.21	64.84	74	74	58	58	16.8	22	24	6001ZZ×2	28	8	7,760	8,610	9,370
		P8M250								27.8	33					9,350	10,400	10,370
	30	P8M150	15	76.39	75.02	83	83	63	63	16.8	22	28	6002ZZ×2	32	9	8,600	9,530	10,070
		P8M250								27.8	33					10,350	11,500	11,340
P8M250		20	27.8							33	36	6004ZZ×2	42	12	10,470	11,620	11,700	

<訂正用>



■2GT・3GT・5GT・8YU(センターベアリングタイプ)

Type	型式		軸径 d	P.D.	O.D.	F	E	A	W	S	ベアリング寸法				¥基準単価 1~9コ	
	歯数	対応ベルト									No.	D	B	G	AGTF	BGTF
AGTF BGTF	40	GT2060	6	25.46	24.96	30	21	7.0	10.3	2.15	606ZZ×1	17	6	17	2,350	—
		GT2090						21	10.0	13.3	3.65	606ZZ×1	17	6	17	2,890
	30	GT3060	6	28.65	27.89	32	23	7.3	11.0	2.50	606ZZ×1	17	6	17	2,460	—
		GT3090						23	10.3	14.0	4.00	606ZZ×1	17	6	17	2,750
	20	GT5090	8	31.83	30.69	35	24	10.3	14.0	4.00	698ZZ×1	19	6	19	2,440	2,490
		GT5120						24	13.3	17.0	5.50	698ZZ×1	19	6	19	2,560
	24	GT5090	10	38.20	37.06	42	30	10.3	14.0	4.50	6800ZZ×1	19	5	20	2,930	3,040
		GT5120						30	13.3	17.0	3.50	6800ZZ×2	19	5	20	3,260
	28	GT5090	10	44.56	43.42	48	36	10.3	14.0	4.50	6800ZZ×1	19	5	20	3,140	3,180
		GT5120						36	13.3	17.0	6.00	6800ZZ×1	19	5	20	3,210

<訂正用>

