




図面：D38用はP₁ザグリ穴は90°づつ配置されます

規格表：付属品 六角穴付ボルトの寸法を修正

RoHS

MBPGS-H



材 質 SS400

表面処理 四酸化鉄皮膜 (Fe₃O₄)

L	L ₁	D	D ₁	P	d	d ₁	T	P ₁	d ₂	d ₃	T ₁	付属品 六角穴付ボルト	型 式		L	¥基準単価 1~9本
													Type	No.		
40	25	80	40	57	9	14	9	18	7	12	7	M8-45 4本 M8-55 4本 M8-60 4本	M6-15 2本	38	40	3,500
50	35														50	4,130
55	40														55	4,760
45	30	90	47	68	11	17	11	20	9	14	9	M10-50 4本 M10-60 4本 M10-70 4本	M8-16 2本	45	45	4,660
55	40														55	5,350
65	50														65	5,780
55	40	100	52	75	13	20	13	20	9	14	9	M12-60 4本 M12-70 4本 M12-80 4本	M8-16 2本	50	55	5,780
65	50														65	6,550
75	60														75	7,320

●MBPGS-H38にはガススプリング取付用ボルト穴がP₁=18とP₁=25の2種の間ピッチで加工しています。