

NPA 200コ〜の価格を変更

■JIS B 2401 Pシリーズ (固定用・運動用)

| Catalog No. | | JIS | W | 内径 | | | 相手材 | | | | ¥単価 | | | | | | | | | | |
|-------------|------|-------|----------|-------|----------------|------------|------------|-------|-------|----|-----|--------|-------|--------|-------|--------|-------|--------|-------|----|----|
| Type | No. | 呼び番号 | | do | NPA・NPB 許容差 | NPS 許容差 | NPF 許容差 | d | 許容差 | D | 許容差 | NPA | | NPB | | NPS | | NPF | | | |
| | | | | | | | | | | | | 1~199コ | 200コ~ | 1~199コ | 200コ~ | 1~199コ | 200コ~ | 1~199コ | 200コ~ | | |
| | 3 | P3 | 1.9±0.08 | 2.8 | | | 3 | | 6 | | 70 | 10 | 66 | 13 | 72 | 14 | 73 | 14 | 70 | 10 | |
| | 4 | P4 | | 3.8 | ±0.14 | ±0.21 | ±0.16 | 4 | | 7 | | 70 | 10 | 66 | 13 | 72 | 14 | 73 | 14 | 70 | 10 |
| | 5 | P5 | | 4.8 | | | | 5 | | 8 | | 70 | 10 | 66 | 13 | 72 | 14 | 82 | 16 | 70 | 10 |
| | 6 | P6 | | 5.8 | ±0.15 | ±0.22 | ±0.18 | 6 | 0 | 9 | | 70 | 10 | 66 | 13 | 80 | 16 | 82 | 16 | 70 | 10 |
| | 7 | P7 | | 6.8 | | | | 7 | -0.05 | 10 | 0 | 70 | 10 | 66 | 13 | 80 | 16 | 108 | 21 | 70 | 10 |
| | 8 | P8 | | 7.8 | ±0.16 | ±0.24 | ±0.19 | 8 | | 11 | | 70 | 10 | 66 | 13 | 80 | 16 | 112 | 22 | 70 | 10 |
| | 9 | P9 | | 8.8 | | | | 9 | | 12 | | 70 | 10 | 66 | 13 | 80 | 16 | 112 | 22 | 70 | 10 |
| | 10 | P10 | | 9.8 | ±0.17 | ±0.25 | ±0.20 | 10 | | 13 | | 70 | 10 | 72 | 14 | 80 | 16 | 112 | 22 | 70 | 10 |
| | 10A | P10A | | 9.8 | | | | 10 | | 14 | | 86 | 13 | 72 | 14 | 98 | 19 | 140 | 28 | 86 | 13 |
| | 11 | P11 | | 10.8 | | | | 11 | | 15 | | 86 | 13 | 72 | 14 | 98 | 19 | 140 | 28 | 86 | 13 |
| | 11.2 | P11.2 | 11.0 | ±0.18 | ±0.27 | ±0.21 | 11.2 | | 15.2 | | 86 | 13 | 72 | 14 | 98 | 19 | 140 | 28 | 86 | 13 | |
| | 12 | P12 | 11.8 | | | | 12 | | 16 | | 86 | 13 | 90 | 18 | 98 | 19 | 140 | 28 | 86 | 13 | |
| | 12.5 | P12.5 | 12.3 | ±0.19 | ±0.28 | ±0.22 | 12.5 | | 16.5 | | 86 | 13 | 90 | 18 | 98 | 19 | 140 | 28 | 86 | 13 | |
| | 14 | P14 | 13.8 | | | | 14 | 0 | 18 | | 86 | 13 | 90 | 18 | 98 | 19 | 140 | 28 | 86 | 13 | |
| | 15 | P15 | 14.8 | | | | 15 | -0.06 | 19 | 0 | 104 | 16 | 103 | 20 | 133 | 26 | 145 | 29 | 104 | 16 | |
| | 16 | P16 | 15.8 | ±0.20 | ±0.30 | ±0.24 | 16 | | 20 | | 104 | 16 | 103 | 20 | 133 | 26 | 145 | 29 | 104 | 16 | |
| | 18 | P18 | 17.8 | ±0.21 | ±0.31 | ±0.25 | 18 | | 22 | | 104 | 16 | 103 | 20 | 133 | 26 | 176 | 35 | 104 | 16 | |
| | 20 | P20 | 19.8 | ±0.22 | ±0.33 | ±0.26 | 20 | | 24 | | 104 | 16 | 103 | 20 | 143 | 28 | 176 | 35 | 104 | 16 | |
| | 21 | P21 | 20.8 | ±0.23 | ±0.34 | ±0.27 | 21 | | 25 | | 104 | 16 | 103 | 20 | 143 | 28 | 210 | 42 | 104 | 16 | |
| | 22 | P22 | 21.8 | | | | 22 | | 26 | | 104 | 16 | 103 | 20 | 143 | 28 | 210 | 42 | 104 | 16 | |
| | 22A | P22A | 21.7 | | | | 22 | | 28 | | 117 | 18 | 108 | 21 | 185 | 37 | 307 | 61 | 117 | 18 | |
| | 22.4 | P22.4 | 22.1 | ±0.24 | ±0.36 | ±0.28 | 22.4 | | 28.4 | | 117 | 18 | 108 | 21 | 185 | 37 | 307 | 61 | 117 | 18 | |
| | 24 | P24 | 23.7 | | | | 24 | | 30 | | 117 | 18 | 108 | 21 | 185 | 37 | 325 | 65 | 117 | 18 | |
| | 25 | P25 | 24.7 | | | | 25 | | 31 | | 120 | 18 | 108 | 21 | 185 | 37 | 325 | 65 | 120 | 18 | |
| | 25.5 | P25.5 | 25.2 | ±0.25 | ±0.37 | ±0.30 | 25.5 | | 31.5 | | 120 | 18 | 108 | 21 | 185 | 37 | 337 | 67 | 120 | 18 | |
| | 26 | P26 | 25.7 | ±0.26 | ±0.39 | ±0.31 | 26 | | 32 | | 120 | 18 | 108 | 21 | 185 | 37 | 337 | 67 | 120 | 18 | |
| | 28 | P28 | 27.7 | ±0.28 | ±0.42 | ±0.33 | 28 | | 34 | | 120 | 18 | 112 | 22 | 203 | 40 | 370 | 74 | 120 | 18 | |
| | 29 | P29 | 28.7 | | | | 29 | | 35 | | 125 | 19 | 112 | 22 | 203 | 40 | 370 | 74 | 125 | 19 | |
| | 29.5 | P29.5 | 29.2 | ±0.29 | ±0.43 | ±0.34 | 29.5 | | 35.5 | | 125 | 19 | 112 | 22 | 203 | 40 | 374 | 74 | 125 | 19 | |
| | 30 | P30 | 29.7 | | | | 30 | | 36 | | 125 | 19 | 105 | 21 | 203 | 40 | 374 | 74 | 125 | 19 | |
| | 31 | P31 | 30.7 | ±0.30 | ±0.45 | ±0.36 | 31 | | 37 | | 125 | 19 | 105 | 21 | 207 | 41 | 402 | 80 | 125 | 19 | |
| | 31.5 | P31.5 | 31.2 | ±0.31 | ±0.46 | ±0.37 | 31.5 | | 37.5 | | 125 | 19 | 115 | 23 | 224 | 44 | 402 | 80 | 125 | 19 | |
| | 32 | P32 | 31.7 | | | | 32 | | 38 | | 125 | 19 | 115 | 23 | 224 | 44 | 466 | 93 | 125 | 19 | |
| | 34 | P34 | 33.7 | ±0.33 | ±0.49 | ±0.39 | 34 | 0 | 40 | | 125 | 19 | 115 | 23 | 224 | 44 | 466 | 93 | 125 | 19 | |
| | 35 | P35 | 34.7 | | | | 35 | -0.08 | 41 | 0 | 125 | 19 | 115 | 23 | 224 | 44 | 494 | 98 | 125 | 19 | |
| | 35.5 | P35.5 | 35.2 | ±0.34 | ±0.51 | ±0.40 | 35.5 | | 41.5 | | 125 | 19 | 157 | 31 | 224 | 44 | 494 | 98 | 127 | 19 | |
| | 36 | P36 | 35.7 | | | | 36 | | 42 | | 127 | 19 | 157 | 31 | 257 | 51 | 494 | 98 | 127 | 19 | |
| | 38 | P38 | 37.7 | | | | 38 | | 44 | | 127 | 19 | 157 | 31 | 257 | 51 | 494 | 98 | 127 | 19 | |
| | 39 | P39 | 38.7 | ±0.37 | ±0.55 | ±0.44 | 39 | | 45 | | 127 | 19 | 157 | 31 | 257 | 51 | 524 | 104 | 127 | 19 | |
| | 40 | P40 | 39.7 | | | | 40 | | 46 | | 137 | 21 | 160 | 32 | 273 | 54 | 524 | 104 | 137 | 21 | |
| | 41 | P41 | 40.7 | ±0.38 | ±0.57 | ±0.45 | 41 | | 47 | | 137 | 21 | 160 | 32 | 273 | 54 | 552 | 110 | 137 | 21 | |
| | 42 | P42 | 41.7 | ±0.39 | ±0.58 | ±0.48 | 42 | | 48 | | 137 | 21 | 160 | 32 | 273 | 54 | 552 | 110 | 137 | 21 | |
| | 44 | P44 | 43.7 | | | | 44 | | 50 | | 150 | 23 | 160 | 32 | 273 | 54 | 552 | 110 | 150 | 23 | |
| | 45 | P45 | 44.7 | ±0.41 | ±0.61 | ±0.49 | 45 | | 51 | | 150 | 23 | 160 | 32 | 277 | 55 | 650 | 130 | 150 | 23 | |
| | 46 | P46 | 45.7 | ±0.42 | ±0.63 | ±0.50 | 46 | | 52 | | 150 | 23 | 160 | 32 | 277 | 55 | 650 | 130 | 150 | 23 | |
| | 48 | P48 | 47.7 | ±0.44 | ±0.66 | ±0.52 | 48 | | 54 | | 150 | 23 | 180 | 36 | 277 | 55 | 650 | 130 | 150 | 23 | |
| | 50 | P50 | 49.7 | ±0.45 | ±0.67 | ±0.54 | 50 | | 56 | | 228 | 35 | 240 | 48 | 379 | 75 | 805 | 161 | 228 | 35 | |

<訂正用>