



Price 標準ユニット価格

価格 (例) HAU BA 6-3030-W1000-D800-H700

ユニット形状がBAの欄で、フレーム種類が6-3030の行を右に見ます。次に、W+D+Hの合計値2500により縦の列を選択し、交わったところがユニット価格13,090円になります。この価格には、ユニットを構成する全ての部品（ブラケット、ボルト、先入れナット等）が含まれています。この構成部品の内容は、P.2130をご参照ください。

■四面溝タイプ

Catalog No.		(W+D+H)															
Type	ユニット形状	フレーム種類HFS	900 1249	1250 1599	1600 1949	1950 2299	2300 2649	2650 2999	3000 3349	3350 3699	3700 4049	4050 4399	4400 4749	4750 5099	5100 5449	5450 5799	5800 6000
BA	5-2020	6,610	7,340	8,070	8,790	9,520	10,250	10,980	—	—	—	—	—	—	—	—	—
	5-4040	13,460	15,360	17,270	19,170	21,070	22,980	24,880	26,790	—	—	—	—	—	—	—	—
	6-3030	7,930	9,220	10,510	11,800	13,090	14,370	15,660	16,950	—	—	—	—	—	—	—	—
	6L-3030	6,990	8,020	9,040	10,060	11,080	12,100	13,130	14,150	—	—	—	—	—	—	—	—
	8-4040	11,260	13,600	15,940	18,270	20,610	22,950	25,290	27,630	29,960	32,300	34,640	36,980	39,320	—	—	—
	8L-4040	10,240	12,110	13,970	15,830	17,690	19,550	21,420	23,280	25,140	27,000	28,860	30,730	32,590	—	—	—
	8-4545	12,590	15,600	18,610	21,620	24,630	27,640	30,650	33,660	36,670	39,680	42,690	45,700	48,710	—	—	—
	8L-4545	11,180	13,500	15,820	18,150	20,470	22,800	25,120	27,440	29,770	32,090	34,420	36,740	39,060	—	—	—
	6-5050	16,880	20,460	24,050	27,630	31,220	34,800	38,380	41,970	45,550	49,140	52,720	56,300	59,890	—	—	—
	6-6060	—	20,140	23,790	27,440	31,100	34,750	38,410	42,060	45,710	49,370	53,020	56,680	60,330	—	—	—
8-6060	—	31,360	36,860	42,360	47,870	53,370	58,870	64,370	69,870	75,380	80,880	86,380	91,880	—	—	—	
8-8080	—	39,780	46,430	53,080	59,730	66,380	73,030	79,680	86,330	92,980	99,630	106,280	112,930	119,580	126,230	—	—
8-9090	—	47,450	56,800	66,150	75,500	84,860	94,210	103,560	112,910	122,260	131,620	140,970	150,320	159,670	169,020	—	—
BB	5-2020	11,210	12,280	13,350	14,420	15,490	16,550	17,620	—	—	—	—	—	—	—	—	—
	5-4040	22,660	25,450	28,240	31,030	33,830	36,620	39,410	42,200	—	—	—	—	—	—	—	—
	6-3030	13,130	15,020	16,910	18,800	20,690	22,580	24,470	26,360	—	—	—	—	—	—	—	—
	6L-3030	11,390	12,890	14,390	15,890	17,390	18,890	20,390	21,880	—	—	—	—	—	—	—	—
	8-4040	18,270	21,700	25,130	28,560	31,990	35,410	38,840	42,270	45,700	49,130	52,560	55,990	59,420	—	—	—
	8L-4040	16,590	19,920	23,250	26,580	29,910	33,240	36,570	39,900	43,230	46,560	49,890	53,220	56,550	59,880	—	—
	8-4545	20,090	24,510	28,920	33,340	37,750	42,170	46,580	51,000	55,410	59,830	64,240	68,650	73,070	—	—	—
	8L-4545	18,090	21,500	24,900	28,310	31,720	35,130	38,540	41,950	45,360	48,760	52,170	55,580	58,990	—	—	—
	6-5050	27,630	32,890	38,140	43,400	48,650	53,910	59,170	64,420	69,680	74,940	80,190	85,450	90,710	—	—	—
	6-6060	—	32,280	37,640	43,000	48,350	53,710	59,070	64,430	69,790	75,150	80,510	85,870	91,230	—	—	—
8-6060	—	50,580	58,650	66,720	74,790	82,860	90,930	99,000	107,070	115,140	123,210	131,280	139,340	—	—	—	
8-8080	—	64,670	74,420	84,180	93,930	103,680	113,440	123,190	132,940	142,700	152,450	162,200	171,960	181,710	191,460	—	—
8-9090	—	75,740	89,460	103,180	116,890	130,610	144,320	158,040	171,760	185,470	199,190	212,910	226,620	240,340	254,050	—	—
HAU BC	5-2020	11,210	12,280	13,350	14,420	15,490	16,550	17,620	—	—	—	—	—	—	—	—	—
	5-4040	22,660	25,450	28,240	31,030	33,830	36,620	39,410	42,200	—	—	—	—	—	—	—	—
	6-3030	13,130	15,020	16,910	18,800	20,690	22,580	24,470	26,360	—	—	—	—	—	—	—	—
	6L-3030	11,390	12,890	14,390	15,890	17,390	18,890	20,390	21,880	—	—	—	—	—	—	—	—
	8-4040	18,270	21,700	25,130	28,560	31,990	35,410	38,840	42,270	45,700	49,130	52,560	55,990	59,420	—	—	—
	8L-4040	16,590	19,920	23,250	26,580	29,910	33,240	36,570	39,900	43,230	46,560	49,890	53,220	56,550	59,880	—	—
	8-4545	20,090	24,510	28,920	33,340	37,750	42,170	46,580	51,000	55,410	59,830	64,240	68,650	73,070	—	—	—
	8L-4545	18,090	21,500	24,900	28,310	31,720	35,130	38,540	41,950	45,360	48,760	52,170	55,580	58,990	—	—	—
	6-5050	27,630	32,890	38,140	43,400	48,650	53,910	59,170	64,420	69,680	74,940	80,190	85,450	90,710	—	—	—
	6-6060	—	32,280	37,640	43,000	48,350	53,710	59,070	64,430	69,790	75,150	80,510	85,870	91,230	—	—	—
8-6060	—	50,580	58,650	66,720	74,790	82,860	90,930	99,000	107,070	115,140	123,210	131,280	139,340	—	—	—	
8-8080	—	64,670	74,420	84,180	93,930	103,680	113,440	123,190	132,940	142,700	152,450	162,200	171,960	181,710	191,460	—	—
8-9090	—	75,740	89,460	103,180	116,890	130,610	144,320	158,040	171,760	185,470	199,190	212,910	226,620	240,340	254,050	—	—
BD	5-2020	4,670	5,210	5,760	6,310	6,850	7,400	7,940	—	—	—	—	—	—	—	—	—
	5-4040	9,570	11,000	12,420	13,850	15,280	16,710	18,140	19,560	—	—	—	—	—	—	—	—
	6-3030	5,700	6,660	7,630	8,590	9,560	10,530	11,490	12,460	—	—	—	—	—	—	—	—
	6L-3030	5,110	5,870	6,640	7,410	8,170	8,940	9,710	10,470	—	—	—	—	—	—	—	—
	8-4040	8,200	9,950	11,700	13,460	15,210	16,960	18,720	20,470	22,220	23,980	25,730	27,480	29,240	—	—	—
	8L-4040	7,500	8,900	10,300	11,690	13,090	14,480	15,880	17,280	18,670	20,070	21,470	22,860	24,260	—	—	—
	8-4545	9,270	11,530	13,790	16,050	18,300	20,560	22,820	25,080	27,330	29,590	31,850	34,110	36,360	—	—	—
	8L-4545	8,170	9,910	11,660	13,400	15,140	16,890	18,630	20,370	22,110	23,860	25,600	27,340	29,090	—	—	—
	6-5050	12,230	14,920	17,610	20,300	22,980	25,670	28,360	31,050	33,740	36,420	39,110	41,800	44,490	—	—	—
	6-6060	—	14,740	17,480	20,220	22,960	25,700	28,440	31,180	33,920	36,660	39,410	42,150	44,890	—	—	—
8-6060	—	23,000	27,130	31,260	35,380	39,510	43,640	47,760	51,890	56,020	60,140	64,270	68,400	—	—	—	
8-8080	—	29,020	34,000	38,990	43,980	48,970	53,950	58,940	63,930	68,920	73,900	78,890	83,880	88,870	93,850	—	—
8-9090	—	35,120	42,140	49,150	56,160	63,180	70,190	77,210	84,220	91,230	98,250	105,260	112,280	119,290	126,300	—	—
BE	5-2020	8,150	8,870	9,600	10,330	11,060	11,790	12,510	—	—	—	—	—	—	—	—	—
	5-4040	16,450	18,350	20,260	22,160	24,070	25,970	27,870	29,780	—	—	—	—	—	—	—	—
	6-3030	9,510	10,800	12,090	13,370	14,660	15,950	17,240	18,530	—	—	—	—	—	—	—	—
	6L-3030	8,350	9,380	10,400	11,420	12,440	13,460	14,490	15,510	—	—	—	—	—	—	—	—
	8-4040	13,220	15,560	17,900	20,230	22,570	24,910	27,250	29,590	31,920	34,260	36,600	38,940	41,280	—	—	—
	8L-4040	12,110	13,970	15,830	17,690	19,550	21,420	23,280	25,140	27,000	28,870	30,730	32,590	34,450	—	—	—
	8-4545	14,550	17,560	20,570	23,580	26,590	29,600	32,610	35,620	38,630	41,640	44,650	47,660	50,670	—	—	—
	8L-4545	13,140	15,460	17,780	20,110	22,430	24,760	27,080	29,400	31,730	34,050	36,380	38,700	41,020	—	—	—
	6-5050	19,990	23,580	27,160	30,740	34,330	37,910	41,500	45,080	48,660	52,250	55,830	59,420	63,000	—	—	—
	6-6060	—	23,210														