





* WIRING : 2 COAX.



*INSPECTION HEADS:
1.APPEARANCE:
RE CONNECTOR; INSERTION
RUST,SHAPE.
RE HOOD;CRACK,SHAPE
TRANSFORMATION.
RE CABLE;CRACK,DIA.
LENGTH.
2.STRUCTURE,MEASURE:
CONFIRM ALL OF THE DIME-
NSION AND PART.
3.WIRING:
ANY OPEN,SHORT,MISSED
WIRING,INTERMITMENT ARE
NOT PERMITTED.
4.HI-POT TEST:
NECESSITY UNNECESSITY
5.PACKING:
TIED A POINT ONE BY ONE,
PACKED IN A POLY BAG.

No.	ITEM	PARTS	Q'TY
①	CONNECTOR"A"	RCA PINS(GOLD PLATING)	2
②	CONNECTOR"B"	STEREO MINI PLUG(GOLD PLATING)	1
③	HOOD"A"	RED MOLD	1
④		WHITE MOLD	1
⑤	HOOD"B"	BLACK MOLD	1
⑥	CABLE	UL STANDARD, 2 COAX.(75Ω)	1
⑦	CABLE SHIELD	SPIRAL	
⑧	CABLE COLOR	BLACK	
⑨			
⑩			
⑪			
⑫			
⑬			
ITEM NO.:		MSORC-1.5 =1.5m MSORC-3 =3m MSORC-5 =5m	APD: DES: DWN