

回転軸

—D公差 h9(みがき棒)/h7(研磨棒)/g6(研磨棒)—
—ストレートタイプ—



Price
価格

■数量スライド価格 (●1円未満切り捨て) P.127

数量区分	標準対応						個別対応 大口
	小口			大口			
数量	1～9	10～14	15～19	20～49	50～300	301～400	401～
値引率	基準単価	5%	10%	20%	20%	30%	お見積り
出荷日	通常			+1日	+2日	+3日	

①h9(みがき棒)

●D寸法50は101本以上の場合出荷日、価格共にお見積りとなります。
●表示数量超えはWOSにてご確認ください。●標準対応大口以上はSラー対応なし。

Type	¥ NSFMR (S45C相当・表面処理なし)										¥ SFMR (S45C相当・四三酸化鉄皮膜)									
	最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0		最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0	
3	280	340	400	—	—	—	—	—	—		290	350	410	—	—	—	—	—	—	
4	250	310	380	400	—	—	—	—	—		270	320	390	410	—	—	—	—	—	
5	260	310	380	400	470	—	—	—	—		270	320	390	410	480	—	—	—	—	
6	300	340	380	420	620	710	—	—	—		320	370	410	450	670	760	—	—	—	
8	300	340	380	420	620	710	870	—	—		320	370	410	450	670	760	930	—	—	
10	300	340	380	420	620	710	870	—	—		320	370	410	450	670	760	930	—	—	
12	330	380	420	450	640	730	1,060	1,240	—		370	430	470	500	720	820	1,180	1,380	—	
15	360	410	460	480	690	790	1,130	1,320	—		400	460	520	540	770	880	1,260	1,470	—	
20	440	560	570	640	890	1,000	1,330	1,600	2,070	510	650	660	740	1,030	1,150	1,540	1,840	2,380		
25	520	730	820	900	1,130	1,370	1,850	2,380	3,300	600	840	950	1,040	1,300	1,580	2,130	2,740	3,800		
30	—	780	890	980	1,290	1,510	2,100	2,800	4,010	—	900	1,030	1,130	1,490	1,740	2,420	3,220	4,610		
35	—	1,160	1,300	1,430	1,920	2,180	3,080	4,040	5,700	—	1,340	1,500	1,650	2,210	2,510	3,550	4,650	6,560		
40	—	1,400	1,560	1,730	2,300	2,630	3,690	4,830	6,810	—	1,620	1,800	1,990	2,650	3,030	4,250	5,560	7,830		
50	—	1,820	2,040	2,250	3,020	3,410	4,790	6,260	8,810	—	2,100	2,350	2,590	3,480	3,920	5,510	7,200	10,130		

Type	¥ PSFMR (S45C相当・無電解ニッケルメッキ)										¥ SSFMR (SUS304)									
	最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0		最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0	
3	330	390	440	—	—	—	—	—	—		380	420	520	—	—	—	—	—	—	
4	310	370	420	470	—	—	—	—	—		380	420	520	610	—	—	—	—	—	
5	310	370	420	470	550	—	—	—	—		380	420	520	610	670	—	—	—	—	
6	370	410	480	520	740	850	—	—	—		—	—	—	—	—	—	—	—	—	
8	370	410	480	520	740	850	970	—	—		430	470	550	620	950	1,050	1,170	—	—	
10	370	410	480	520	740	850	970	—	—		430	470	550	620	980	1,050	1,170	—	—	
12	400	480	510	560	790	890	1,260	1,570	—		490	580	630	710	1,010	1,160	1,450	1,830	—	
15	440	520	540	600	890	1,020	1,440	1,790	—		620	720	740	820	1,180	1,320	1,660	2,090	—	
20	590	750	790	880	1,180	1,350	1,760	2,940	3,480	700	880	900	1,000	1,470	1,960	2,940	3,890	4,430		
25	740	1,100	1,210	1,350	2,030	2,710	4,050	5,270	6,330	840	1,140	1,250	1,390	2,110	2,780	4,250	5,500	6,560		
30	—	1,160	1,310	1,730	2,550	3,400	5,130	6,830	8,220	—	1,250	1,440	1,820	2,750	3,620	5,540	7,400	8,790		
35	—	1,870	2,500	3,680	4,980	7,550	9,910	11,820	—		1,980	2,220	2,710	4,010	5,340	8,080	10,450	12,360		
40	—	2,030	2,250	3,000	4,420	5,980	9,070	11,810	14,170	—	2,390	2,670	3,270	4,820	6,430	9,700	12,580	14,830		
50	—	2,650	2,930	3,900	5,750	7,770	11,790	15,470	18,400	—	3,090	3,480	4,240	5,980	7,970	12,610	16,350	19,280		

②h7(研磨棒) ③g6(研磨棒)

Type	¥ NSFHR・NSFR (S45C相当・表面処理なし)										¥ SFHR・SFR (S45C相当・四三酸化鉄皮膜)									
	最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0		最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0	
2	510	—	—	—	—	—	—	—	—		510	—	—	—	—	—	—	—	—	
2.5	450	—	—	—	—	—	—	—	—		450	—	—	—	—	—	—	—	—	
3	320	380	450	—	—	—	—	—	—		330	390	460	—	—	—	—	—	—	
4	290	350	430	450	—	—	—	—	—		300	360	440	460	—	—	—	—	—	
5	290	350	430	450	530	—	—	—	—		300	360	440	460	550	—	—	—	—	
6	330	380	430	470	710	800	—	—	—		360	410	460	510	760	860	—	—	—	
8	330	380	430	470	710	800	980	—	—		360	410	460	510	760	860	1,050	—	—	
10	330	380	430	470	710	800	980	—	—		360	410	460	510	760	860	1,050	—	—	
12	370	430	470	500	720	830	1,190	1,400	—		420	480	530	560	810	930	1,330	1,560	—	
13	390	450	510	530	760	880	1,260	1,470	—		440	510	570	590	850	980	1,400	1,640	—	
15	400	460	520	540	780	900	1,280	1,500	—		450	520	580	610	870	1,000	1,430	1,670	—	
16	400	520	530	570	840	950	1,350	1,600	2,070	460	600	610	660	970	1,100	1,560	1,850	2,380		
17	400	530	530	620	900	1,010	1,380	1,630	2,090	470	610	620	720	1,040	1,170	1,590	1,880	2,410		
18	420	560	580	670	980	1,110	1,490	1,780	2,300	490	650	670	780	1,140	1,280	1,720	2,050	2,650		
20	490	630	650	730	1,000	1,130	1,520	1,800	2,330	570	730	750	840	1,160	1,300	1,750	2,080	2,680		
22	580	780	870	960	1,190	1,460	1,970	2,200	2,690	670	900	1,010	1,110	1,370	1,680	2,270	2,540	3,100		
25	590	820	930	1,020	1,270	1,550	2,090	2,700	3,750	680	950	1,070	1,180	1,470	1,790	2,410	3,110	4,320		
30	—	880	1,000	1,110	1,470	1,710	2,380	3,170	4,550	—	1,020	1,160	1,280	1,690	1,970	2,740	3,650	5,230		
35	—	1,320	1,470	1,620	2,180	2,470	3,500	4,590	6,480	—	1,520	1,700	1,870	2,510	2,850	4,030	5,280	7,450		
40	—	1,600	1,770	1,950	2,610	2,990	4,190	5,480	7,730	—	1,840	2,040	2,250	3,010	3,440	4,820	6,310	8,890		
50	—	2,070	2,310	2,550	3,430	3,870	5,430	7,100	10,000	—	2,380	2,660	2,940	3,950	4,450	6,250	8,170	11,500		

Type	¥ PSFHR・PSFR (S45C相当・無電解ニッケルメッキ)										¥ SSFHR・SSFR (SUS304)									
D	最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0		最短L ↓ 50.0	L50.1 ↓ 100.0	L100.1 ↓ 150.0	L150.1 ↓ 200.0	L200.1 ↓ 300.0	L300.1 ↓ 400.0	L400.1 ↓ 600.0	L600.1 ↓ 800.0	L800.1 ↓ 1000.0	
2	550	—	—	—	—	—	—	—	—		630	—	—	—	—	—	—	—	—	
2.5	480	—	—	—	—	—	—	—	—		550	—	—	—	—	—	—	—	—	
3	370	440	500	—	—	—	—	—	—		410	470	580	—	—	—	—	—	—	
4	340	410	470	530	—	—	—	—	—		410	470	580	670	—	—	—	—	—	
5	340	410	470	530	620	—	—	—	—		410	470	580	670	740	—	—	—	—	
6	410	460	540	590	840	960	—	—	—		470	520	610	680	1,050	1,160	—	—	—	
8	410	460	540	590	840	960	1,100	—	—		470	520	610	680	1,050	1,160	1,300	—	—	
10	410	460	540	590	840	960	1,100	—	—		470	520	610	680	1,080	1,160	1,300	—	—	
12	450	540	570	630	890	1,010	1,430	1,660	—		540	640	690	780	1,120	1,280	1,610	2,030	—	
13	480	570	600	660	950	1,080	1,520	1,760	—		—	—	—	—	—	—	—	—	—	
15	490	580	610	680	1,010	1,150	1,630	2,030	—		680	790	820	910	1,310	1,460	1,840	2,320	—	
16	530	670	700	760	1,150	1,320	1,780	2,390	2,920		—	—	—	—	—	—	—	—	—	
17	540	680	710	820	1,170	1,340	1,810	2,670	3,200		690	850	900	960	1,410	1,560	2,190	2,890	3,420	
18	580	760	800	930	1,320	1,510	1,970	3,120	3,720		—	—	—	—	—	—	—	—	—	
20	670	850	890	990	1,340	1,530	2,000	3,330	3,930		770	970	990	1,110	1,630	2,170	3,260	4,320	4,920	
22	820	1,130	1,250	1,440	1,870	2,240	3,590	4,150	—		930	—	1,380	1,540	2,340	3,080	4,720	6,110	7,320	
25	830	1,240	1,370	1,530	2,300	3,070	4,600	5,980	7,190		—	1,260	1,380	1,590	2,020	3,050	4,020	6,150	8,220	
30	—	1,310	1,480	1,960	2,890	3,860	5,820	7,760	9,340		—	1,380	1,590	2,020	3,050	4,020	6,150	8,220	9,800	
35	—	1,920	2,120	2,830	4,180	5,650	8,570	11,260	13,430		—	2,190	2,460	3,010	4,450	5,930	8,970	11,610	13,780	
40	—	2,310	2,550	3,400	5,020	6,780	10,290	13,520	15,900		—	2,640	2,960	3,630	5,350	7,140	10,770	13,950	16,330	
50	—	3,010	3,320	4,420	6,530	8,820	13,380	17,580	19,800		—	3,420	3,860	4,710	6,640	8,850	14,000	18,170	20,390	