





\* WIRING: 2 COAX.

| A |       | B                      |
|---|-------|------------------------|
| 1 | ————— | 1 COAX.                |
| 2 | ————— | 2 COAX.                |
| 3 | ————— | 3 SHIELD OF BOTH COAX. |



**\*INSPECTION HEADS:**

1.APEARANCE:  
RE CONNECTOR; INSERTION  
RUST,SHAPE.  
RE HOOD;CRACK,SHAPE  
TRANSFORMATION.  
RE CABLE;CRACK,DIA.  
LENGTH.

2.STRUCTURE,MEASURE:  
CONFIRM ALL OF THE DIME-  
NSION AND PART.

3.WIRING:  
ANY OPEN,SHORT,MISSED  
WIRING,INTERMITMENT ARE  
NOT PERMITTED.

#### 4.HI-POT TEST: NECESSITY UNNECESSITY

5.PACKING:  
TIED A POINT ONE BY ONE,  
PACKED IN A POLY BAG.

| No. | ITEM         | PARTS                          | Q'TY |
|-----|--------------|--------------------------------|------|
| ①   | CONNECTOR"A" | STEREO MINI PLUG(GOLD PLATING) | 1    |
| ②   | CONNECTOR"B" | STEREO MINI PLUG(GOLD PLATING) | 1    |
| ③   | HOOD"A"      | BLACK MOLD                     | 1    |
| ④   | HOOD"B"      | BLACK MOLD                     | 1    |
| ⑤   | CABLE        | UL STANDARD, 2 COAX.(75Ω )     | 1    |
| ⑥   | CABLE SHIELD | SPIRAL                         |      |
| ⑦   | CABLE COLOR  | BLACK                          |      |
| ⑧   |              |                                |      |
| ⑨   |              |                                |      |
| ⑩   |              |                                |      |
| ⑪   |              |                                |      |
| ⑫   |              |                                |      |
| ⑬   |              |                                |      |

|           |                 |      |      |     |
|-----------|-----------------|------|------|-----|
| ITEM NO.: | EMSOD-1.5 =1.5m | APD: | DES: | DWN |
|           | EMSOD-3 =3m     |      |      |     |
|           | EMSOD-5 =5m     |      |      |     |