



DATE:AUG, 22, 2014



* WIRING : 2 COAX.

- | | |
|-----------|----------------------|
| A | B |
| 1 ————— 1 | COAX. |
| 2 ————— 2 | COAX. |
| 3 ————— 3 | SHIELD OF BOTH COAX. |



*INSPECTION HEADS:

- 1.APEARANCE:
RE CONNECTOR; INSERTION RUST,SHAPE.
RE HOOD;CRACK,SHAPE TRANSFORMATION.
- 2.STRUCTURE,MEASURE:
RE CABLE;CRACK,DIA. LENGTH.
- 3.WIRING:
CONFIRM ALL OF THE DIMENSION AND PART.
- 4.HI-POT TEST:
ANY OPEN,SHORT,MISSED WIRING,INTERMITMENT ARE NOT PERMITTED.
- 5.PACKING:
NECESSITY UNNECESSITY
TIED A POINT ONE BY ONE,
PACKED IN A POLY BAG.

No.	ITEM	PARTS	Q'TY
①	CONNECTOR"A"	STEREO MINI PLUG(GOLD PLATING)	1
②	CONNECTOR"B"	STEREO MINI PLUG(GOLD PLATING)	1
③	HOOD"A"	BLACK MOLD	1
④	HOOD"B"	BLACK MOLD	1
⑤	CABLE	UL STANDARD, 2 COAX.(75Ω)	1
⑥	CABLE SHIELD	SPIRAL	
⑦	CABLE COLOR	BLACK	
⑧			
⑨			
⑩			
⑪			
⑫			
⑬			

ITEM NO.:	MSODS-1.5 =1.5m	APD:	DES:	DWN
	MSODS-3 =3m			
	MSODS-5 =5m			