

回転軸

一片端段付・止め輪溝タイプ/両端段付・止め輪溝タイプ



Price
価格

■数量スライド価格 (◎1円未満切り捨て) R127

数量区分	標準対応						個別対応
	小口			大口			大口
数量	1～9	10～14	15～19	20～49	50～300	301～400	401～
値引率	基準単価	5%	10%	20%	20%	30%	
出荷日	通常			+1日	+2日	+3日	お見積り

◎D寸法50は101本以上の場合出荷日、価格共にお見積りとなります。

◎表示数量超えはWOSにてご確認ください。◎標準対応大口以上はストック対応なし。

■段部止め輪溝タイプ

Type	¥ NSFRX (S45C相当・表面処理なし)										¥ SFRX (S45C相当・四三酸化鉄皮膜)									
D	最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0			最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0		
6	510	570	640	770	1,080	—	—	—	—	—	530	590	660	790	1,110	—	—	—	—	—
8	510	570	640	770	1,080	1,230	—	—	—	—	530	590	660	790	1,110	1,260	—	—	—	—
10	510	570	640	770	1,080	1,230	1,480	—	—	—	530	590	660	790	1,110	1,260	1,520	—	—	—
12	570	670	720	820	1,130	1,280	1,860	—	—	—	600	700	750	860	1,180	1,340	1,940	—	—	—
13	620	710	760	870	1,200	1,380	1,980	—	—	—	650	740	800	910	1,260	1,440	2,070	—	—	—
15	630	720	770	890	1,220	1,400	2,010	2,350	—	—	660	750	810	930	1,280	1,460	2,100	2,450	—	—
16	680	850	890	1,070	1,410	1,580	2,160	2,540	—	—	730	910	950	1,140	1,510	1,690	2,300	2,710	—	—
17	690	860	900	1,090	1,430	1,600	2,190	2,570	—	—	740	920	960	1,160	1,530	1,710	2,330	2,740	—	—
18	690	860	900	1,090	1,580	1,780	2,390	2,840	—	—	740	920	960	1,160	1,690	1,900	2,550	3,030	—	—
20	780	980	1,030	1,140	1,580	1,780	2,390	2,840	—	—	840	1,050	1,100	1,220	1,690	1,900	2,550	3,030	—	—
22	930	1,150	1,310	1,440	1,790	2,190	2,970	3,500	—	—	990	1,230	1,400	1,540	1,910	2,340	3,160	3,730	—	—
25	1,030	1,290	1,460	1,610	2,010	2,450	3,300	3,930	—	—	1,100	1,380	1,560	1,720	2,140	2,610	3,520	4,190	—	—
30	1,230	1,480	1,700	1,870	2,460	2,880	3,820	4,860	—	—	1,340	1,610	1,850	2,040	2,680	3,140	4,160	5,290	—	—
35	1,710	2,230	2,470	2,750	3,680	4,190	5,600	7,100	—	—	1,860	2,430	2,690	2,990	4,010	4,560	6,090	7,720	—	—
40	2,050	2,680	2,970	3,300	4,420	5,030	6,720	8,520	—	—	2,230	2,920	3,230	3,590	4,810	5,470	7,310	9,270	—	—
50	2,650	3,490	3,860	4,300	5,760	6,550	8,750	11,090	—	—	2,890	3,800	4,200	4,680	6,270	7,120	9,520	12,060	—	—

Type	¥ PSFRX (S45C相当・無電解ニッケルメッキ)										¥ SSFRX (SUS304)									
D	最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0			最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0		
6	590	700	780	900	1,230	—	—	—	—	—	650	710	840	940	1,400	—	—	—	—	—
8	590	700	780	900	1,230	1,410	—	—	—	—	650	710	840	940	1,400	1,620	—	—	—	—
10	590	700	780	900	1,230	1,410	1,590	—	—	—	650	710	840	940	1,400	1,620	1,800	—	—	—
12	660	810	820	970	1,300	1,480	2,090	—	—	—	750	890	950	1,070	1,540	1,770	2,240	—	—	—
13	700	860	890	1,030	1,390	1,660	2,360	—	—	—	—	—	—	—	—	—	—	—	—	—
15	730	890	900	1,050	1,410	1,680	2,390	2,680	—	—	940	1,100	1,130	1,450	2,110	2,330	2,950	3,720	—	—
16	890	1,130	1,170	1,320	1,610	1,930	2,620	3,510	—	—	—	—	—	—	—	—	—	—	—	—
17	900	1,140	1,170	1,330	1,630	1,950	2,650	3,540	—	—	970	1,220	1,250	1,340	2,160	2,390	3,340	3,820	—	—
18	900	1,140	1,170	1,450	1,960	2,230	2,930	4,410	—	—	—	—	—	—	—	—	—	—	—	—
20	1,120	1,390	1,570	1,820	2,370	2,790	3,820	5,300	—	—	1,160	1,460	1,580	1,880	2,490	3,320	4,970	6,640	—	—
22	1,320	1,640	1,830	2,020	2,640	3,020	3,950	5,500	—	—	—	—	—	—	—	—	—	—	—	—
25	1,430	1,890	2,100	2,320	3,190	4,250	6,350	8,440	—	—	1,590	1,900	2,140	2,440	3,240	4,330	6,470	8,610	—	—
30	2,000	2,570	2,880	3,270	4,230	5,610	8,120	10,830	—	—	2,220	2,680	3,000	3,410	4,390	5,830	8,410	11,230	—	—
35	3,240	3,740	4,120	4,770	6,150	8,200	11,860	15,780	—	—	3,380	4,060	4,560	4,940	6,400	8,550	12,330	16,380	—	—
40	4,060	4,120	4,530	5,250	6,770	9,040	13,070	17,370	—	—	4,390	4,620	5,020	5,430	7,050	9,410	13,570	18,020	—	—
50	4,470	4,520	4,990	5,760	7,450	9,940	18,720	24,060	—	—	4,690	5,090	5,540	5,990	7,750	10,350	19,280	24,440	—	—

■両端止め輪溝タイプ

Type	¥ NSFRZ (S45C相当・表面処理なし)										¥ SFRZ (S45C相当・四三酸化鉄皮膜)									
D	最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0			最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 798.0		
6	580	650	760	830	1,230	—	—	—	—	—	600	670	780	850	1,260	—	—	—	—	—
8	580	650	760	830	1,230	1,400	—	—	—	—	600	670	780	850	1,260	1,430	—	—	—	—
10	580	650	760	830	1,230	1,470	1,690	—	—	—	600	670	780	850	1,260	1,500	1,730	—	—	—
12	650	760	830	880	1,270	1,530	2,110	—	—	—	680	800	870	920	1,330	1,600	2,200	—	—	—
13	710	810	890	950	1,370	1,650	2,260	—	—	—	740	850	930	990	1,430	1,720	2,360	—	—	—
15	710	820	900	960	1,390	1,670	2,290	2,660	—	—	740	860	940	1,000	1,450	1,740	2,390	2,780	—	—
16	770	1,010	1,040	1,160	1,640	1,810	2,450	2,890	—	—	820	1,080	1,110	1,240	1,750	1,930	2,610	3,080	—	—
17	780	1,010	1,050	1,250	1,660	1,830	2,480	2,920	—	—	830	1,080	1,120	1,330	1,770	1,950	2,640	3,110	—	—
18	780	1,010	1,050	1,250	1,780	2,000	2,680	3,200	—	—	830	1,080	1,120	1,330	1,900	2,130	2,860	3,410	—	—
20	800	1,100	1,140	1,970	2,710	3,040	4,080	4,850	—	—	860	1,180	1,220	2,100	2,890	3,240	4,350	5,160	—	—
22	1,030	1,290	1,460	2,270	2,860	3,540	4,680	5,220	—	—	1,100	1,380	1,560	2,420	3,050	3,770	4,980	5,560	—	—
25	1,390	1,660	1,880	2,470	3,150	3,780	4,790	5,760	—	—	1,480	1,770	2,010	2,630	3,360	4,030	5,100	6,130	—	—
30	1,930	2,100	2,240	2,700	3,420	4,060	4,770	6,280	—	—	2,100	2,290	2,440	2,940	3,720	4,420	5,190	6,830	—	—
35	2,610	3,160	3,280	3,640	4,160	4,750	6,990	9,120	—	—	2,840	3,440	3,570	3,960	4,530	5,170	7,600	9,920	—	—
40	3,130	3,800	3,940	4,370	5,000	5,710	8,380	10,940	—	—	3,410	4,140	4,290	4,750	5,440	6,210	9,110	11,900	—	—
50	4,410	5,320	5,530	6,110	7,010	7,970	11,730	15,320	—	—	4,800	5,790	6,020	6,650	7,620	8,670	12,750	16,660	—	—

Type	¥ PSFRZ (S45C相当・無電解ニッケルメッキ)									¥ SSFRZ (SUS304)								
D	最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 796.0		最短L 50.0	L50.1 100.0	L100.1 150.0	L150.1 200.0	L200.1 300.0	L300.1 400.0	L400.1 600.0	L600.1 796.0	
6	670	750	890	960	1,350	—	—	—	—	720	810	950	1,060	1,600	—	—	—	
8	670	750	890	960	1,350	1,590	—	—	—	720	810	950	1,060	1,600	1,840	—	—	
10	670	750	890	960	1,350	1,590	1,810	—	—	720	810	950	1,060	1,600	1,840	2,040	—	
12	750	880	940	1,040	1,430	1,680	2,370	—	—	840	1,010	1,080	1,220	1,750	2,020	2,530	—	
13	800	940	1,010	1,100	1,570	1,890	2,670	—	—	—	—	—	—	—	—	—	—	
15	810	950	1,020	1,120	1,590	1,910	2,700	3,040	—	1,060	1,240	1,290	1,430	2,060	2,290	2,890	3,650	
16	980	1,210	1,330	1,470	1,920	2,200	2,980	3,990	—	—	—	—	—	—	—	—	—	
17	990	1,220	1,340	1,490	1,940	2,220	3,010	4,020	—	1,110	1,390	1,430	1,520	2,220	2,590	3,620	4,140	
18	1,130	1,400	1,480	1,650	2,200	2,520	3,290	4,970	—	—	—	—	—	—	—	—	—	
20	1,850	2,020	2,220	2,640	3,120	3,560	4,750	7,200	—	1,970	2,120	2,240	2,690	3,310	4,160	6,250	8,110	
22	1,910	2,370	2,640	2,930	3,830	4,360	5,700	7,560	—	—	—	—	—	—	—	—	—	
25	2,380	2,720	3,030	3,380	3,960	5,290	7,960	10,630	—	2,440	2,900	3,140	3,390	4,000	5,460	8,040	10,700	
30	3,490	4,180	4,480	4,890	5,990	6,980	10,030	13,410	—	3,630	4,350	4,520	5,160	6,220	7,340	10,470	13,830	
35	5,420	6,110	6,730	7,390	8,400	10,110	14,810	19,460	—	5,760	6,320	6,800	7,750	8,530	10,510	15,200	20,200	
40	6,500	7,340	8,080	8,880	10,090	12,150	17,760	23,350	—	6,980	7,590	8,160	9,280	10,240	12,610	18,240	24,250	
50	8,450	9,520	10,600	11,520	13,130	15,800	23,090	30,350	—	9,420	9,880	10,630	12,220	13,310	16,400	23,760	31,520	