


特殊鋼フリープレート 価格表

-SKS3/SKD11/DC53-



Price 価格 (例)PSKD11FQM-255-165-18のとき
 A寸法 × 面積単価 = 価格(1円単位は切捨)
 255 × 45.1 = 11,500(円)

数量スライド価格 (1円単位切り捨て) P127

数量区分	標準対応			個別対応 大口
	小口	15~20	21~	
数量	1~9	10~14	15~20	21~
値引率	基準単価	5%	10%	お見積り

◎表示数量超えはWOSIにてご確認ください。

SKD11

型式	A	B	T	5~7	7.5~9	9.5~11	11.5~13	13.5~16	16.5~20	20.5~22	22.5~25	25.5~28	28.5~30	30.5~35
PSKD11F□	20 ~50	20~25	20	A×25.8	A×20.7	A×19.8	A×20.7	A×22.4	A×24.1	A×25.8	A×27.5	A×28.4	A×30.1	—
	50.5~75			A×25.8	A×20.7	A×19.8	A×19.8	A×21.6	A×23.3	A×25	A×26.7	A×27.5	A×29.2	—
	75.5~100			A×25	A×21.6	A×18.9	A×19.8	A×21.6	A×23.3	A×25	A×26.7	A×27.5	A×29.2	—
	100.5~250			—	—	A×18.1	A×19.8	A×20.7	A×22.4	A×24.1	A×25.8	A×27.5	A×28.4	—
	25.5~50			A×25.8	A×20.7	A×18.9	A×19.8	A×21.6	A×23.3	A×25	A×26.7	A×27.5	A×29.2	—
	50.5~75	A×25.8	A×20.7	A×18.9	A×19.8	A×21.6	A×23.3	A×25	A×26.7	A×27.5	A×29.2	—		
	75.5~100	A×25	A×21.6	A×18.1	A×19.8	A×20.7	A×22.4	A×24.1	A×25.8	A×27.5	A×28.4	—		
	100.5~200	—	A×23.3	A×17.2	A×18.9	A×19.8	A×21.6	A×23.3	A×25	A×26.7	A×27.5	—		
	200.5~500	—	—	A×23.3	A×25	A×26.7	A×27.5	A×29.2	A×30.9	A×32.7	A×34.4	—		
	40.5~50	A×26.7	A×25	A×24.1	A×23.3	A×25	A×27.5	A×27.5	A×31	A×35.3	A×38.7	—		
	50.5~75	A×26.7	A×25	A×24.1	A×18.9	A×19.8	A×22.4	A×23.3	A×26.7	A×31	A×34.4	—		
	75.5~100	A×25.8	A×24.1	A×19.8	A×18.9	A×19.8	A×22.4	A×23.3	A×26.7	A×31	A×34.4	—		
	100.5~200	—	A×23.3	A×18.1	A×18.9	A×19.8	A×21.6	A×23.3	A×26.7	A×31	A×34.4	—		
	200.5~500	—	—	A×18.9	A×18.1	A×18.9	A×19.8	A×21.6	A×23.3	—	—	—		
	60.5~75	A×27.5	A×26.7	A×25	A×24.1	A×25.8	A×27.5	A×28.4	A×31.9	A×35.3	A×38.7	A×38.7		
	75.5~100	A×27.5	A×26.7	A×25	A×19.8	A×19.8	A×23.3	A×25	A×25.8	A×31	A×31	A×33.6		
	100.5~200	—	A×24.1	A×19.8	A×18.1	A×19.8	A×22.4	A×23.3	A×25	A×29.2	A×31	A×33.6		
	200.5~500	—	—	A×18.9	A×17.2	A×19.8	A×19.8	A×21.6	A×23.3	A×26.7	A×27.5	A×32.7		
	80.5~100	A×29.2	A×27.5	A×25.8	A×25	A×26.7	A×31	A×32.7	A×35.3	A×37	A×40.4	A×43		
	100.5~200	—	A×18.9	A×21.6	A×19.8	A×22.4	A×25.8	A×27.5	A×28.4	A×32.7	A×35.3	A×38.7		
200.5~500	—	—	A×19.8	A×19.8	A×21.6	A×25	A×25.8	A×27.5	A×31.8	A×35.3	A×37			
100.5~125	—	A×31	A×28.4	A×27.5	A×32.7	A×35.3	A×37	A×41.3	A×45.6	A×45.6	A×50.8			
125.5~200	—	A×27.5	A×23.3	A×22.4	A×28.4	A×31.9	A×35.3	A×38.7	A×41.3	A×41.3	A×45.6			
200.5~500	—	—	A×22.4	A×21.6	A×25	A×27.5	A×29.2	A×32.7	A×37	A×37.8	A×43.9			
125.5~200	—	A×37	A×35.3	A×35.3	A×40.4	A×43	A×45.6	A×52.5	A×51.6	A×60.1				
200.5~500	—	—	A×30.1	A×28.4	A×30.9	A×35.3	A×38.7	A×43	A×49.8	A×49.8	A×57.6			
150.5~200	—	A×37.8	A×34.4	A×33.6	A×35.3	A×39.5	A×42.2	A×47.3	A×49.8	A×53.3	A×61.9			
200.5~500	—	—	A×27.5	A×27.5	A×31.8	A×37	A×39.5	A×46.4	A×48.1	A×51.5	A×61.8			
160.5~200	—	A×45.6	A×43	A×43	A×43.9	A×48.1	A×50.8	A×60.1	A×62.8	A×70.4	A×72.2			
200.5~500	—	—	—	A×38.7	A×41.2	A×45.6	A×47.3	A×56.7	A×60.1	A×64.5	A×72.1			
200.5~500	—	—	—	A×41.2	A×43.9	A×53.3	A×55.9	A×72.1	A×72.1	A×73.8	A×86.8			
250.5~500	—	—	—	A×52.4	A×56.7	A×63.5	A×69.6	A×85	A×89.3	A×99.6	A×105.6			

型式	A	B	T	5~7	7.5~9	9.5~11	11.5~13	13.5~16	16.5~20	20.5~22	22.5~25	25.5~28	28.5~30	30.5~35
PSKD11R□	20 ~50	20~25	20	A×37.4	A×29.3	A×28.3	A×29.3	A×31.4	A×33.4	A×36.4	A×38.4	A×39.4	A×42.5	—
	50.5~75			A×37.4	A×29.3	A×26.3	A×27.3	A×30.3	A×32.4	A×35.4	A×37.4	A×38.4	A×40.4	—
	75.5~100			A×35.4	A×30.3	A×26.3	A×27.3	A×30.3	A×32.4	A×35.4	A×37.4	A×38.4	A×40.4	—
	100.5~250			—	—	A×25.3	A×28.3	A×29.3	A×31.4	A×33.4	A×36.4	A×38.4	A×39.4	—
	25.5~50			A×36.4	A×29.3	A×26.3	A×27.3	A×29.3	A×32.4	A×34.4	A×36.4	A×37.4	A×39.4	—
	50.5~75	A×36.4	A×29.3	A×26.3	A×27.3	A×30.3	A×32.4	A×34.4	A×36.4	A×37.4	A×39.4	—		
	75.5~100	A×35.4	A×30.3	A×25.3	A×27.3	A×28.3	A×30.3	A×33.4	A×35.4	A×37.4	A×38.4	—		
	100.5~200	—	A×32.4	A×23.3	A×26.3	A×27.3	A×29.3	A×32.4	A×34.4	A×36.4	A×37.4	—		
	200.5~500	—	—	A×32.4	A×34.4	A×37.4	A×38.4	A×40.4	A×43.5	A×45.5	A×47.5	—		
	40.5~50	A×37.4	A×34.4	A×33.4	A×31.4	A×34.4	A×37.4	A×37.4	A×41.5	A×47.5	A×52.6	—		
	50.5~75	A×37.4	A×34.4	A×33.4	A×25.3	A×26.3	A×30.3	A×31.4	A×35.4	A×41.5	A×46.5	—		
	75.5~100	A×36.4	A×33.4	A×27.3	A×25.3	A×26.3	A×30.3	A×31.4	A×35.4	A×41.5	A×46.5	—		
	100.5~200	—	A×32.4	A×25.3	A×24.3	A×25.3	A×26.3	A×28.3	A×30.3	—	—	—		
	200.5~500	—	—	A×25.3	A×24.3	A×25.3	A×26.3	A×28.3	A×30.3	—	—	—		
	60.5~75	A×38.4	A×36.4	A×33.4	A×32.4	A×34.4	A×36.4	A×37.4	A×42.5	A×46.5	A×46.5	A×50.5		
	75.5~100	A×38.4	A×36.4	A×33.4	A×26.3	A×34.4	A×36.4	A×37.4	A×40.4	A×40.4	A×40.4	A×43.5		
	100.5~200	—	A×33.4	A×26.3	A×23.3	A×26.3	A×29.3	A×30.3	A×32.4	A×38.4	A×40.4	A×43.5		
	200.5~500	—	—	A×25.3	A×22.3	A×26.3	A×25.3	A×27.3	A×30.3	A×34.4	A×35.4	A×42.4		
	80.5~100	A×40.4	A×37.4	A×34.4	A×32.4	A×35.4	A×40.4	A×43.5	A×48.5	A×52.6	A×52.6	A×55.6		
	100.5~200	—	A×25.3	A×28.3	A×25.3	A×29.3	A×33.4	A×35.4	A×36.4	A×42.5	A×45.5	A×49.5		
200.5~500	—	—	A×25.3	A×25.3	A×32.4	A×35.4	A×35.4	A×40.4	A×45.5	A×45.5	A×47.5			
100.5~125	—	A×41.5	A×37.4	A×35.4	A×43.5	A×46.5	A×48.5	A×53.6	A×59.6	A×58.6	A×65.7			
125.5~200	—	A×36.4	A×30.3	A×28.3	A×33.4	A×36.4	A×40.4	A×45.5	A×49.5	A×52.6	A×58.6			
200.5~500	—	—	A×28.3	A×27.3	A×32.4	A×35.4	A×37.4	A×41.4	A×47.5	A×48.5	A×55.6			
125.5~200	—	A×49.5	A×46.5	A×46.5	A×46.5	A×52.6	A×55.6	A×58.6	A×67.7	A×66.7	A×77.8			
200.5~500	—	—	A×39.4	A×36.4	A×46.5	A×45.5	A×49.5	A×55.6	A×64.7	A×63.6	A×73.7			
150.5~200	—	A×50.5	A×45.5	A×43.5	A×46.5	A×51.6	A×54.6	A×60.6	A×63.7	A×68.7	A×79.8			
200.5~500	—	—	A×35.4	A×34.4	A×41.4	A×47.5	A×50.5	A×59.6	A×61.6	A×65.7	A×79.8			
160.5~200	—	A×60.6	A×56.6	A×55.6	A×62.7	A×65.7	A×77.8	A×80.8	A×90.9	A×90.9	A×92			
200.5~500	—	—	—	A×49.5	A×53.6	A×58.6	A×60.6	A×72.7	A×76.8	A×82.8	A×91.9			
200.5~500	—	—	—	A×51.5	A×55.6	A×67.7	A×70.7	A×92.9	A×91.9	A×93.9	A×110.1			
250.5~500	—	—	—	A×66.7	A×72.7	A×80.8	A×88.9	A×110.1	A×114.1	A×128.3	A×134.3			

DC53

型式	A	B	T	5~7	7.5~9	9.5~11	11.5~13	13.5~16	16.5~20	20.5~22	22.5~25	25.5~28	28.5~30	30.5~35
PDC53F□	20 ~50	20~25	20	A×29.4	A×23.6	A×22.6	A×23.6	A×25.5	A×27.5	A×29.4	A×31.4	A×32.4	A×34.4	—
	50.5~75			A×29.4	A×23.6	A×21.6	A×22.6	A×24.6	A×26.5	A×28.4	A×30.5	A×31.4	A×33.4	—
	75.5~100			A×28.4	A×24.6	A×21.6	A×22.6	A×24.6	A×26.5	A×28.4	A×30.5	A×31.4	A×33.4	—
	100.5~250			—	—	A×20.7	A×22.6	A×23.6	A×25.5	A×27.5	A×29.4	A×31.4	A×32.4	—
	25.5~50			A×29.4	A×23.6	A×21.6	A×22.6	A×24.6	A×26.5	A×28.4	A×30.5	A×31.4	A×33.4	—
	50.5~75	A×29.4	A×23.6	A×21.6	A×22.6	A×24.6	A×26.5	A×28.4	A×30.5	A×31.4	A×33.4	—		
	75.5~100	A×28.4	A×24.6	A×20.7	A×22.6	A×23.6	A×25.5	A×27.5	A×29.4	A×31.4	A×32.4	—		
	100.5~200	—	A×26.5	A×19.6	A×21.6	A×22.6	A×24.6	A×26.5	A×28.4	A×30.5	A×31.4	—		
	200.5~500	—	—	A×26.5	A×28.4	A×30.4	A×31.3	A×33.4	A×35.3	A×37.3	A×39.2	—		
	40.5~50	A×30.5	A×28.4	A×27.5	A×26.5	A×28.4	A×31.4	A×31.4	A×35.3	A×40.2	A×44.2	—		
	50.5~75	A×30.5	A×28.4	A×27.5	A×21.6	A×22.6	A×25.5	A×26.5	A×30.5	A×35.3	A×39.2	—		
	75.5~100	A×29.4	A×27.5	A×22.6	A×21.6	A×22.6	A×25.5	A×26.5	A×30.5	A×35.3	A×39.2	—		
	100.5~200	—	A×26.5	A×21.6	A×20.7	A×21.6	A×22.6	A×24.6	A×26.5	A×31.4	A×35.3	—		
	200.5~500	—	—	A×21.6	A×20.6	A×21.6	A×22.6	A×24.6	A×26.5	—	—	—		
	60.5~75	A×31.4	A×30.5	A×28.4	A×27.5	A×29.4	A×31.4	A×32.4	A×36.3	A×40.2	A×40.2	A×44.2		
	75.5~100	A×31.4	A×30.5	A×28.4	A×22.6	A×22.6	A×26.5	A×28.4	A×29.4	A×35.3	A×35.3	A×42.2		
	100.5~200	—	A×27.5	A×22.6	A×20.7	A×22.6	A×25.5	A×28.4	A×33.4	A×33.4	A×35.3	A×42.2		
	200.5~500	—	—	A×21.6	A×19.6	A×22.6	A×22.6	A×26.5	A×28.4	A×30.4	A×32.4	A×39.2		
	80.5~100	A×33.4	A×31.4	A×29.4	A×28.4	A×30.5	A×35.3	A×37.3	A×40.2	A×45.1	A×46.1	A×49		
	100.5~200	—	A×31.4	A×24.6	A×22.6	A×25.5	A×29.4	A×31.4	A×36.3	A×37.3	A×42.2	A×46.1		
200.5~500	—	—	A×22.6	A×22.6	A×24.6	A×28.4	A×30.4	A×35.3	A×36.3	A×40.2	A×44.2			
100.5~125	—	A×35.3	A×32.4	A×31.4	A×37.3	A×40.2	A×42.2	A×47.1	A×52	A×52	A×63.8			
125.5~200														