


# ベアリングホルダセット

-インローダブル止め輪なし フリー指定タイプ-



◎類似寸法は加工部品Cナビ <http://cp.misumi.jp/10-013/>

◎CADデータフォルダ名: 14\_Bearings\_with\_Holder



| Type       | ベアリング品番 | シール           | 指定1mm単位 |       | d  | DH7 | 許容差    | B   | H   | W   | T | dh | D <sub>1g7</sub> | 許容差    | P.C.D. | K   | A   | F  | d <sub>1</sub> | d <sub>2</sub> | H <sub>1</sub> |
|------------|---------|---------------|---------|-------|----|-----|--------|-----|-----|-----|---|----|------------------|--------|--------|-----|-----|----|----------------|----------------|----------------|
|            |         |               | L       | S     |    |     |        |     |     |     |   |    |                  |        |        |     |     |    |                |                |                |
|            | 623     |               | 20~40   | 5~28  | 3  | 10  | +0.015 | 4   | 33  | 16  | 7 | 7  | 14               | -0.006 | 24     | 27  | 24  |    | 6.5            | 3.5            | 3.1            |
|            | 624     |               | 20~40   | 5~28  | 4  | 13  |        | 5   | 35  | 18  |   | 9  | 17               | -0.024 | 26     | 28  | 26  |    |                |                |                |
|            | 605     |               | 20~40   | 5~27  | 5  | 14  | +0.018 | 5   | 38  | 20  |   | 10 | 18               |        | 28     | 30  | 28  |    |                |                |                |
|            | 625     |               | 30~40   | 10~22 |    | 16  | 0      | 5   | 40  | 22  |   | 12 | 20               |        | 30     | 31  | 30  |    | 8              | 4.5            | 4.1            |
|            | 606     |               | 20~40   | 5~27  | 6  | 17  |        | 6   | 41  | 23  |   | 13 | 21               | -0.007 | 31     | 32  | 31  |    |                |                |                |
|            | 626     |               | 30~50   | 10~32 |    | 19  | +0.021 | 6   | 44  | 25  |   | 15 | 24               | -0.028 | 34     | 34  | 34  |    |                |                |                |
|            | 678     |               | 20~40   | 5~27  | 12 | 12  | +0.018 | 3.5 | 35  | 18  |   | 10 | 16               | -0.028 | 26     | 28  | 26  |    | 6.5            | 3.5            | 3.1            |
|            | 698     |               | 25~50   | 5~37  | 8  | 19  | +0.021 | 6   | 44  | 25  |   | 15 | 24               |        | 34     | 34  | 34  |    |                |                |                |
|            | 608     |               | 20~50   | 5~37  | 22 | 22  | 0      | 7   | 47  | 29  |   | 18 | 27               |        | 37     | 36  | 37  |    |                |                |                |
|            | 628     |               | 30~50   | 10~32 | 24 | 24  | 0      | 8   | 50  | 32  |   | 20 | 30               | -0.007 | 40     | 37  | 40  |    |                |                |                |
|            | 6700    |               | 20~40   | 5~27  | 15 | 15  | +0.018 | 4   | 40  | 22  |   | 12 | 19               | -0.028 | 30     | 31  | 30  |    |                |                |                |
|            | 6800    |               | 20~40   | 5~27  | 19 | 19  |        | 5   | 44  | 25  |   | 15 | 24               |        | 34     | 34  | 34  |    |                |                |                |
|            | 6900    |               | 20~60   | 5~47  | 10 | 22  | +0.021 | 6   | 47  | 29  |   | 19 | 27               |        | 37     | 36  | 37  |    | 8              | 4.5            | 4.1            |
|            | 6000    |               | 30~60   | 10~42 |    | 26  | 0      | 8   | 52  | 34  |   | 22 | 32               | -0.009 | 42     | 39  | 42  |    |                |                |                |
|            | 6200    |               | 40~60   | 15~37 |    | 30  |        | 9   | 56  | 38  |   | 24 | 36               | -0.034 | 46     | 42  | 46  |    | 8              | 4.5            | 4.1            |
| (ラウンドタイプ)  | 6701    |               | 20~40   | 5~27  | 21 | 21  | +0.018 | 4   | 44  | 25  |   | 15 | 23               |        | 34     | 34  | 34  |    |                |                |                |
|            | 6801    |               | 25~50   | 5~37  | 18 | 18  |        | 5   | 47  | 29  |   | 17 | 26               | -0.007 | 37     | 36  | 37  |    |                |                |                |
|            | 6901    |               | 30~60   | 10~42 | 12 | 24  | +0.021 | 6   | 50  | 31  |   | 21 | 30               | -0.028 | 40     | 38  | 40  |    |                |                |                |
| BGFRYB     | 6001    |               | 30~60   | 10~42 | 28 | 28  |        | 8   | 54  | 36  |   | 24 | 34               | -0.009 | 44     | 40  | 44  |    |                |                |                |
| BGFRY      | 6201    |               | 40~70   | 15~47 |    | 32  | +0.025 | 10  | 58  | 40  |   | 26 | 38               | -0.034 | 48     | 43  | 48  |    |                |                |                |
| BAFRY      | 6702    | 両シールド         | 25~60   | 10~42 | 21 | 21  | +0.021 | 4   | 47  | 29  |   | 18 | 26               | -0.007 | 37     | 36  | 37  |    |                |                |                |
| SBGFRY     | 6802    |               | 25~60   | 10~42 | 24 | 24  | 0      | 5   | 50  | 32  |   | 20 | 30               | -0.028 | 40     | 37  | 40  |    |                |                |                |
| (スクエアタイプ)  | 6902    | *VV 非接触 ゴムシール | 30~70   | 10~50 | 15 | 28  |        | 7   | 59  | 37  |   | 25 | 35               |        | 47     | 45  | 47  |    |                |                |                |
|            | 6002    |               | 40~70   | 15~45 |    | 32  | +0.025 | 9   | 62  | 40  |   | 28 | 38               |        | 50     | 46  | 50  |    | 9.5            | 5.5            | 5.1            |
| BGFSYB     | 6202    |               | 40~70   | 15~45 |    | 35  | 0      | 11  | 66  | 44  |   | 29 | 42               |        | 54     | 49  | 54  |    |                |                |                |
| BGFSY      | 6803    |               | 25~60   | 10~40 |    | 26  | +0.021 | 5   | 52  | 34  |   | 22 | 32               |        | 42     | 39  | 42  |    | 8              | 4.5            | 4.1            |
| BAFSY      | 6903    | DD 接触 ゴムシール   | 40~70   | 15~45 |    | 30  | 0      | 7   | 60  | 38  |   | 27 | 36               |        | 48     | 46  | 48  |    |                |                |                |
| (コンパクトタイプ) | 6003    |               | 40~70   | 15~45 |    | 35  | +0.025 | 10  | 66  | 44  |   | 31 | 42               | -0.009 | 54     | 50  | 54  |    | 9.5            | 5.5            | 5.1            |
| BGFCYB     | 6203    |               | 50~70   | 20~40 |    | 40  | 0      | 12  | 72  | 50  |   | 34 | 48               | -0.034 | 60     | 54  | 60  |    |                |                |                |
| BGFCY      | 6704    |               | 30~70   | 10~50 |    | 27  | +0.021 | 4   | 59  | 35  |   | 23 | 33               |        | 47     | 45  | 41  | 23 | 8              | 4.5            | 4.1            |
| BAFCY      | 6804    |               | 35~70   | 10~50 |    | 32  |        | 7   | 62  | 40  |   | 28 | 38               |        | 50     | 46  | 44  | 24 | 9.5            | 5.5            | 5.1            |
|            | 6904    |               | 45~70   | 15~44 |    | 37  |        | 9   | 72  | 47  |   | 34 | 45               |        | 59     | 54  | 54  | 24 |                |                |                |
|            | 6004    |               | 55~80   | 20~49 |    | 42  |        | 12  | 77  | 54  |   | 36 | 50               |        | 64     | 59  | 56  | 32 |                |                |                |
|            | 6204    |               | 55~80   | 20~49 |    | 47  | +0.025 | 14  | 81  | 58  |   | 40 | 54               | -0.018 | 68     | 62  | 59  | 34 | 11             | 6.6            | 6.1            |
|            | 6805    |               | 35~70   | 15~44 |    | 37  |        | 7   | 72  | 47  |   | 34 | 45               | -0.009 | 59     | 54  | 54  | 24 |                |                |                |
|            | 6905    |               | 35~70   | 15~44 |    | 42  |        | 9   | 77  | 54  |   | 36 | 50               | -0.034 | 64     | 59  | 55  | 32 |                |                |                |
|            | 6005    |               | 55~80   | 20~47 |    | 47  |        | 12  | 88  | 58  |   | 41 | 54               | -0.010 | 72     | 67  | 63  | 36 | 14             | 9              | 8.1            |
|            | 6205    |               | 55~80   | 20~47 |    | 52  | +0.030 | 15  | 94  | 64  |   | 45 | 60               | -0.040 | 78     | 72  | 68  | 39 |                |                |                |
|            | 6806    |               | 35~70   | 15~42 |    | 42  | +0.025 | 7   | 77  | 54  |   | 36 | 50               | -0.034 | 64     | 59  | 56  | 32 | 11             | 6.6            | 6.1            |
|            | 6906    |               | 35~70   | 15~42 |    | 47  | 0      | 9   | 88  | 58  |   | 41 | 54               |        | 72     | 67  | 62  | 36 |                |                |                |
|            | 6006    |               | 55~80   | 20~47 |    | 55  |        | 13  | 96  | 66  |   | 48 | 62               | -0.010 | 80     | 73  | 70  | 40 | 14             | 9              | 8.1            |
|            | 6206    |               | 55~120  | 20~87 |    | 62  |        | 16  | 104 | 74  |   | 55 | 70               | -0.040 | 88     | 79  | 77  | 44 |                |                |                |
|            | 6007    |               | 55~120  | 20~87 |    | 62  |        | 14  | 104 | 74  |   | 55 | 70               |        | 88     | 79  | 75  | 44 |                |                |                |
|            | 6207    |               | 55~120  | 20~87 |    | 72  | +0.030 | 17  | 126 | 88  |   | 64 | 84               | -0.012 | 105    | 95  | 92  | 51 | 17.5           | 11             | 11             |
|            | 6008    |               | 65~120  | 25~82 |    | 68  |        | 15  | 114 | 82  |   | 60 | 78               | -0.010 | 96     | 86  | 80  | 54 | 14             | 9              | 8.1            |
|            | 6208    |               | 65~120  | 25~82 |    | 80  |        | 18  | 134 | 96  |   | 74 | 92               | -0.012 | 113    | 102 | 98  | 56 |                |                |                |
|            | 6010    |               | 65~120  | 25~82 |    | 80  |        | 16  | 134 | 96  |   | 74 | 92               | -0.012 | 113    | —   | 98  | 56 | 17.5           | 11             | 11             |
|            | 6210    | 両シールド         | 70~120  | 25~82 |    | 90  | +0.035 | 20  | 147 | 110 |   | 83 | 106              | -0.047 | 126    | —   | 104 | 72 |                |                |                |

◎適用サイズは価格表でご確認ください。 ◎\*VV(非接触ゴムシール)は67番台・623番・624番・605番・606番は選択できません。



Order 注文例  
 型式: [Type] [ベアリング] [シール] - L - S  
 BAFCY 608 ZZ - 47 - S18  
 BGFRY 6200 VV - 40  
 Sを指定されない場合は最小のS寸法となります。例の場合 S=15



Delivery 出荷日: 3 日発送  
 ストック A 200円/1本 P90



Price 価格  
 数量スライド価格 (◎1円未満切り捨て) P89  

|     |      |       |       |       |       |        |
|-----|------|-------|-------|-------|-------|--------|
| 数量  | 1~9  | 10~14 | 15~19 | 20~24 | 25~50 | 51以上   |
| 値引率 | 標準単価 | 5%    | 10%   | 15%   | 20%   | 出荷日・価格 |
| 出荷日 | 通常   | 通常    | 通常    | +5日   | 共に見積  |        |

| ベアリング品番 | シール | ¥標準単価   |       |       |        |         |       |       |          |       |       |
|---------|-----|---------|-------|-------|--------|---------|-------|-------|----------|-------|-------|
|         |     | ラウンドタイプ |       |       |        | スクエアタイプ |       |       | コンパクトタイプ |       |       |
|         |     | BGFRYB  | BGFRY | BAFRY | SBGFRY | BGFSYB  | BGFSY | BAFSY | BGFCYB   | BGFCY | BAFCY |
| 623     |     | 3,300   | 3,340 | 3,850 | —      | 3,700   | 3,750 | 4,330 | 3,570    | 3,630 | 4,160 |
| 624     |     | 3,330   | 3,390 | 3,890 | —      | 3,770   | 3,820 | 4,400 | 3,670    | 3,720 | 4,220 |
| 605     |     | 3,380   | 3,430 | 3,950 | —      | 3,840   | 3,900 | 4,460 | 3,760    | 3,820 | 4,290 |
| 625     |     | 3,500   | 3,550 | 4,090 | —      | 3,910   | 3,970 | 4,620 | 3,820    | 3,880 | 4,460 |
| 606     |     | 3,570   | 3,630 | 4,170 | 6,890  | 4,010   | 4,070 | 4,660 | 3,870    | 3,910 | 4,520 |
| 626     |     | 3,690   | 3,730 | 4,350 | 7,090  | 4,130   | 4,200 | 4,890 | 3,980    | 4,040 | 4,730 |
| 678     |     | 4,530   | 4,610 | 5,470 | 8,740  | 5,110   | 5,180 | 6,180 | 4,920    | 5,000 | 5,950 |
| 698     |     | 4,330   | 4,410 | 5,240 | 8,360  | 4,880   | 4,950 | 5,910 | 4,710    | 4,790 | 5,690 |
| 608     |     | 3,730   | 3,790 | 4,430 | 7,180  | 4,230   | 4,290 | 4,940 | 4,080    | 4,130 | 4,800 |
| 628     |     | 3,940   | 4,010 | 4,760 | 7,600  | 4,440   | 4,500 | 5,370 | 4,280    | 4,350 | 5,170 |
| 6700    |     | 4,950   | 5,000 | 5,800 | 8,200  | 5,670   | 5,780 | 6,460 | 5,350    | 5,390 | 6,230 |
| 6800    |     | 4,730   | 4,790 | 5,540 | 7,840  | 5,420   | 5,550 | 6,180 | 5,120    | 5,160 | 5,960 |
| 6900    |     | 4,300   | 4,350 | 5,040 | 7,130  | 4,930   | 4,850 | 5,620 | 4,650    | 4,690 | 5,420 |
| 6000    |     | 4,120   | 4,190 | 4,960 | 6,990  | 4,640   | 4,700 | 5,580 | 4,470    | 4,540 | 5,360 |
| 6200    |     | 4,190   | 4,260 | 5,270 | 7,240  | 4,760   | 4,830 | 5,930 | 4,580    | 4,650 | 5,700 |
| 6701    |     | 5,380   | 5,440 | 6,530 | 9,050  | 6,010   | 6,080 | 7,300 | 5,800    | 5,850 | 7,060 |
| 6801    |     | 5,150   | 5,200 | 6,250 | 8,660  | 5,750   | 5,820 | 6,990 | 5,540    | 5,600 | 6,750 |
| 6901    |     | 4,680   | 4,730 | 5,680 | 7,870  | 5,230   | 5,290 | 6,350 | 5,040    | 5,090 | 6,140 |
| 6001    |     | 4,470   | 4,540 | 5,520 | 7,750  | 5,040   | 5,120 | 6,190 | 4,850    | 4,910 | 5,980 |
| 6201    |     | 4,720   | 4,800 | 5,800 | 8,270  | 5,290   | 5,370 | 6,770 | 5,110    | 5,190 | 6,280 |
| 6702    |     | 5,960   | 6,010 | 7,340 | 10,260 | 6,660   | 6,730 | 8,200 | 6,440    | 6,500 | 7,910 |
| 6802    |     | 5,700   | 5,750 | 7,020 | 9,810  | 6,370   | 6,440 | 7,840 | 6,160    | 6,220 | 7,570 |
| 6902    |     | 5,180   | 5,230 | 6,380 | 8,920  | 5,790   | 5,850 | 7,130 | 5,600    | 5,650 | 6,880 |
| 6002    |     | 5,030   | 5,100 | 6,330 | 8,930  | 5,660   | 5,750 | 7,100 | 5,460    | 5,540 | 6,830 |
| 6202    |     | 5,130   | 5,210 | 6,450 | 9,210  | 5,860   | 5,950 | 7,220 | 5,760    | 5,830 | 6,940 |
| 6803    |     | 6,920   | 7,000 | 8,350 | 13,890 | 7,660   | 7,740 | 9,320 | 7,360    | 7,440 | 9,030 |
| 6903    |     | 6,290   | 6,360 | 7,590 | 12,170 | 6,960   | 7,040 | 8,470 | 6,690    | 6,760 | 8,210 |
| 6003    |     | 6,390   | 6,460 | 7,700 | 12,270 | 7,070   | 7,140 | 8,580 | 6,780    | 6,860 | 8,310 |
| 6203    |     | 6,470   | 6,540 | 7,790 | 12,380 | 7,160   | 7,240 | 8,680 | 6,890    | 6,960 | 8     |