


# L型ブロック

-0.1mm単位指定-



型式		材質
並級	精級	
SSLF	SSLG	SS400
SCLF	SCLG	S50C
SULF	—	SUS303
ALLF	—	A5052P

型式	指定0.1mm単位				
	A	B	L	C	D
SSLF SCLF SULF ALLF	10.0 200.0	10.0 100.0	10.0 200.0	5.0 200.0 (C≦A)	5.0 100.0 (B-D≦80.0 D≦B)

型式	指定0.1mm単位				
	A	B	L	C	D
SSLG SCLG	10.0 160.0	10.0 100.0	10.0 100.0	5.0 160.0 (C≦A)	5.0 100.0 (B-D≦60.0 D≦B)

Price 価格

数量	1~9	10~14	15~19
値引率	基準単価	5%	10%

数量スライド価格 (◎1円単位切り捨て) P89  
◎表示数量超過はお見積り

## 並級 (B10.0~60.0mm)

0.1mm単位		B 0.1mm単位											
A	L	10.0~30.0				30.1~50.0				50.1~60.0			
		SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF
10.0~60.0	10.0 60.0	1,940	2,010	5,040	4,850	2,860	3,010	7,760	5,390	3,450	3,640	9,860	5,930
60.1~100.0		2,050	2,130	6,690	6,130	3,050	3,230	10,360	6,800	3,570	3,760	13,120	7,480
100.1~130.0		2,360	2,480	8,220	6,960	3,930	4,130	13,180	7,730	4,570	4,820	16,720	8,500
130.1~160.0		2,750	2,910	9,830	7,870	4,630	4,850	15,810	8,740	5,430	5,720	20,120	9,610
160.1~180.0	60.1 100.0	2,860	3,040	10,590	8,580	4,660	4,890	16,990	9,540	5,620	5,920	21,710	10,500
180.1~200.0		3,010	3,210	11,490	9,130	5,020	5,280	18,230	10,150	5,840	6,140	23,460	11,160
10.0~60.0		2,050	2,130	6,690	5,340	3,050	3,230	10,360	5,930	3,570	3,760	13,120	6,510
60.1~100.0		2,560	2,730	9,150	6,650	3,780	3,970	14,030	7,390	5,310	5,560	18,920	8,130
100.1~130.0	2,990	3,210	12,060	7,740	4,450	4,700	18,540	8,600	6,330	6,670	25,070	9,460	
130.1~160.0	3,480	3,740	14,420	9,020	5,240	5,500	22,240	10,010	7,460	7,830	30,080	11,020	
160.1~180.0	100.1 130.0	3,650	3,960	15,330	9,680	5,590	5,850	21,900	10,750	8,050	8,440	33,250	11,830
180.1~200.0		3,860	4,210	17,340	12,780	5,940	6,230	26,260	14,200	8,630	9,080	36,430	15,620
10.0~60.0		2,360	2,480	8,220	5,570	3,930	4,130	13,180	6,180	4,570	4,890	16,860	6,800
60.1~100.0		2,990	3,210	11,350	7,380	4,450	4,700	17,440	8,200	6,330	6,670	23,610	9,020
100.1~130.0	130.1 160.0	3,710	4,000	14,320	7,990	5,770	6,030	22,220	8,870	7,360	7,730	29,140	9,760
130.1~160.0		4,320	4,660	18,210	9,370	6,820	7,170	28,460	10,410	8,710	9,140	37,270	11,460
160.1~180.0		4,480	4,700	19,740	10,760	6,990	7,340	30,990	11,960	9,450	9,910	41,250	13,160
180.1~200.0		4,720	5,150	21,780	13,910	7,500	7,870	33,940	15,460	10,130	10,670	45,850	17,000
10.0~60.0	160.1 180.0	2,750	2,910	9,830	6,650	4,630	4,850	15,810	7,390	5,430	5,720	20,120	8,130
60.1~100.0		3,480	3,740	13,570	8,170	5,240	5,500	20,930	9,070	7,460	7,830	28,330	9,970
100.1~130.0		4,320	4,660	17,140	8,960	6,820	7,170	26,780	9,960	8,710	9,140	35,080	10,960
130.1~160.0		5,090	5,500	21,910	9,830	7,990	8,410	34,160	10,920	10,280	10,790	44,810	12,020
160.1~180.0	180.1 200.0	5,310	5,700	23,790	12,220	8,430	8,850	37,510	13,580	11,060	11,590	49,510	14,930
180.1~200.0		5,580	6,140	26,260	16,430	8,690	9,150	40,700	18,250	11,870	12,450	54,280	20,080
10.0~60.0		2,860	3,040	10,750	8,460	4,660	4,890	17,040	9,410	5,620	5,920	21,910	10,350
60.1~100.0		3,650	3,960	15,850	9,300	5,590	5,850	24,500	10,330	8,050	8,440	33,250	10,350
100.1~130.0	180.1 200.0	4,480	4,700	19,740	9,990	6,990	7,340	30,990	11,100	9,450	9,910	41,250	12,220
130.1~160.0		5,310	5,700	23,960	13,430	8,430	8,850	34,070	14,920	11,060	11,590	49,510	16,410
160.1~180.0		5,400	5,920	26,220	14,520	8,630	9,040	40,900	16,130	11,880	12,650	54,930	17,750
180.1~200.0		5,720	6,310	28,690	17,340	9,220	9,700	44,830	19,270	12,990	13,640	60,320	21,200
10.0~60.0	180.1 200.0	3,010	3,210	11,720	9,250	5,020	5,280	19,600	10,270	5,840	6,140	24,360	11,300
60.1~100.0		3,860	4,210	17,340	10,280	5,940	6,230	26,750	11,410	8,630	9,080	36,430	12,560
100.1~130.0		4,720	5,150	21,780	11,370	7,500	7,870	33,940	12,630	10,130	10,670	45,250	13,900
130.1~160.0		5,580	6,140	26,260	14,510	8,690	9,150	40,700	16,120	11,870	12,450	54,280	17,730
160.1~180.0	200.0	5,720	6,310	28,690	16,150	7,760	8,170	44,830	17,950	12,990	13,640	54,750	19,740
180.1~200.0		6,300	6,990	31,700	18,250	10,220	11,050	49,920	20,290	13,990	13,980	60,320	22,320

## 並級 (B60.1~100.0mm)

0.1mm単位		B 0.1mm単位															
A	L	60.1~70.0				70.1~80.0				80.1~90.0				90.1~100.0			
		SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF
10.0~60.0	10.0 60.0	4,530	4,780	12,940	6,470	4,740	5,010	13,160	7,540	5,170	5,460	13,570	8,620	5,270	5,580	13,840	9,700
60.1~100.0		4,690	4,940	17,220	8,160	4,900	5,180	17,490	9,520	5,350	5,650	18,040	10,880	5,460	5,770	18,400	12,250
100.1~130.0		6,000	6,320	21,930	9,270	6,290	6,620	22,280	10,820	6,850	7,220	22,980	12,360	7,000	7,370	23,430	13,910
130.1~160.0		7,130	7,520	26,400	10,490	7,470	7,880	26,830	12,240	8,140	8,580	27,660	13,980	8,310	8,760	28,230	15,730
160.1~180.0	60.1 100.0	7,380	7,760	28,500	11,450	7,740	8,140	28,910	13,360	8,440	8,880	29,850	15,270	8,600	9,060	30,450	17,180
180.1~200.0		7,670	8,050	30,790	12,170	8,040	8,480	31,290	14,200	8,770	9,210	32,260	16,230	8,940	9,390	32,910	18,250
10.0~60.0		4,690	4,940	17,220	7,110	4,900	5,180	17,490	8,300	5,350	5,650	18,040	9,490	5,460	5,770	18,400	10,670
60.1~100.0		6,960	7,290	24,840	13,300	7,300	7,640	25,380	10,350	7,960	8,330	26,030	11,830	8,120	8,490	26,550	13,300
100.1~130.0	100.1 130.0	8,320	8,760	32,900	10,320	8,710	9,180	33,420	12,040	9,500	10,020	34,470	13,760	9,700	10,220	35,160	15,480
130.1~160.0		9,800	10,280	39,490	12,020	10,260	10,760	40,110	14,020	11,200	11,740	41,370	16,030	11,420	12,130	42,190	18,020
160.1~180.0		10,560	11,080	43,640	12,910	11,070	11,600	44,330	15,050	12,070	12,660	45,710	17,200	12,320	12,920	46,630	19,360
180.1~200.0		11,330	11,900	47,820	17,040	11,880	12,480	48,590	19,880	12,950	13,620	50,090	22,720	13,210	13,880	51,100	25,560
10.0~60.0	130.1 160.0	6,000	6,410	22,140	7,420	6,290	6,720	22,280	8,660	6,850	7,330	23,190	9,890	7,000	7,480	23,650	11,130
60.1~100.0		8,320	8,760	30,980	9,830	8,710	9,180	31,470	11,480	9,500	10,020	32,560	13,120	9,700	10,220	33,100	14,760
100.1~130.0		9,660	10,150	38,240	10,640	10,130	10,640	38,850	12,420	11,040	11,590	40,060	14,200	11,270	11,830	40,870	15,970
130.1~160.0		11,430	12,010	48,920	12,500	11,980	12,590	49,690	14,580	13,060	13,730	51,240	19,150	13,320	13,990	52,270	20,840
160.1~180.0	160.1 180.0	12,400	13,000	54,130	14,350	12,980	13,630	55,000	16,750	14,170	14,870	56,710	19,150	14,450	15,160	57,850	21,540
180.1~200.0		13,290	13,990	60,180	18,550	13,930	14,670	60,320	21,650	15,200	16,000	63,050	24,740	15,450	16,320	64,320	27,830
10.0~60.0		7,130	7,520	26,400	8,870	7,470	7,880	26,830	10,350	8,140	8,580	27,660	11,830	8,310	8,760	28,230	13,300
60.1~100.0		9,800	10,280	37,180	10,880	10,260	10,760	39,110	12,710	11,200	11,740	38,940	14,520	11,420	11,980	39,730	16,330
100.1~130.0	180.1 200.0	11,430	12,010	46,040	11,950	11,980	12,590	46,770	13,950	13,060	13,730	48,240	15,360	13,320	13,990	49,190	17,930
130.1~160.0		13,490	14,170	58,820	13,110	14,130	14,840	59,750	15,290	15,410	16,180	61,620	17,480	15,720	16,500	62,850	19,660
160.1~180.0		14,520	15,220	64,990	16,290	15,210	15,940	67,100	19,010	16,590	17,400	68,080	21,720	16,920	17,750	69,440	24,440
180.1~200.0		15,570	16,350	71,240	21,910	16,310	17,130	72,380	25,560	17,800	18,690	74,650	29,210	18,160	19,060	76,140	32,870
10.0~60.0	180.1 200.0	7,380	7,760	28,750	11,290	7,740	8,140	29,200	13,170	8,440	8,880	30,120	15,050	8,600	9,060	30,730	16,940
60.1~100.0		10,560	11,080	43,640	12,410	11,070	11,600	44,									