



PRECISION SHAFTS -ONE SIDE FEMALE SCREW TYPE / WITH WRENCH FLATS TYPE-

精密シャフト

一片端めねじ/片端めねじスパナ溝付き



軸端の直角度精度が高く(⊥0.03)、高精度を必要とする部分の組み合わせに適しています。

Technical drawing showing shaft specifications, material options (SUJ2, SUS440C, etc.), and surface treatments. Includes a table for D公差 and a diagram of the shaft with dimensions L, M, SC, W, and l1.

Table with columns: 型式 (Type), D, L (指定1mm単位), M (並目) 選択, スパナ溝寸法 (SC, W, l1), and c. Lists various shaft types like VFJT, VSFJT, VPFJT, VPSFJT, VRJT, VFJC, VSFJC, VPFJC, VPSFJC, VRJC.

Order and alteration instructions. Includes 'Order 注文例' and 'Alteration 追加加工' sections with examples of part numbers and specifications.



Table of alterations (追加加工) with columns: Alterations, Code, Spec., and ¥/1Code. Details various processing options like LKC, FC, WFC, SX, MSC, and MD.

Price and quantity information table. Includes 'Price 価格' and '数量スライド価格' sections with tables for quantity discounts and price ranges.

カタログ規格外品はこちら P137 CADデータフォルダ名: 01_Shafits

Main shaft specification table. Columns: 型式 (Type), D, and various length options (最短L, L51, L101, L201, L301, L451) with corresponding prices.

Main shaft specification table. Columns: 型式 (Type), D, and various length options (最短L, L50, L100, L200, L300, L450, L500) with corresponding prices.



精密タイプは(A)の様な段付加工が不要で、組付に有効です。

1 シャフト