


低圧用ねじ込み継手


-同径タイプ・異径タイプ-

価格改訂




Type	No.	Rc (PT)	SGPPU			SUTPU			SGPPU			SUTPU		
			B1 (L)	(A)	B	B1 (L)	(A)	B	1~9コ	¥基準単価	¥スライド単価	1~9コ	¥基準単価	¥スライド単価
SGPPU	6A	1/8	15	30	13	25	16	30	13	27	610	450	990	940
SUTPU	8A	1/4	19	33.5	13.5	31	20	34	14	34	560	530	990	940
SGPPU	10A	3/8	23	38	16	37	25	38	16	40	560	530	1,020	970
SUTPU	15A	1/2	27	41	17	42	30	41	17	46	470	450	1,170	1,110
SGPPU	20A	3/4	33	51	18.5	49	34	43	17	55	570	540	1,370	1,150
SUTPU	25A	1	41	54	20	59	44	51	20	64	780	740	2,090	1,980

*B1部の形状 SUTPU6A・8A=2面割 SUTPU10A・15A=6角 SUTPU20A・25A=8角 SGPPUは全て8角

■特長
ナットを回して外すことができるため、管自身を回すことなく取外しが可能な継手です。

Type	No.	Rc (PT)	SGPCS			SUTCS			SGPCS			SUTCS		
			(D)	L	(D)	L	(A)	(B)	1~9コ	¥基準単価	¥スライド単価	1~9コ	¥基準単価	¥スライド単価
SGPCS	8A	1/4	19	19	22	19	740	670	1,190	1,070				
SUTCS	10A	3/8	23	23	26	23	740	670	1,220	1,100				
SGPCS	15A	1/2	27	30	30	27	660	590	1,260	1,130				
SUTCS	20A	3/4	33	32	36	32	680	610	1,760	1,180				
SGPCS	25A	1	41	38	44	38	1,090	980	2,910	2,610				




Type	No.	Rc (PT)	D	(T)	(t)	(B)	(f)	(g)	P.C.D.	d	適用 ボルト径	¥基準単価	¥スライド単価
												1~9コ	10~30コ
SGPF	15A	1/2	95	13	12	38	1	51	70	15	M12	530	480
SUTFR	20A	3/4	100	15	14	42	1	56	75	15	M12	580	520
SGPF	25A	1	125	17	14	49	1	67	90	19	M16	830	750
SUTFR	32A	11/4	135	19	16	64	2	76	100	19	M16	1,020	920
SGPF	40A	11/2	140	20	16	68	2	81	105	19	M16	1,130	1,020
SUTFR	50A	2	155	24	16	82	2	96	120	19	M16	1,400	1,260

Type	No.	Rc (PT)	D	(T)	(t)	(B)	P.C.D.	d	適用 ボルト径	¥基準単価	¥スライド単価
										1~9コ	10~30コ
SGPF	15A	1/2	95	16	12	30	70	15	M12	1,180	1,020
SUTFR	20A	3/4	100	20	14	36	75	15	M12	1,330	1,170
SGPF	25A	1	125	20	14	44	90	19	M16	2,060	1,820
SUTFR	32A	11/4	135	22	16	53	100	19	M16	2,700	2,410
SGPF	40A	11/2	140	24	16	60	105	19	M16	2,640	2,400
SUTFR	50A	2	155	24	16	73	120	19	M16	3,090	2,740



Type	No.	Rc (PT)	(D)	A	¥基準単価		¥スライド単価	
					1~9コ	10~30コ	1~9コ	10~30コ
SGSTL	15A	1/2	27	27	980	830		
SGSTL	20A	3/4	33	32	1,110	940		
SGSTL	25A	1	41	38	1,440	1,220		



Type	No.	Rc (PT)	R (PT)	L	B	¥基準単価		¥スライド単価	
						1~9コ	10~30コ	1~19コ	20~50コ
SGPPB	12	1/8	1/4	18	17	230	200	250	180
SUTPB	13	1/8	3/8	19	21	210	200	250	180
SGPPB	14	1/8	1/2	22	26	320	240	290	230
SUTPB	23	1/4	3/8	19	21	220	200	250	180
SGPPB	24	1/4	1/2	22	26	210	170	310	230
SUTPB	26	1/4	3/4	25	32	240	200	430	350
SGPPB	28	1/4	1	28	38	320	250	660	570
SUTPB	34	3/8	1/2	22	26	210	180	290	230
SGPPB	36	3/8	3/4	25	32	210	170	430	350
SUTPB	38	3/8	1	28	38	290	260	630	570
SGPPB	46	1/2	3/4	25	32	210	170	430	350
SUTPB	48	1/2	1	28	38	280	230	660	570
SGPPB	68	3/4	1	28	38	280	230	660	570
SUTPB	60	3/4	1/4	31	46	460	410	910	590
SGPPB	80	1	1/4	31	46	460	410		