

## ヒンジピン

-止めねじ止めタイプ・ツバ付止めねじタイプ-

2日目納短縮



http://fa.misumi.jp

## ヒンジピン

-両面取タイプ-


2日目納短縮



http://fa.misumi.jp



Type	材質	硬度	表面処理
CLSG	S45C相当	—	四三酸化鉄皮膜
CLSGH	S45C相当	40~45HRC	—
PCLSG	S45C相当	—	無電解ニッケルメッキ
PCLSGH	S45C相当	40~45HRC	—
SCLSG	SUS304	—	—
SCLSGH	SUS440C相当	45~50HRC	—



Type	D	L	指定1mm単位		N	¥基準単価					
			F	E		CLSG	CLSGH	PCLSG	PCLSGH	SCLSG	SCLSGH
CLSG	3	5.0~50.0			0.5	360	380	460	550	540	710
CLSGH	4	5.0~50.0				360	380	460	560	540	720
PCLSG	5	10.0~60.0				380	400	490	580	570	750
PCLSGH	6	10.0~100.0				430	520	550	690	650	940
CLSG	8	10.0~100.0				480	550	620	760	730	950
CLSGH	10	15.0~100.0				540	550	600	800	790	1,100
PCLSG	12	15.0~200.0				590	780	840	1,040	900	1,160
PCLSGH	13	25.0~200.0				600	600	840	1,040	900	1,200
CLSG	14	25.0~200.0				680	620	880	1,090	1,030	1,330
CLSGH	15	30.0~200.0				710	630	920	1,130	1,080	1,400
PCLSG	17	30.0~200.0				770	860	990	1,190	1,160	1,490
PCLSGH	18	30.0~200.0				820	900	1,050	1,250	1,220	1,580
CLSG	20	30.0~200.0				870	950	1,120	1,330	1,300	1,680
CLSGH	22	30.0~200.0				910	980	1,170	1,390	1,360	1,760
PCLSG	25	30.0~200.0				980	1,050	1,440	1,640	1,820	2,180
PCLSGH						1,050	1,120	1,700	1,890	2,270	2,600

②SCLSGHは焼入により変色する場合があります。

## ツバ付止めねじタイプ



Type	D公差	材質	硬度	表面処理	D公差 (g6)
HCLSG		S45C相当	—	四三酸化鉄皮膜	3 -0.002 4 -0.008
HCLSGH		S45C相当	40~45HRC	—	4~6 -0.004 -0.012
PHCLSG		S45C相当	—	無電解ニッケルメッキ	8·10 -0.005 -0.014
PHCLSGH		S45C相当	40~45HRC	—	12~18 -0.006 -0.017
SHCLSG		SUS304	—	—	20~25 -0.007 -0.020
SHCLSGH		SUS440C相当	45~50HRC	—	

Type	D	L	指定0.1mm単位		(n)	(N)	¥基準単価					
			E	F			HCLSG	HCLSGH	PHCLSG	PHCLSGH	SHCLSG	SHCLSGH
HCLSG	3	5.0~50.0			5.5	2.9	560	690	660	830	770	970
HCLSG	4	5.0~50.0			6.5	3.9	580	730	690	880	810	1,030
HCLSG	5	10.0~60.0			8	4.9	660	830	790	990	920	1,160
HCLSG	6	10.0~100.0			9	5.8	680	880	820	1,050	960	1,220
HCLSG	8	10.0~100.0			12	7.8	710	910	860	1,100	1,020	1,290
HCLSG	10	15.0~100.0			14	9.8	750	950	900	1,150	1,060	1,350
HCLSG	12	15.0~200.0			17	11.8	850	1,080	1,060	1,340	1,280	1,610
HCLSG	13	20.0~200.0			18	12.8	930	1,180	1,150	1,430	1,340	1,630
HCLSG	14	20.0~200.0			19	13.8	970	1,250	1,170	1,490	1,370	1,730
HCLSG	15	20.0~200.0			20	14.8	1,000	1,270	1,210	1,530	1,430	1,800
HCLSG	17	20.0~200.0			21	15.8	1,020	1,300	1,240	1,570	1,470	1,850
HCLSG	18	20.0~200.0			23	17.8	1,050	1,340	1,280	1,620	1,510	1,910
HCLSG	20	20.0~200.0			26	19.8	1,060	1,360	1,300	1,650	1,540	1,950
HCLSG	22	20.0~200.0			27	21.8	1,250	1,470	1,510	1,780	1,880	2,380
HCLSG	25	20.0~200.0			30	24.8	1,430	1,570	1,720	1,910	2,220	2,800

②SHCLSGHは焼入により変色する場合があります。

## ツバ付止めねじタイプ



Order 注文例	型式	- L - E · F - E · F -	MMC	Alteration 追加工	抜きタップ追加工	ツバ厚変更	L寸公差変更
	CLSGH15	- 120.5 - F30 - T30	MMC				
	HCLSG20	- 120.3 - E10 - F10					
	SH-CLSG15	- 120.5 - F20 - E10					

脱脂洗浄サービス P124

## ツバ付止めねじタイプ

## 数量スライド価格 (1円未満切り捨て) P127

## 標準対応

## 個別対応

## 数量区分

## 小口

## 大口

## 大口

## 数量区分