

耐熱
グレード

HEAT INSULATION SHEETS

断熱板



ボルト4穴タイプ、ボルト6穴タイプ
以外の穴加工はこちら

☎ P.1309

2日納期短縮
出荷期短縮

断熱板 断熱板特注穴加工に対応いたします。
穴加工特注品のご相談は以下まで。
特注 穴加工 モールド特注窓口
TEL 03-5805-7232 FAX 03-5805-7235
MAIL coto@misumi.co.jp

☎ 追加加工価格も数量スライド適用 ☎ P.49



Price
価格

■数量スライド価格 (☎1円未満切り捨て) P.47

数量区分	標準対応			個別対応 大口
数 量	1～9	10～20	21～30	31～
値引率	基準単価	5%	10%	お見積り

☎表示数量超えはWOSにてご確認ください。

■寸法固定タイプ

型 式	T	A	¥基準単価 1~9枚		
			300	400	500
3		300	3,850	—	—
		400	5,390	8,080	—
		500	6,930	10,090	11,540
		600	9,470	11,540	13,250
		700	—	13,250	16,250
5		300	5,350	—	—
		400	7,490	10,780	—
		500	9,620	13,390	16,620
		600	11,120	16,620	19,670
		700	—	19,240	23,940
10		300	8,980	—	—
		400	12,570	17,480	—
		500	16,340	21,660	26,890
		600	20,350	26,890	33,510
		700	—	31,160	38,830
15		300	13,300	—	—
		400	18,880	24,890	—
		500	23,310	30,900	38,480
		600	29,070	38,480	42,800
		700	—	44,490	50,870

一寸法固定タイプ
HIPH



Alterations
追加加工

型 式 - A - B - T - D - E - S - F - G - (DW...etc.)
HIPHS-4H - A420 - B350 - T10 - D60 - E360.0 - S300.0 - DW120

☎穴加工付タイプに適用

Alterations	Code	Spec.	¥/1Code
DW DDW DT DDT	DW DDW DT DDT	DW・DT：D穴2ヶ所加工 DDW・DDT：D穴3ヶ所加工 DW DDW DT DDTは、F・G点からのセンター振り分けです。 DW DDW DT DDT=指定1mm単位 D+8≤DW≤A-(D+16) (D×2)+16≤DDW≤A-(D+16) D+8≤DT≤B-(D+16) (D×2)+16≤DDT≤B-(D+16)	DW・DT 300 DDW・DDT 400
ZC	ZC	T=5の皿ボルトM5用穴加工を 低頭ボルトM4用ザグリ加工に 変更します。(☎P.1319) d1=8, d2=4.5, t=3	0
HK	HK	ボルト穴を 通り穴に変更します。 ボルト穴径 を選択	4穴タイプ —200 6穴タイプ —300

■寸法指定タイプ・穴加工付タイプ

型 式		T	A	¥基準単価 1~9枚												
B																
				20~50	51~100	101~150	151~200	201~250	251~300	301~350	351~400	401~450	451~500	501~550	551~600	
一吋法指定タイプ HIPHS	3		20~50	260	—	—	—	—	—	—	—	—	—	—	—	—
			51~100	370	630	—	—	—	—	—	—	—	—	—	—	—
			101~150	630	670	1,190	—	—	—	—	—	—	—	—	—	—
			151~200	770	1,190	1,520	2,320	—	—	—	—	—	—	—	—	—
			201~250	900	1,520	1,710	2,570	3,230	—	—	—	—	—	—	—	—
			251~300	1,030	1,620	1,810	2,710	3,420	4,050	—	—	—	—	—	—	—
			301~350	1,160	2,070	2,380	3,560	3,960	4,860	5,940	—	—	—	—	—	—
			351~400	1,290	2,340	2,850	4,050	4,860	5,670	6,930	8,510	—	—	—	—	—
			401~450	1,420	2,600	3,770	4,960	6,120	6,480	7,920	9,580	9,900	—	—	—	—
			451~500	1,550	2,860	4,170	5,480	6,780	7,290	8,910	10,620	11,700	12,150	—	—	—
			501~550	1,750	3,250	4,760	6,260	7,780	8,550	9,900	11,700	12,150	12,600	13,950	—	—
			551~600	1,880	3,520	5,150	6,790	8,420	9,900	10,800	12,150	12,600	13,950	15,300	17,100	17,100
			601~650	2,000	3,770	5,550	7,300	9,050	10,800	11,700	12,600	13,950	15,300	17,100	18,900	18,900
			651~700	2,140	4,050	5,940	7,860	9,760	11,660	12,600	13,950	15,300	17,100	18,900	20,700	22,500
701~750	2,280	4,300	6,330	8,360	10,390	12,430	13,950	15,300	17,100	18,900	20,700	22,500	22,500			
751~800	2,400	4,560	6,720	8,850	11,020	13,210	15,300	17,100	18,900	20,700	22,500	25,200	25,200			
一穴加工付タイプ HIPHS	5	HIPHS価格(右表)に ボルト穴加工料金が 加算されます。	20~50	300	—	—	—	—	—	—	—	—	—	—	—	—
			51~100	430	720	—	—	—	—	—	—	—	—	—	—	—
			101~150	720	760	1,430	—	—	—	—	—	—	—	—	—	—
			151~200	1,020	1,430	1,710	2,570	—	—	—	—	—	—	—	—	—
			201~250	1,190	2,050	2,280	3,420	3,960	—	—	—	—	—	—	—	—
			251~300	1,370	2,280	2,470	3,710	4,500	5,630	—	—	—	—	—	—	—
			301~350	1,550	2,750	2,950	4,190	5,220	6,530	7,830	—	—	—	—	—	—
			351~400	1,710	3,100	3,710	5,270	6,480	7,880	9,140	11,340	—	—	—	—	—
			401~450	1,890	3,450	4,960	6,480	7,920	9,000	10,440	12,640	13,950	—	—	—	—
			451~500	2,070	3,800	5,470	6,720	8,910	10,130	11,750	14,040	14,580	17,100	—	—	—
			501~550	2,320	4,320	5,920	6,960	9,900	10,800	12,600	15,300	17,100	18,900	20,700	—	—
			551~600	2,500	4,660	6,300	7,200	10,800	11,700	13,050	17,100	18,900	20,700	22,500	24,300	24,300
			601~650	2,670	5,010	7,200	8,100	11,700	13,050	14,400	18,900	20,700	22,500	24,300	27,000	27,000
			651~700	2,850	5,360	7,860	10,350	12,790	14,400	16,200	20,250	22,500	24,300	27,000	29,700	29,700
701~750	3,020	5,700	8,430	11,100	13,770	16,200	18,900	21,630	24,300	27,000	29,700	31,950	31,950			
751~800	3,190	6,050	8,920	11,810	14,610	17,500	20,390	23,190	26,080	28,960	31,780	34,200	34,200			
一穴加工付タイプ HIPHS-4H	10	φDを0でご指定頂い た場合は-200円と なります。 φ穴加工付タイプは T≥5 A≥45, B≥45に適用	20~50	430	—	—	—	—	—	—	—	—	—	—	—	—
			51~100	510	860	—	—	—	—	—	—	—	—	—	—	—
			101~150	860	1,190	2,230	—	—	—	—	—	—	—	—	—	—
			151~200	1,570	2,230	2,850	4,050	—	—	—	—	—	—	—	—	—
			201~250	1,950	3,320	3,600	4,140	6,840	—	—	—	—	—	—	—	—
			251~300	2,230	3,690	3,960	5,180	7,560	9,450	—	—	—	—	—	—	—
			301~350	2,510	4,480	4,730	6,210	9,050	11,300	13,550	—	—	—	—	—	—
			351~400	2,800	5,040	5,720	7,250	11,210	13,230	15,800	18,360	—	—	—	—	—
			401~450	3,070	5,600	6,010	8,280	13,080	15,120	18,050	20,590	23,100	—	—	—	—
			451~500	3,350	6,170	8,990	9,320	14,460	17,010	20,050	22,820	25,610	27,900	—	—	—
			501~550	3,770	7,010	10,260	11,250	16,200	18,000	21,600	26,100	27,900	31,500	34,200	—	—
			551~600	4,050	7,580	11,100	12,600	18,000	20,700	24,300	27,900	31,500	34,200	36,900	39,600	39,600
			601~650	4,340	8,150	11,950	14,400	19,340	23,110	27,000	30,560	34,200	36,900	39,600	44,100	44,100
			651~700	4,620	8,710	12,790	16,200	20,740	24,780	28,760	32,790	36,900	39,600	44,100	45,900	45,900
701~750	4,900	9,270	13,640	18,000	22,360	26,720	31,020	35,370	39,600	43,660	45,900	48,880	48,880			
751~800	5,180	9,840	14,480	19,130	23,770	28,340	32,990	37,620	42,270	45,900	48,880	51,000	51,000			
一穴加工付タイプ HIPHS-6H	15		20~50	570	—	—	—	—	—	—	—	—	—	—	—	—
			51~100	740	1,240	—	—	—	—	—	—	—	—	—	—	—
			101~150	1,280	1,710	3,160	—	—	—	—	—	—	—	—	—	—
			151~200	2,380	3,140	3,780	5,670	—	—	—	—	—	—	—	—	—
			201~250	2,760	4,500	5,090	7,200	9,770	—	—	—	—	—	—	—	—
			251~300	3,160	5,530	5,810	8,690	11,210	14,000	—	—	—	—	—	—	—
			301~350	3,590	6,400	6,890	10,310	13,190	16,470	19,760	—	—	—	—	—	—
			351~400	3,990	7,230	8,510	12,600	16,250	19,580	23,040	26,170	—	—	—	—	—
			401~450	4,400	8,010	11,600	14,400	18,650	22,370	25,830	29,370	32,930	—	—	—	—
			451~500	4,790	8,780	12,790	16,200	20,600	24,570	28,540	32,510	36,480	40,450	—	—	—
			501~550	5,400	10,050	14,620	18,000	23,400	27,000	31,050	37,310	41,400	44,100	45,050	—	—
			551~600	5,810	10,820	15,820	19,350	25,200	29,700	33,750	40,500	44,100	45,050	50,150	53,550	53,550
			601~650	6,200	11,600	17,020	20,700	27,000	32,400	36,000	43,200	45,050	50,150	53,550	56,100	56,100
			651~700	6,610	12,440	18,210	22,050	28,800	35,100	38,700	45,900	50,150	53,550	56,100	62,900	62,900
701~750	7,000	13,220	19,410	23,400	30,600	36,900	41,850	46,750	53,550	56,100	62,900	69,700	69,700			
751~800	7,370	14,060	20,680	25,200	32,400	39,600	45,000	49,300	56,100	62,900	69,700	77,500	77,500			

一寸法指定タイプ
HIPHS

一寸穴加工付タイプ
HIPHS価格(右表)に
ボルト穴加工料金が
加算されます。

HIPHS-4H
4穴タイプ(HIPHS+1,000円)

HIPHS-6H
6穴タイプ(HIPHS+1,500円)

☎φDを0でご指定頂いた場合は—200円となります。

☎穴加工付タイプは
T≥5
A≥45, B≥45に適用

■寸法固定タイプ

型 式 Type	A	B	選択 T
HIPH	300	300	3
	400	300 400	
	500	300 400	5
	600	500	10
	700	400 500	15
	800	500	