

材料屋24でミスミ型番・出荷日・価格を一発表示!(http://misumi.jp/fa24)



種類	型式	材質
平鋼	FSS	SS400D
	FSC	S45CD
	FSSS	SUS304D
	FSSA	A6063S

6.3
32 (6.3/32)

Price 価格 (例) FSS-250-32-9のとき
A寸法 × 面積単価 = 価格(1円単位は切捨)
250 × 3.7 = 920(円)

数量スライド価格 (1円単位切り捨て) P.127
数量区分 標準対応 個別対応
小口 大口
数量 1~4 5~20 21~
値引率 基準単価 5% お見積り
表示数量超えはWOSにてご確認ください。

■ FSS (材質SS400D) 価格

A 1mm単位	T	B	5	6	9	10	12	16	19	22	25	30
30~50	16	16	AX14.2	AX14.2	AX14.3	AX14.1	AX14.4	AX14.5	—	—	—	—
51~150		15	AX6.9	AX6.9	AX7	AX7	AX7.1	AX7.2	—	—	—	—
151~300		14	AX3.9	AX3.9	AX4	AX4	AX4.2	AX4.2	—	—	—	—
301~800	13	AX2.8	AX2.8	AX2.7	AX2.8	AX2.7	AX2.4	—	—	—	—	
30~50	22	22	AX14.2	AX14.3	AX14.4	AX14.2	AX14.5	AX14.8	AX15	—	—	—
51~150		20	AX7	AX7	AX7.1	AX7.1	AX7.2	AX7.5	AX7.6	—	—	—
151~300		18	AX3.9	AX4	AX4.2	AX4.2	AX4.2	AX5.4	AX5.5	—	—	—
301~800	17	AX2.8	AX2.7	AX2.7	AX2.6	AX2.6	AX3.7	AX3.9	—	—	—	
30~50	25	25	AX14.3	AX14.3	AX14.5	AX14.4	AX14.6	AX14.9	AX15.1	AX16.5	—	—
51~150		23	AX7	AX7	AX7.1	AX7.1	AX7.3	AX7.5	AX8.4	AX9.1	—	—
151~300		21	AX4	AX4	AX4.3	AX4.2	AX4.3	AX5.5	AX5.7	AX6.7	—	—
301~800	20	AX2.7	AX2.7	AX2.6	AX2.5	AX2.5	AX3.7	AX3.8	AX4.9	—	—	
30~50	32	32	AX14.3	AX14.4	AX14.6	AX14.5	AX14.9	AX15.2	AX15.4	AX16.9	AX17.1	—
51~150		30	AX7.1	AX7.1	AX7.2	AX7.3	AX7.5	AX7.7	AX8.7	AX9.4	AX10.2	—
151~300		28	AX4	AX4.2	AX4.3	AX4.3	AX5.5	AX5.2	AX5.4	AX7.1	AX7.3	—
301~800	27	AX2.8	AX2.7	AX2.5	AX3.8	AX3.6	AX3.7	AX3.9	AX4.7	AX4.9	—	
30~50	38	38	AX14.4	AX14.5	AX14.8	AX14.8	AX15.1	AX15.4	AX15.7	AX17.3	AX17.5	—
51~150		36	AX7.1	AX7.1	AX7.3	AX7.5	AX7.6	AX7.9	AX8.9	AX9.6	AX10.5	—
151~300		34	AX4.2	AX4.3	AX4.5	AX4.5	AX5.3	AX6.5	AX6.8	AX6.2	AX6.4	—
301~800	33	AX2.7	AX2.6	AX3.7	AX3.6	AX3.7	AX4.8	AX5.1	AX6	AX6.3	—	
30~50	50	50	AX14.6	AX14.6	AX15	AX15	AX15.4	AX15.9	AX16.2	AX17.9	AX18.3	AX20.1
51~150		48	AX7.2	AX7.3	AX7.6	AX7.7	AX7.9	AX9.1	AX9.4	AX10.9	AX11.9	AX13.5
151~300		46	AX4.2	AX4.3	AX5.3	AX5.2	AX6.5	AX6.4	AX6.1	AX7.7	AX8.1	AX8.8
301~800	45	AX2.6	AX2.5	AX3.7	AX3.7	AX4.8	AX4.6	AX4.9	AX6.6	AX5.9	AX6.4	
30~50	60	60	—	AX16	AX16.4	AX16.4	AX16.8	AX17.4	AX17.8	—	AX19	—
51~150		58	—	AX7.8	AX8.1	AX8.9	AX9.3	AX10.2	AX11.4	—	AX12.5	—
151~300		56	—	AX5.6	AX5.4	AX6.4	AX6.5	AX6.3	AX6.7	—	AX10	—
301~800	55	—	AX3.8	AX3.7	AX4.7	AX4.8	AX6.1	AX6.4	—	AX6.3	—	
30~50	75	75	—	AX14.8	AX15.2	AX15.4	AX16.2	AX17.4	AX17.8	AX19.5	AX20.6	AX22.4
51~150		73	—	AX7.7	AX9.2	AX9.4	AX10.2	AX11.8	AX12.7	AX13.7	AX14.2	AX15.8
151~300		71	—	AX5.3	AX5.6	AX6.3	AX6.5	AX8.1	AX9.1	AX10.3	AX10.8	AX12.1
301~800	70	—	AX3.8	AX4.7	AX4.8	AX5	AX6.5	AX6.9	AX8	AX8.4	AX9.6	
30~50	100	100	—	AX21.3	AX22.6	AX22.7	AX23.4	AX24.3	AX25.7	AX29.8	AX32.1	AX36.8
51~150		98	—	AX9.9	AX11.2	AX11.2	AX12.6	AX14.4	AX16.2	AX19.1	AX20.5	AX24.2
151~300		96	—	AX8.1	AX7.1	AX8.5	AX8.4	AX10.7	AX11.8	AX14.3	AX15.6	AX18.4
301~800	95	—	AX5.8	AX6.2	AX6	AX5.8	AX7.7	AX8.7	AX11	AX12.2	AX14.3	
30~50	125	125	—	AX24.2	AX26	—	AX27	AX27.4	AX30.7	AX35.4	AX37.8	AX43.3
51~150		123	—	AX11.6	AX13.2	—	AX14.9	AX17	AX18.1	AX21.1	AX23.4	AX26.8
151~300		121	—	AX7.8	AX8.8	—	AX10.7	AX12.7	AX14.4	AX17	AX18.9	AX21
301~800	120	—	AX5.1	AX5.8	—	AX7.7	AX9.5	AX10.9	AX13.1	AX15	AX17.9	

■ FSC (材質S45CD) 価格

A 1mm単位	T	B	5	6	9	12	16	19	22	25	30
30~50	16	16	AX14.6	AX15	AX15.1	AX15.2	AX15.4	—	—	—	—
51~150		15	AX7.7	AX7.8	AX7.8	AX7.9	AX8.1	—	—	—	—
151~300		14	AX3.9	AX4	AX4	AX4.2	AX5.4	—	—	—	—
301~800	13	AX2.7	AX2.7	AX2.6	AX2.6	AX3.6	—	—	—	—	
30~50	22	22	AX14.8	AX15.1	AX15.2	AX15.3	AX15.7	—	—	—	—
51~150		20	AX7.8	AX7.9	AX7.9	AX8	AX8.4	—	—	—	—
151~300		18	AX4	AX4.2	AX4.3	AX5.4	AX5.3	—	—	—	—
301~800	17	AX2.8	AX2.7	AX2.6	AX3.7	AX3.6	—	—	—	—	
30~50	25	25	AX15.1	AX15.2	AX15.3	AX15.4	AX15.8	AX16.1	AX17.6	—	—
51~150		23	AX7.8	AX7.9	AX8	AX8.1	AX8.5	AX8.7	AX10	—	—
151~300		21	AX4.2	AX4.2	AX4.3	AX5.5	AX5.4	AX6.1	—	—	—
301~800	20	AX2.7	AX2.7	AX2.6	AX3.7	AX3.6	AX5.3	—	—	—	
30~50	32	32	—	AX15.3	AX15.4	AX15.7	AX16.1	AX16.5	AX18.2	AX18.5	—
51~150		30	—	AX8	AX8.1	AX8.4	AX8.7	AX9.1	AX10.4	AX11.3	—
151~300		28	—	AX4.4	AX5.5	AX5.3	AX6.3	AX6.4	AX6.3	AX6.5	—
301~800	27	—	AX2.7	AX3.7	AX3.6	AX4.8	AX4.7	AX5.8	AX6.1	—	
30~50	38	38	—	AX15.4	AX15.7	AX15.9	AX16.5	AX16.8	AX18.6	AX19	—
51~150		36	—	AX8.1	AX8.3	AX8.5	AX8.9	AX9.3	AX10.8	AX11.8	—
151~300		34	—	AX4.5	AX5.2	AX5.2	AX6.2	AX6.5	AX7.3	AX7.7	—
301~800	33	—	AX2.7	AX3.6	AX3.5	AX4.7	AX5	AX5.5	AX5.8	—	
30~50	50	50	—	AX15.7	AX15.9	AX16.2	AX17	AX17.5	AX19.5	AX20	AX22.1
51~150		48	—	AX8.4	AX8.6	AX8.8	AX10	AX10.4	AX12.2	AX13.2	AX15.1
151~300		46	—	AX5.7	AX5.2	AX6.1	AX6.2	AX6.4	AX8.6	AX9.6	AX10.5
301~800	45	—	AX3.9	AX3.7	AX4.6	AX5.5	AX6	AX6.1	AX7.2	AX7.8	
30~50	60	60	—	AX17.1	AX17.4	AX17.7	AX18.6	AX19.2	—	AX20.8	—
51~150		58	—	AX8.9	AX9.2	AX10.1	AX11.3	AX12	—	AX13.8	—
151~300		56	—	AX5.7	AX6.7	AX6.3	AX7.5	AX7.8	—	AX11.6	—
301~800	55	—	AX3.9	AX4.8	AX5.6	AX5.6	AX6	—	AX8.3	—	
30~50	75	75	—	AX15.7	AX16	AX16.9	AX18.4	AX19	AX21	AX22.2	AX24.2
51~150		73	—	AX8.6	AX10	AX10.9	AX12.7	AX13.3	AX15.1	AX15.7	AX17.5
151~300		71	—	AX5.5	AX6.3	AX7.2	AX9.1	AX9.6	AX11.7	AX12.7	AX14.3
301~800	70	—	AX4	AX4.8	AX5.6	AX7.4	AX7.8	AX9.3	AX10.3	AX11.7	
30~50	100	100	—	AX23	AX23.9	AX23.4	AX24.9	AX26.8	AX31.7	AX37.7	AX43.3
51~150		98	—	AX11.6	AX12.1	AX13.2	AX15.4	AX17.1	AX22.3	AX22.2	AX26.4
151~300		96	—	AX8.5	AX8.1	AX9.1	AX11.6	AX13.2	AX16.7	AX18.7	AX21.7
301~800	95	—	AX6	AX6.1	AX6.4	AX8.8	AX10.4	AX13	AX15.2	AX17.7	
30~50	125	125	—	AX26.4	AX27.5	AX27.1	AX29.5	AX31.7	—	AX25.9	—
51~150		123	—	AX13.3	AX14	AX15.2	AX17.9	AX20	—	AX25.4	—
151~300		121	—	AX8.3	AX9.9	AX11.3	AX13.7	AX15.8	—	AX22.6	—
301~800	120	—	AX7	AX6.7	AX8.3	AX10.6	AX12.6	—	AX17.6	—	

■ FSSS (材質SUS304D) 価格

A 1mm単位	T	B	5	6	9	10	12	16	19	22	25	30
30~50	15	15	AX20.3	AX20.9	AX21.8	—	—	—	—	—	—	—
51~150		14	AX11.5	AX11.7	AX12	—	—	—	—	—	—	—
151~300		13	AX5.2	AX5.3	AX5.7	—	—	—	—	—	—	—
301~800	12	AX3.3	AX3.4	AX3.7	—	—	—	—	—	—	—	
30~50	20	20	AX20.5	AX21.2	AX22.2	AX22.4	AX23.2	AX24	—	—	—	—
51~150		18	AX11.7	AX11.9	AX12.4	AX12.6	AX13.3	AX14.1	—	—	—	—
151~300		17	AX5.4	AX5.5	AX6	AX6.2	AX7	AX8.1	—	—	—	—
301~800	16	AX3.4	AX3.6	AX4.5	AX4.7	AX5.4	AX6.5	—	—	—	—	
30~50	25	25	AX20.9	AX21.5	AX22.6	AX22.9	AX23.8	AX24.8	AX26.5	—	AX29.8	—
51~150		23	AX11.9	AX12.2	AX12.8	AX13	AX13.9	AX14.7	AX16.6	—	AX17.4	—
151~300		22	AX5.6	AX5.8	AX6.4	AX6.4	AX7.6	AX8	AX9.2	AX11.7	—	AX14.1
301~800	21	AX3.6	AX3.8	AX5.3	AX5.5	AX6.4	AX7.6	AX10	—	AX12.6	—	
30~50	32	32	AX21.2	AX21.9	AX23.2	AX23.5	AX24.7	AX25.9	AX28	AX31.4	AX32.7	—
51~150		30	AX12.2	AX12.5	AX13.3	AX13.5	AX14.6	AX15.7	AX18.9	AX20.4	AX21.6	—
151~300		29	AX5.8	AX6.1	AX7.9	AX8.1	AX9.1	AX11	AX14.6	AX16.6	AX17.9	—
301~800	28	AX3.9	AX4.6	AX6.3	AX6.5	AX7.5	AX9.3	AX12.2	AX14.1	AX15.2	—	
30~50	38	38	AX21.5	AX22.2	AX23.7	AX24.2	AX25.3	AX26.7	AX30.1	AX33.7	AX35.3	—
51~150		36	AX12.5	AX12.8	AX13.7	AX14.1	AX15.2	AX16.4	AX20	AX22.7	AX25.1	—
151~300		35	AX6.1	AX6.4	AX8.8	AX9.1	AX10.1	AX12.7	AX16.5	AX17.9	AX20.3	—
301~800	34	AX4.6	AX5	AX6.7	AX7.4	AX8.5	AX10.5	AX14.1	AX16.2	AX17.4	—	
30~50	50	50	AX21.7	AX22.6	AX25.4	AX26.4	AX28.3	AX32.1	AX35.4	AX40.3	—	—
51~150		48	AX12	AX12.8	AX15.4	AX16.2	AX17.9	AX21.2	AX24.2	AX27.2	—	—
151~300		47	AX8.5	AX9.3	AX11.8	AX12.4	AX14.1	AX17.4	AX19.7	AX22.2		