

布ベーク
グレード

HEAT INSULATION SHEETS

断熱板



ボルト4穴タイプ、ボルト6穴タイプ
以外の穴加工はこちら

☎ P.1309

2日納期短縮
出荷期短縮

断熱板 断熱板特注穴加工に対応いたします。
穴加工特注品のご相談は以下まで。
特注 穴加工 専用ライン 03-5805-7232
モールド特注窓口 03-5805-7235
MAIL coto@misumi.co.jp FAX 03-5805-7235

☎ 追加加工価格も数量スライド適用 ☎ P.49



Price
価格

■数量スライド価格 (☎1円未満切り捨て) P.47

数量区分	標準対応			個別対応 大口
数 量	1～9	10～20	21～30	31～
値引率	基準単価	5%	10%	お見積り

☎表示数量超えはWOSにてご確認ください。

■寸法固定タイプ

型 式	T	A	¥ 基準単価 1~9枚		
			300	B	500
3		300	2,690	—	—
		400	3,500	4,040	—
		500	4,310	4,760	5,480
		600	5,210	6,290	7,190
		700	—	7,190	8,360
		800	—	—	9,350
5		300	4,220	—	—
		400	6,110	7,730	—
		500	7,550	9,620	10,700
		600	9,350	11,960	13,310
		700	—	12,860	14,840
		800	—	—	16,010
10		300	9,880	—	—
		400	13,030	17,800	—
		500	16,090	22,120	23,290
		600	19,240	27,430	29,050
		700	—	30,760	32,200
		800	—	—	33,550
15		300	11,490	—	—
		400	17,700	24,450	—
		500	21,930	28,860	32,280
		600	27,330	36,240	40,290
		700	—	42,270	46,680
		800	—	—	48,750

一寸法固定タイプ
HIPC

■寸法指定タイプ・穴加工付タイプ

型 式	T	A	¥ 基準単価 1～9枚													
			B													
			20～50	51～100	101～150	151～200	201～250	251～300	301～350	351～400	401～450	451～500	501～550	551～600		
一寸法指定タイプ HIPCS	3	20～50	170	—	—	—	—	—	—	—	—	—	—	—	—	
		51～100	330	370	—	—	—	—	—	—	—	—	—	—	—	
		101～150	370	400	840	—	—	—	—	—	—	—	—	—	—	
		151～200	460	520	1,060	1,110	—	—	—	—	—	—	—	—	—	
		201～250	570	740	1,290	1,360	1,930	—	—	—	—	—	—	—	—	
		251～300	660	870	1,540	1,620	2,290	2,780	—	—	—	—	—	—	—	
		301～350	740	1,000	1,760	1,860	2,640	3,210	3,240	—	—	—	—	—	—	
		351～400	820	1,110	2,000	2,100	3,010	3,660	3,690	4,250	—	—	—	—	—	
		401～450	920	1,250	2,220	2,360	3,370	4,100	4,120	4,560	4,770	—	—	—	—	
		451～500	1,000	1,380	2,460	2,620	3,740	4,530	4,580	5,040	5,260	5,750	—	—	—	
		501～550	1,110	1,560	2,810	3,000	4,290	5,210	5,240	6,060	6,640	6,930	7,190	—	—	
		551～600	1,210	1,700	3,030	3,220	4,640	5,510	5,640	6,580	7,220	7,530	7,790	11,300	—	
		601～650	1,290	1,820	3,270	3,480	4,990	6,090	6,130	7,100	7,800	8,070	8,430	12,180	—	
		651～700	1,380	1,940	3,510	3,630	5,370	6,560	6,610	7,580	8,340	8,750	9,010	13,070	—	
		701～750	1,470	2,080	3,730	3,990	5,740	6,990	7,060	8,120	8,930	9,290	9,670	13,990	—	
751～800	1,550	2,190	3,970	4,030	6,050	7,440	7,500	8,630	9,500	9,830	10,090	14,810	—			
ー寸法指定タイプ HIPCS	5	20～50	240	—	—	—	—	—	—	—	—	—	—	—	—	
		51～100	460	630	—	—	—	—	—	—	—	—	—	—	—	
		101～150	570	790	1,200	—	—	—	—	—	—	—	—	—	—	
		151～200	680	1,060	1,540	1,870	—	—	—	—	—	—	—	—	—	
		201～250	810	1,280	1,860	2,290	2,860	—	—	—	—	—	—	—	—	
		251～300	920	1,490	2,190	2,710	3,400	4,430	—	—	—	—	—	—	—	
		301～350	1,030	1,600	2,540	3,130	3,940	4,700	5,750	—	—	—	—	—	—	
		351～400	1,140	1,940	2,860	3,330	4,500	6,370	6,520	8,140	—	—	—	—	—	
		401～450	1,200	2,140	2,950	3,440	4,900	7,140	7,310	9,090	9,280	—	—	—	—	
		451～500	1,380	2,360	3,270	3,810	5,440	7,930	8,090	10,090	10,280	11,250	—	—	—	
		501～550	1,560	2,700	4,020	4,440	6,360	9,070	9,280	11,600	11,770	12,900	12,990	—	—	
		551～600	1,670	2,900	4,030	4,710	6,720	9,850	10,100	12,540	12,770	14,030	14,100	15,210	—	
		601～650	1,790	3,130	4,700	5,860	7,410	10,630	10,880	13,070	13,760	15,140	15,220	16,380	—	
		651～700	1,900	3,350	5,000	6,060	7,960	11,360	11,450	13,470	14,810	15,630	16,160	17,510	—	
		701～750	2,020	3,560	5,370	6,700	8,490	11,990	12,440	14,690	15,810	16,730	17,430	18,780	—	
751～800	2,140	3,780	5,680	7,130	9,020	12,260	12,800	15,230	16,170	16,850	17,510	18,860	—			
ー穴加工付タイプ 〔HIPCS価格(右表)に ボルト穴加工料金が 加算されます。〕 HIPCS—4H 4穴タイプ(HIPCS+1,000円) HIPCS—6H 6穴タイプ(HIPCS+1,500円)	10	20～50	440	—	—	—	—	—	—	—	—	—	—	—		
		51～100	840	1,200	—	—	—	—	—	—	—	—	—	—	—	
		101～150	1,060	1,600	2,910	—	—	—	—	—	—	—	—	—	—	
		151～200	1,280	2,010	3,710	4,440	—	—	—	—	—	—	—	—	—	
		201～250	1,490	2,410	4,440	5,380	6,720	—	—	—	—	—	—	—	—	
		251～300	1,710	2,820	5,300	6,590	8,100	10,390	—	—	—	—	—	—	—	
		301～350	1,870	2,950	6,110	7,590	9,370	12,030	12,270	—	—	—	—	—	—	
		351～400	2,010	3,290	6,910	8,610	10,640	13,680	13,960	18,740	—	—	—	—	—	
		401～450	2,140	3,490	7,700	9,620	11,900	15,320	15,650	21,000	21,030	—	—	—	—	
		451～500	2,410	4,030	8,510	10,650	13,170	16,970	17,330	23,290	23,330	24,500	—	—	—	
		501～550	2,890	5,060	9,720	11,320	13,340	19,440	19,860	24,950	26,690	28,120	28,280	—	—	
		551～600	3,100	5,460	10,510	11,860	14,690	20,220	21,540	28,890	28,970	30,530	30,710	32,700	—	
		601～650	3,320	5,870	11,310	12,740	15,500	21,300	21,710	31,170	31,250	32,940	33,130	35,290	—	
		651～700	3,540	6,270	11,800	13,350	16,440	21,570	22,790	32,370	33,090	33,860	34,430	36,280	—	
		701～750	3,750	6,680	12,000	13,480	17,520	22,250	23,870	32,910	33,320	34,800	35,060	36,950	—	
751～800	3,970	7,080	12,130	14,830	18,870	23,600	24,950	33,320	33,680	35,340	35,740	37,760	—			
❖ φDを0でご指定頂いた場合は－200円となります。 ❖ 穴加工付タイプはT≥5 A≥45, B≥45に適用	15	20～50	440	—	—	—	—	—	—	—	—	—	—	—		
		51～100	840	1,670	—	—	—	—	—	—	—	—	—	—	—	
		101～150	1,060	2,240	3,630	—	—	—	—	—	—	—	—	—	—	
		151～200	1,280	2,790	4,620	5,380	—	—	—	—	—	—	—	—	—	
		201～250	1,490	3,360	5,610	6,600	8,750	—	—	—	—	—	—	—	—	
		251～300	1,700	3,920	6,330	8,150	10,230	12,120	—	—	—	—	—	—	—	
		301～350	1,920	4,030	6,600	8,760	10,770	12,660	13,470	—	—	—	—	—	—	
		351～400	2,130	5,060	8,570	10,670	15,230	18,670	18,810	25,730	—	—	—	—	—	
		401～450	2,350	5,250	9,570	11,940	17,090	20,900	21,080	26,970	28,810	—	—	—	—	
		451～500	2,560	5,650	10,560	13,160	18,870	23,130	23,300	30,350	31,910	33,990	—	—	—	
		501～550	2,890	7,050	12,050	15,090	21,620	26,540	26,720	36,290	36,610	39,080	40,330	—	—	
		551～600	3,100	7,590	13,050	16,030	23,480	28,770	28,990	38,180	39,770	42,410	43,810	45,200	—	
		601～650	3,320	8,130	14,040	17,580	25,260	30,990	31,260	39,120	42,890	45,760	47,280	48,800	—	
		651～700	3,540	8,720	15,020	18,840	27,110	33,230	33,530	44,520	46,000	49,100	49,910	52,370	—	
		701～750	3,750	9,260	16,010	20,110	28,910	35,530	35,820	48,570	49,160	50,330	51,400	53,560	—	
751～800	3,940	9,850	17,040	21,380	30,750	37,760	37,770	49,520	49,920	51,270	52,610	55,310	—			