


L型ブロック

-0.1mm単位指定-



材料屋24でミスミ型番・出荷日・価格を一発表示!(<http://misumi.jp/fa24>)



型式	指定0.1mm単位					型式	指定0.1mm単位				
	A	B	L	C	D		A	B	L	C	D
SSLF SCLF SULF ALLF	10.0 200.0	10.0 100.0	10.0 200.0	5.0 200.0 (C≦A)	5.0 100.0 (B-D≦80.0 D≦B)	SSLG SCLG	10.0 160.0	10.0 100.0	10.0 100.0	5.0 160.0 (C≦A)	5.0 100.0 (B-D≦60.0 D≦B)

Price 価格

■数量スライド価格 (◎1円単位切り捨て) P127

数量区分	標準対応		個別対応
	小口	大口	
数量	1~9	10~14	15~20
値引率	基準単価	5%	10%

◎表示数量超えはWOSにてご確認ください。

■並級 (B10.0~60.0mm)

0.1mm単位		B 0.1mm単位											
A	L	10.0~30.0				30.1~50.0				50.1~60.0			
		SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF
10.0~60.0	10.0 60.0	2,220	2,300	5,300	5,150	3,270	3,440	8,150	5,720	3,940	4,150	10,360	6,290
60.1~100.0		2,340	2,430	7,030	6,500	3,480	3,690	10,880	7,210	4,070	4,290	13,780	7,930
100.1~130.0		2,700	2,830	8,640	7,380	4,490	4,710	13,840	8,200	5,210	5,500	17,560	9,010
130.1~160.0		3,140	3,320	10,330	8,350	5,280	5,530	16,610	9,270	6,200	6,530	21,130	10,190
160.1~180.0	60.1 100.0	3,270	3,470	11,120	9,100	5,320	5,580	17,840	10,120	6,410	6,750	22,800	11,130
180.1~200.0		3,440	3,660	12,070	9,680	5,730	6,020	19,150	10,760	6,660	7,000	24,640	11,830
10.0~60.0		2,340	2,430	7,030	5,670	3,480	3,690	10,880	6,290	4,070	4,290	13,780	6,910
60.1~100.0		2,920	3,120	9,610	7,050	4,310	4,530	14,740	7,840	6,060	6,340	19,870	8,620
100.1~130.0	100.1 130.0	3,410	3,660	12,670	8,210	5,080	5,360	19,470	9,120	7,220	7,610	26,330	10,030
130.1~160.0		3,970	4,270	15,150	9,570	5,980	6,270	23,360	10,620	8,510	8,930	31,590	11,690
160.1~180.0		4,170	4,520	16,100	10,270	6,380	6,670	23,000	11,400	9,180	9,630	34,920	12,540
180.1~200.0		4,410	4,800	18,210	13,550	6,780	7,110	27,580	15,060	9,840	10,360	38,260	16,560
10.0~60.0	100.1 130.0	2,700	2,830	8,640	5,910	4,490	4,710	13,840	6,560	5,210	5,580	17,710	7,210
60.1~100.0		3,410	3,660	11,920	7,830	5,080	5,360	18,320	8,700	7,220	7,610	24,800	9,570
100.1~130.0		4,230	4,560	15,040	8,470	6,580	6,880	23,340	9,410	8,400	8,820	30,600	10,350
130.1~160.0		4,930	5,320	19,130	9,940	7,780	8,180	29,890	11,040	9,930	10,420	39,140	12,150
160.1~180.0	130.1 160.0	5,110	5,360	20,730	11,410	7,970	8,370	32,540	12,680	10,780	11,300	43,320	13,950
180.1~200.0		5,390	5,880	22,870	14,750	8,550	8,980	35,640	16,390	11,550	12,170	48,150	18,020
10.0~60.0		3,140	3,320	10,330	7,050	5,280	5,530	16,610	7,840	6,200	6,530	21,130	8,620
60.1~100.0		3,970	4,270	14,250	8,670	5,980	6,270	21,980	9,620	8,510	8,930	29,750	10,570
100.1~130.0	160.1 180.0	4,930	5,320	18,000	9,500	7,780	8,180	28,120	10,560	9,930	10,420	36,840	11,620
130.1~160.0		5,810	6,270	23,010	10,420	9,110	9,590	35,870	11,580	11,720	12,310	47,060	12,750
160.1~180.0		6,060	6,500	24,980	12,960	9,620	10,090	39,390	14,400	12,610	13,220	51,990	15,830
180.1~200.0		6,370	7,000	27,580	17,420	9,910	10,440	42,740	19,350	13,540	14,200	57,000	21,290
10.0~60.0	160.1 180.0	3,270	3,470	11,290	8,970	5,320	5,580	17,900	9,980	6,410	6,750	23,010	10,980
60.1~100.0		4,170	4,520	16,650	9,860	6,380	6,670	25,730	10,950	9,180	9,630	34,920	10,980
100.1~130.0		5,110	5,360	20,730	10,590	7,970	8,370	32,540	11,770	10,780	11,300	43,320	12,960
130.1~160.0		6,060	6,500	25,160	14,240	9,620	10,090	35,280	15,820	12,610	13,220	51,990	17,400
160.1~180.0	180.1 200.0	6,160	6,750	27,540	15,400	9,840	10,310	42,950	17,100	13,550	14,430	57,680	18,820
180.1~200.0		6,530	7,200	30,130	18,390	10,520	11,060	47,080	20,430	14,810	15,550	63,340	22,480
10.0~60.0		3,440	3,660	12,310	9,810	5,730	6,020	20,580	10,890	6,660	7,000	25,580	11,980
60.1~100.0		4,410	4,800	18,210	10,900	6,780	7,110	28,090	12,100	9,840	10,360	38,260	13,320
100.1~130.0	180.1 200.0	5,390	5,880	22,870	12,060	8,550	8,980	35,640	13,390	11,550	12,170	47,520	14,740
130.1~160.0		6,370	7,000	27,580	15,390	9,910	10,440	42,740	17,090	13,540	14,200	57,000	18,800
160.1~180.0		6,530	7,200	30,130	17,120	8,850	9,380	47,080	19,030	14,810	15,550	63,340	20,930
180.1~200.0		7,190	7,970	33,290	19,350	11,660	12,600	52,420	21,510	15,950	16,940	73,340	23,660

■並級 (B60.1~100.0mm)

0.1mm単位		B 0.1mm単位															
A	L	60.1~70.0				70.1~80.0				80.1~90.0				90.1~100.0			
		SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF	SSLF	SCLF	SULF	ALLF
10.0~60.0	10.0 60.0	5,170	5,450	13,590	6,860	5,410	5,720	13,820	8,000	5,900	6,230	14,250	9,140	6,010	6,370	14,540	10,290
60.1~100.0		5,350	5,640	18,090	8,650	5,590	5,910	18,370	10,100	6,100	6,450	18,950	11,540	6,230	6,580	19,320	12,990
100.1~130.0		6,840	7,210	23,030	9,830	7,180	7,550	23,400	11,470	7,810	8,240	24,130	13,110	7,980	8,410	24,610	14,750
130.1~160.0		8,130	8,580	27,720	11,120	8,520	8,990	28,180	12,980	9,280	9,790	29,050	14,820	9,480	9,990	29,650	16,680
160.1~180.0	60.1 100.0	8,420	8,850	29,930	12,140	8,830	9,280	30,360	14,170	9,630	10,130	31,350	16,190	9,810	10,330	31,980	18,220
180.1~200.0		8,750	9,180	32,330	12,910	9,170	9,630	32,860	15,060	10,000	10,500	33,880	17,210	10,200	10,710	34,560	19,350
10.0~60.0		5,350	5,640	18,090	7,540	5,590	5,910	18,370	8,800	6,100	6,450	18,950	10,060	6,230	6,580	19,320	11,320
60.1~100.0		7,940	8,320	26,090	14,100	8,330	8,710	26,650	10,980	9,080	9,500	27,340	12,540	9,260	9,680	27,880	14,100
100.1~130.0	100.1 130.0	9,490	9,990	34,550	10,940	9,930	10,470	35,100	12,770	10,830	11,430	36,200	14,590	11,060	11,660	36,920	16,410
130.1~160.0		11,180	11,720	41,470	12,750	11,700	12,270	42,120	14,870	12,770	13,390	43,440	17,000	13,020	13,830	44,300	19,110
160.1~180.0		12,040	12,640	45,830	13,690	12,620	13,230	46,550	15,960	13,760	14,440	48,000	18,240	14,050	14,730	48,970	20,530
180.1~200.0		12,920	13,570	50,220	18,070	13,550	14,230	51,020	21,080	14,770	15,530	52,600	24,090	15,060	15,830	53,660	27,100
10.0~60.0	100.1 130.0	6,840	7,310	23,250	7,870	7,180	7,670	23,400	9,180	7,810	8,360	24,350	10,490	7,980	8,530	24,840	11,800
60.1~100.0		9,490	9,990	32,530	10,420	9,930	10,470	33,050	12,170	10,830	11,430	34,090	13,910	11,060	11,660	34,760	15,650
100.1~130.0		11,020	11,580	40,160	11,280	11,550	12,130	40,800	13,170	12,590	13,220	42,070	15,060	12,850	13,490	42,920	16,930
130.1~160.0		13,040	13,700	51,370	13,250	13,660	14,360	52,180	15,460	14,890	15,660	53,810	20,300	15,190	15,950	54,890	22,100
160.1~180.0	130.1 160.0	14,140	14,820	56,840	15,220	14,800	15,540	57,750	17,760	16,160	16,960	59,550	20,300	16,480	17,290	60,750	22,840
180.1~200.0		15,160	15,950	63,190	19,670	15,890	16,730	63,340	22,950	17,330	18,240	66,210	26,230	17,670	18,610	67,500	29,500
10.0~60.0		8,130	8,580	27,720	9,410	8,520	8,990	28,180	10,980	9,280	9,790	29,050	12,540	9,480	9,990	29,650	14,100
60.1~100.0		11,180	11,720	39,040	11,540	11,700	12,270	41,070	13,480	12,770	13,390	40,890	15,400	13,020	13,660	41,720	17,310
100.1~130.0	160.1 180.0	13,040	13,700	48,350	12,670	13,660	14,360	49,110	14,790	14,890	15,660	50,660	16,290	15,190	15,950	51,650	19,010
130.1~160.0		15,380	16,160	61,770	13,900	16,110</											