

WORKED CIRCULAR PLATES
円形プレート加工品

材料屋24でミスミ型番・出荷日・価格を一発表示!(<http://misumi.jp/fa24>)



Type	材質
SS	SS400
SC	S45C
AL	A5052P-H112
SU	SUS303


形状: F(フラット) 形状: X(凹) 形状: Z(凸)

穴加工: 下図より選択

※形状X・Zには、φWが入ります。

全周面取り C0.5

Type	形状	T	D	V	W	S	H: 穴数	穴種選択	呼び径	指定1mm単位
SS (SS400)	F (フラット)	8	60~300	10~100	20~260	5~25	0	N (通し穴)	5	35~280
SC (S45C)	X (凹)	10								
AL (A5052P)	Z (凸)	15								
SU (SUS303)		20								
		25								
		30								



穴種	通し穴	タップ穴	ザグリ穴	裏面ザグリ穴
Code	N	M	Z	ZR
形状図				
加工仕様	寸法 呼び径 d1 5 6 8 10 5.5 6.5 9 11 M×2<Tはタップ下穴が貫通 M×2≥Tはタップ貫通		寸法 ボルト呼び径 d1-h 5 6 8 10 5.5 6.5 9 11 9.5 11 14 18 ボルト呼び径6は T≥10(形状Zの場合、T-S≥10) 8・10はT≥15(形状Zの場合、T-S≥15)	

型式: Type 形状 T D V W S H 穴種選択 Code 呼び径 Q

例: SS F 10 -D100-V20 H2-N5-Q60

例: SS X 10 -D100-V50-W60-S5-H4-M5-Q80

8 日目出荷

※注文切替

例: SS Z 20 -D200-V30-W100-S10-H4-Z5 -Q150-WB-PC10-PX75

Q, PXの加工限界

通し穴(N)	呼び径
タップ穴(M)	5 6 8 10
ノック穴(PC)	5 6 8 10
d1	5.5 6.5 9 11
穴とD,W,V径との最小距離(b1)	4.5 5.5 7.5 9
穴間の最小距離(b2)	Qn/穴数(H)-d1(M)-(PC)≥d1(M)+(PC)

ザグリ穴(Z)	呼び径
裏面ザグリ穴(ZR)	5 6 8 10
d2	9.5 11 14 18
穴とD,W,V径との最小距離(b1)	2.5 3 4.5 5
穴間の最小距離(b2)	Qn/穴数(H)-d2-(PC)≥d2+(PC)

※図面上のH穴径は d1, M, d2を示します。

Alterations: W径公差変更, ノック穴加工

Code: WA, WB, WC, PC

Spec.: 形状, 公差, 指定

¥/1Code: 1,500, 3,000

Price 価格

数量スライド価格 (◎1円単位切り捨て) P.127

数量区分	標準対応	個別対応
	小口	大口
数量	1~9	10~14
値引率	基準単価	5% 10%

◎表示数量超えはWOSにてご確認ください。

■価格算出方法 下記形状価格に加工価格を加算してください。

(例) SSZ10-D100-V50-W60-S5-H4-N5-Q80のとき


形状価格 + H穴数単価 = 価格

4,050 + 2,800 = 6,850 (円)

■形状価格

Type	T	D	V	¥基準単価
				形状F 形状X 形状Z
SS (SS400)	8・10	60~100	10~50	5,430 6,890 6,890
			51~80	5,680 7,230 7,230
		101~200	10~50	8,840 10,320 10,320
			51~100	9,290 10,850 10,850
		201~300	10~50	13,030 14,960 14,960
			51~100	13,710 15,710 15,710
	15	60~100	10~50	6,060 7,760 7,760
			51~80	6,350 8,160 8,160
		101~200	10~50	10,170 12,070 12,070
			51~100	10,680 12,700 12,700
		201~300	10~50	15,850 18,010 18,010
			51~100	16,650 18,910 18,910
20	60~100	10~50	6,750 8,730 8,730	
		51~80	7,090 9,120 9,120	
	101~200	10~50	11,530 13,670 13,670	
		51~100	12,110 14,370 14,370	
	201~300	10~50	18,330 20,690 20,690	
		51~100	19,270 21,750 21,750	
25	60~100	10~50	7,470 9,590 9,590	
		51~80	7,840 10,090 10,090	
	101~200	10~50	12,960 15,340 15,340	
		51~100	13,640 16,100 16,100	
	201~300	10~50	20,900 23,460 23,460	
		51~100	21,920 24,640 24,640	
30	60~100	10~50	8,250 10,630 10,630	
		51~80	8,670 11,160 11,160	
	101~200	10~50	14,490 17,070 17,070	
		51~100	15,220 17,920 17,920	
	201~300	10~50	23,530 26,320 26,320	
		51~100	24,710 27,650 27,650	

Type	T	D	V	¥基準単価
				形状F 形状X 形状Z
AL (A5052P)	8・10	60~100	10~50	13,420 15,170 15,170
			51~80	14,080 15,950 15,950
		101~200	10~50	17,120 19,010 19,010
			51~100	18,010 19,960 19,960
		201~300	10~50	23,380 25,270 25,270
			51~100	24,570 26,540 26,540
	15	60~100	10~50	14,740 16,800 16,800
			51~80	15,490 17,670 17,670
		101~200	10~50	20,200 22,240 22,240
			51~100	21,220 23,380 23,380
		201~300	10~50	29,990 32,270 32,270
			51~100	31,520 33,900 33,900
20	60~100	10~50	16,240 18,520 18,520	
		51~80	17,070 19,440 19,440	
	101~200	10~50	24,130 26,440 26,440	
		51~100	25,330 27,780 27,780	
	201~300	10~50	36,760 39,390 39,390	
		51~100	38,610 41,380 41,380	
25	60~100	10~50	17,870 20,370 20,370	
		51~80	18,790 21,410 21,410	
	101~200	10~50	26,580 29,110 29,110	
		51~100	27,900 30,550 30,550	
	201~300	10~50	40,450 43,340 43,340	
		51~100	42,490 45,510 45,510	
30	60~100	10~50	19,440 22,240 22,240	
		51~80	20,420 23,360 23,360	
	101~200	10~50	32,320 35,110 35,110	
		51~100	33,950 36,860 36,860	
	201~300	10~50	50,630 54,010 54,010	
		51~100	53,160 56,720 56,720	



■加算価格

H	価格
穴無し	0
2穴	1,500
4穴	2,800
8穴	4,900
12穴	6,400

Type	T	D	V	¥基準単価
				形状F 形状X 形状Z
SC (S45C)	8・10	60~100	10~50	5,680 7,230 7,230
			51~80	5,970 7,590 7,590
		101~200	10~50	9,290 10,850 10,850
			51~100	9,760 11,390 11,390
		201~300	10~50	13,710 15,750 15,750
			51~100	14,420 16,530 16,530
	15	60~100	10~50	6,350 8,160 8,160
			51~80	6,690 8,590 8,590
		101~200	10~50	10,680 12,700 12,700
			51~100	11,220 13,350 13,350
		201~300	10~50	16,680 18,940 18,940
			51~100	17,500 19,880 19,880
20	60~100	10~50	7,090 9,120 9,120	
		51~80	7,470 9,590 9,590	
	101~200	10~50	12,130 14,400 14,400	
		51~100	12,740 15,120 15,120	
	201~300	10~50	19,300 21,780 21,780	
		51~100	20,270 22,890 22,890	
25	60~100	10~50	7,840 10,090 10,090	
		51~80	8,250 10,630 10,630	
	101~200	10~50	13,640 16,120 16,120	
		51~100	14,340 16,940 16,940	
	201~300	10~50	21,970 24,690 24,690	
		51~100	23,070 25,930 25,930	
30	60~100	10~50	8,670 11,160 11,160	
		51~80	9,120 11,720 11,720	
	101~200	10~50	15,250 17,960 17,960	
		51~100	16,040 18,860 18,860	
	201~300	10~50	24,760 27,700 27,700	
		51~100	25,980 29,110 29,110	

Type	T	D	V	¥基準単価
				形状F 形状X 形状Z
SU (SUS303)	8・10	60~100	10~50	15,030 16,360 16,360
			51~80	15,780 17,170 17,170
		101~200	10~50	26,000 27,320 27,320
			51~100	27,290 28,700 28,700
		201~300	10~50	41,080 42,400 42,400
			51~100	43,130 44,540 44,540
	15	60~100	10~50	18,790 20,230 20,230
			51~80	19,740 21,270 21,270
		101~200	10~50	35,450 36,930 36,930
			51~100	37,230 38,760 38,760
		201~300	10~50	59,400 60,900 60,900
			51~100	62,380 63,920 63,920
20	60~100	10~50	21,710 24,910 24,910	
		51~80	22,800 26,150 26,150	
	101~200	10~50	41,720 43,340 43,340	
		51~100	43,810 45,510 45,510	
	201~300	10~50	71,740 73,600 73,600	
		51~100	75,350 77,290 77,290	
25	60~100	10~50	26,010 27,780 27,780	
		51~80	27,320 29,180 29,180	
	101~200	10~50	52,360 54,130 54,130	
		51~100	54,980 56,850 56,850	
	201~300	10~50	90,650 92,760 92,760	
		51~100	95,190 97,400 97,400	
30	60~100	10~50	29,020 30,980 30,980	
		51~80	30,470 32,540 32,540	
	101~200	10~50	61,690 61,510 61,510	
		51~100	63,800 64,590 64,590	
	201~300	10~50	103,230 105,610 105,610	
		51~100	108,380 110,880 110,880	