


# ランナーロックピン

-ストレート・スタンダードタイプ-



RoHS10

適用	型式	材質	硬度
ツバ径 ノーマル	RLR	SKH51	58~60HRC
	RLRL		
	RLRB		
	RLRBF		
ツバ径 ラージ	RLRG		
	RLRGF		

## ■L寸固定タイプ

H	B	P	Y	型式		L									
				Type	D	指定0.1mm単位									
4	2	1.5	1.0	RLR (ツバ径ノーマル)	2	15 20 25 30 35 40									
5		2.3	1.8		3	15 20 25 30 35 40 45 50									
6	2.5	2.8	2.3	RLR	4	20 25 30 35 40 45 50 60 70 80									
7	3	3.3	2.8		5	20 25 30 35 40 45 50 60 70 80									
8		3.8	3.0	6	30 35 40 45 50 60 70 80										
10	4	5.8	5.0	8	30 35 40 45 50 60 70 80										

## ■L寸指定タイプ

H	B	P	Y	型式		L 指定0.1mm単位
				Type	D	
4	2	1.5	1.0	RLRL (ツバ径ノーマル)	2	10.0~100.0
5		2.0	1.5		2.5	
6	2.5	2.8	2.3	RLRL	3	10.0~100.0
7	3	3.3	2.8		4	
8		3.8	3.0	5	15.0~100.0	
10	4	5.8	5.0	6		
					8	

## ■L・P・Y寸指定タイプ

H	B	型式		指定0.1mm単位		
		Type	D	L	P	Y
4	2	RLRB (ツバ径ノーマル)	2	10.0~100.0	0.9~1.9	0.8~1.8
5			2.5		0.9~2.4	0.8~2.3
6	2.5	RLRB	3	10.0~100.0	0.9~2.9	0.8~2.8
7	3		4		1.1~3.9	1.0~3.8
8		3.3	5	1.3~4.9	1.2~4.8	
10	4	RLRB	6	15.0~100.0	1.6~5.9	1.5~5.8
13	5		8		2.1~7.9	2.0~7.8
			10		2.6~9.9	2.5~9.8

H	B	型式		指定0.1mm単位		
		Type	D	L	P	Y
4	2	RLRG (ツバ径ラージ)	2	10.0~100.0	0.9~1.9	0.8~1.8
6			2.5		0.9~2.4	0.8~2.3
7	2.5	RLRG	3	10.0~100.0	0.9~2.9	0.8~2.8
8	3		4		1.1~3.9	1.0~3.8
9		3.3	5	1.3~4.9	1.2~4.8	
11	4	RLRG	6	15.0~100.0	1.6~5.9	1.5~5.8
15	5		8		2.1~7.9	2.0~7.8
			10		2.6~9.9	2.5~9.8

## ■L・P・Y・B寸指定タイプ

H	型式		指定0.1mm単位			
	Type	D	L	P	Y	B
4	RLRBF (ツバ径ノーマル)	2	10.0~100.0	0.9~1.9	0.8~1.8	0.8~3.0
5		2.5		0.9~2.4	0.8~2.3	0.8~3.0
6	RLRBF	3	10.0~100.0	0.9~2.9	0.8~2.8	0.8~3.0
7		4		1.1~3.9	1.0~3.8	1.3~3.8
8	RLRBF	5	15.0~150.0	1.3~4.9	1.2~4.8	1.5~4.5
10		6		1.6~5.9	1.5~5.8	1.5~4.5
13	8	2.1~7.9	2.0~7.8	2.0~6.0		
		10		2.6~9.9	2.5~9.8	2.5~7.5

Ⓜ P>Y

H	型式		指定0.1mm単位			
	Type	D	L	P	Y	B
4	RLRGF (ツバ径ラージ)	2	10.0~100.0	0.9~1.9	0.8~1.8	0.8~3.0
6		2.5		0.9~2.4	0.8~2.3	0.8~3.0
7	RLRGF	3	10.0~100.0	0.9~2.9	0.8~2.8	0.8~3.0
8		4		1.1~3.9	1.0~3.8	1.3~3.8
9	RLRGF	5	15.0~150.0	1.3~4.9	1.2~4.8	1.5~4.5
11		6		1.6~5.9	1.5~5.8	1.5~4.5
15	8	2.1~7.9	2.0~7.8	2.0~6.0		
		10		2.6~9.9	2.5~9.8	2.5~7.5

Ⓜ P>Y



Order  
注文例

型式 - L - P - Y - B  
 RLR 3 - 30  
 RLRG 4 - 37.5 - P2.8 - Y2.3  
 RLRGF4 - 37.5 - P2.8 - Y2.3 - B3.0



Delivery  
出荷日

• RLR  
 • RLRL・RLRB・RLRG・RLRBF・RLRGF  
 在庫品 2 日日出荷



Alterations  
追加加工

型式 - L - P - Y - B - (HC・LKC...etc.)  
 RLRGF4 - 37.51 - P2.8 - Y2.3 - B2.4 - HC5-LKC  
 2 日日出荷

追加加工	記号	詳細
	HC	ツバ径変更 HC=指定0.1mm単位 Ⓜ D≤HC<H Ⓧ RLR適用不可
	LKC	全長公差変更 $L \pm 0.1 \dots L + 0.02$ (L寸0.01mm単位指定可) Ⓧ RLR適用不可
	TC	ツバ厚変更 TC=指定0.1mm単位 Ⓜ 2.0≤TC<4 Ⓜ TC使用時もL寸は指定寸法通りです。 Ⓜ 4-TC≤Lmax.-L Ⓧ RLR適用不可
	KC	1面ツバカット Ⓧ L<16は適用不可 Ⓧ RLR適用不可

追加加工	記号	詳細														
	TRN	ツバ下の逃げ加工 (プレートの面取が不要) Ⓧ RLR適用不可														
	DR	D寸端部 R加工 (R0.1~0.3) 簡易加工のため厳密なR形状ではありません。 Ⓧ RLR適用不可														
	DC	D寸指定 (0.1mm単位) Ⓜ P≤DC-0.1 Ⓧ RLR・RLRLは適用不可 Ⓜ Y≤DC-0.2 Ⓧ D=2・2.5は適用不可 <table border="1"> <thead> <tr> <th>D</th> <th>DC指定範囲 (t6)</th> </tr> </thead> <tbody> <tr><td>3</td><td>2.0~2.9</td></tr> <tr><td>4</td><td>3.0~3.9</td></tr> <tr><td>5</td><td>4.0~4.9</td></tr> <tr><td>6</td><td>5.0~5.9</td></tr> <tr><td>8</td><td>6.0~7.9</td></tr> <tr><td>10</td><td>8.0~9.9</td></tr> </tbody> </table>	D	DC指定範囲 (t6)	3	2.0~2.9	4	3.0~3.9	5	4.0~4.9	6	5.0~5.9	8	6.0~7.9	10	8.0~9.9
D	DC指定範囲 (t6)															
3	2.0~2.9															
4	3.0~3.9															
5	4.0~4.9															
6	5.0~5.9															
8	6.0~7.9															
10	8.0~9.9															